



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminum track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily.
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors.
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided.

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit Square RCS750

Application

- Retail
- Indoor architectural lighting

Versions



RBS750 recessed track, white



RCS750 track, white



RCS750 track, alu





RBS750 recessed track, alu




RCS750 track, black

Dimensional drawing



3-circuit Square RCS750

Dimensional drawing



Operating and Electrical	
Protection class IEC	Safety class I
Protection class IEC	Safety class I
Mechanical and Housing	
Ingress protection code	IP30
Ingress protection code	IP30
Approval and Application	
CE mark	Yes
CE mark	Yes
Glow-wire test	Temperature 850 °C, duration 5 s
Glow-wire test	Temperature 850 °C, duration 5 s

Mechanical and Housing		
Order Code	Full Product Name	Accessory color
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	White
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	White
910500188815	RCS750 3C L1000 WH (XTS4100-3)	White
910500188915	RCS750 3C L2000 WH (XTS4200-3)	White
910500189015	RCS750 3C L3000 WH (XTS4300-3)	White
910500189115	RCS750 3C L4000 WH (XTS4400-3)	White
910500188415	RCS750 3C L1000 ALU (XTS4100-1)	Aluminum
910500188515	RCS750 3C L2000 ALU (XTS4200-1)	Aluminum
910500188615	RCS750 3C L3000 ALU (XTS4300-1)	Aluminum
910500188715	RCS750 3C L4000 ALU (XTS4400-1)	Aluminum
910930009018	RBS750 3C L2000 ALU (XTSF4200-1)	Aluminum
910930009218	RBS750 3C L3000 ALU (XTSF4300-1)	Aluminum
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Black
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Black
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Black

3-circuit Square RCS750



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2025, December 11 – data subject to change