



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminum track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily.
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors.
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided.

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit Square RCS750

Application

- Retail
- Indoor architectural lighting

Versions



RBS750 recessed track, white







RCS750 track, white




RBS750 recessed track, alu

Dimensional drawing



3-circuit Square RCS750

Dimensional drawing



Operating and Electrical

| | |
|----------------------|----------------|
| Protection class IEC | Safety class I |
| Protection class IEC | Safety class I |

Mechanical and Housing

| | |
|-------------------------|------|
| Ingress protection code | IP30 |
| Ingress protection code | IP30 |

Approval and Application

| | |
|----------------|----------------------------------|
| CE mark | Yes |
| CE mark | Yes |
| Glow-wire test | Temperature 850 °C, duration 5 s |
| Glow-wire test | Temperature 850 °C, duration 5 s |

Mechanical and Housing

| Order Code | Full Product Name | Accessory color |
|--------------|----------------------------------|-----------------|
| 910930009118 | RBS750 3C L2000 WH (XTSF4200-3) | White |
| 910930009318 | RBS750 3C L3000 WH (XTSF4300-3) | White |
| 910500188815 | RCS750 3C L1000 WH (XTS4100-3) | White |
| 910500188915 | RCS750 3C L2000 WH (XTS4200-3) | White |
| 910500189015 | RCS750 3C L3000 WH (XTS4300-3) | White |
| 910500189115 | RCS750 3C L4000 WH (XTS4400-3) | White |
| 910500188415 | RCS750 3C L1000 ALU (XTS4100-1) | Aluminum |
| 910500188515 | RCS750 3C L2000 ALU (XTS4200-1) | Aluminum |
| 910500188615 | RCS750 3C L3000 ALU (XTS4300-1) | Aluminum |
| 910500188715 | RCS750 3C L4000 ALU (XTS4400-1) | Aluminum |
| 910930009018 | RBS750 3C L2000 ALU (XTSF4200-1) | Aluminum |
| 910930009218 | RBS750 3C L3000 ALU (XTSF4300-1) | Aluminum |
| 910930013218 | RCS750 3C L1000 BK (XTS4100-2) | Black |
| 910930013318 | RCS750 3C L2000 BK (XTS4200-2) | Black |
| 910930013418 | RCS750 3C L3000 BK (XTS4300-2) | Black |
| 910930013518 | RCS750 3C L4000 BK (XTS4400-2) | Black |

