



# RCS750 3-circuit square track system – flexible and multifunctional

## 3-circuit square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminium track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available.

### Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided

### Features







- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

# 3-circuit square RCS750

## Application

- Retail
- Indoor architectural lighting

## Dimensional drawing



## 3-circuit square RCS750

### Operating and Electrical

Protection class IEC	Safety class I
----------------------	----------------

Protection class IEC	Safety class I
----------------------	----------------

### Mechanical and Housing

Ingress protection code	IP30
-------------------------	------

Ingress protection code	IP30
-------------------------	------

### Approval and Application

CE mark	Yes
---------	-----

CE mark	Yes
---------	-----

Glow-wire test	Temperature 850
----------------	-----------------

°C, duration 5 s
------------------

Glow-wire test	Temperature 850
----------------	-----------------

°C, duration 5 s
------------------

### Mechanical and Housing

Order Code	Full Product Name	Accessory colour
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	White
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	White
910500188815	RCS750 3C L1000 WH (XTS4100-3)	White
910500188915	RCS750 3C L2000 WH (XTS4200-3)	White
910500189015	RCS750 3C L3000 WH (XTS4300-3)	White
910500189115	RCS750 3C L4000 WH (XTS4400-3)	White
910500188415	RCS750 3C L1000 ALU (XTS4100-1)	Aluminium
910500188515	RCS750 3C L2000 ALU (XTS4200-1)	Aluminium
910500188615	RCS750 3C L3000 ALU (XTS4300-1)	Aluminium
910500188715	RCS750 3C L4000 ALU (XTS4400-1)	Aluminium
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Black
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Black
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Black

