



It delivers super flexibility, a complete product range and seamless system integration for hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application



- Guest room
- Bath room
- Corridor
- Lobby

Specifications



Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W

Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class	Class II & Class III for MR16 version
IEC61140	
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners



Dimensional drawing



Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116



General Information

Driver included	Yes
Number of gear units	1 unit

Light Technical

Color rendering index (CRI)	>90
Optic type	-

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No

Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

Mechanical and Housing

Optical cover type	PMMA
Housing Color	Grey
Mech. impact protection code	IK04
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 600 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	SDCM<3
Luminous flux tolerance	-10% / +10%

Over Time Performance (IEC Compliant)

Median useful life L80B50	50,000 hour(s)
---------------------------	----------------

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401720892	RS378B P6 927 PSU-E NB M55	- degree(s)	2700 K	92 lm/W	3,864 lm
911401720902	RS378B P6 930 PSU-E NB M55	- degree(s)	3000 K	87 lm/W	1,305 lm
911401720912	RS378B P6 940 PSU-E NB M55	- degree(s)	4000 K	80 lm/W	1,200 lm
911401720922	RS378B P6 927 PSU-E MB M55	- degree(s)	2700 K	77 lm/W	2,540 lm
911401720932	RS378B P6 930 PSU-E MB M55	- degree(s)	3000 K	97 lm/W	4,074 lm
911401720942	RS378B P6 940 PSU-E MB M55	- degree(s)	4000 K	82 lm/W	900 lm
911401720952	RS378B P6 927 PSU-E WB M55	- degree(s)	2700 K	92 lm/W	3,864 lm
911401720962	RS378B P6 930 PSU-E WB M55	- degree(s)	3000 K	100 lm/W	1,500 lm
911401720972	RS378B P6 940 PSU-E WB M55	- degree(s)	4000 K	93 lm/W	1,400 lm
911401720982	RS378B P11 927 PSU-E NB M55	-	2700 K	76 lm/W	836 lm
911401720992	RS378B P11 930 PSU-E NB M55	-	3000 K	85 lm/W	510 lm
911401721002	RS378B P11 940 PSU-E NB M55	-	4000 K	95 lm/W	570 lm
911401721012	RS378B P11 927 PSU-E MB M55	-	2700 K	87 lm/W	957 lm
911401721022	RS378B P11 930 PSU-E MB M55	-	3000 K	85 lm/W	510 lm
911401721032	RS378B P11 940 PSU-E MB M55	-	4000 K	90 lm/W	540 lm
911401721042	RS378B P11 927 PSU-E WB M55	-	2700 K	87 lm/W	957 lm
911401721052	RS378B P11 930 PSU-E WB M55	-	3000 K	90 lm/W	540 lm
911401721062	RS378B P11 940 PSU-E WB M55	-	4000 K	95 lm/W	570 lm
911401721622	RS378B P42 930 PSU-E NB M102	-	3000 K	71 lm/W	2,350 lm
911401721632	RS378B P42 940 PSU-E NB M102	-	4000 K	73 lm/W	2,400 lm
911401721642	RS378B P42 927 PSU-E MB M102	-	2700 K	106 lm/W	2,540 lm
911401721652	RS378B P42 930 PSU-E MB M102	- degree(s)	3000 K	71 lm/W	2,350 lm
911401721662	RS378B P42 940 PSU-E MB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
911401721682	RS378B P42 930 PSU-E WB M102	- degree(s)	3000 K	71 lm/W	2,350 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401721692	RS378B P42 940 PSU-E WB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
911401721432	RS378B P24 927 PSU-E NB M70	-	2700 K	92 lm/W	1,012 lm
911401721442	RS378B P24 930 PSU-E NB M70	-	3000 K	100 lm/W	1,100 lm
911401721452	RS378B P24 940 PSU-E NB M70	-	4000 K	78 lm/W	1,170 lm
911401721472	RS378B P24 930 PSU-E MB M70	-	3000 K	100 lm/W	1,100 lm
911401721482	RS378B P24 940 PSU-E MB M70	-	4000 K	90 lm/W	1,350 lm
911401721492	RS378B P24 927 PSU-E WB M70	-	2700 K	92 lm/W	1,012 lm
911401721502	RS378B P24 930 PSU-E WB M70	-	3000 K	76 lm/W	1,140 lm
911401721512	RS378B P24 940 PSU-E WB M70	-	4000 K	94 lm/W	1,410 lm
911401721522	RS378B P33 927 PSU-E NB M87	-	2700 K	100 lm/W	1,500 lm
911401721532	RS378B P33 930 PSU-E NB M87	-	3000 K	98 lm/W	2,350 lm
911401721542	RS378B P33 940 PSU-E NB M87	-	4000 K	100 lm/W	2,400 lm
911401721562	RS378B P33 930 PSU-E MB M87	-	3000 K	98 lm/W	2,350 lm
911401721572	RS378B P33 940 PSU-E MB M87	-	4000 K	100 lm/W	2,400 lm
911401721592	RS378B P33 930 PSU-E WB M87	-	3000 K	98 lm/W	2,350 lm
911401721602	RS378B P33 940 PSU-E WB M87	-	4000 K	100 lm/W	2,400 lm
911401721252	RS378B P15 927 PSU-E NB M55	-	2700 K	85 lm/W	510 lm
911401721262	RS378B P15 930 PSU-E NB M55	-	3000 K	97 lm/W	580 lm
911401721272	RS378B P15 940 PSU-E NB M55	-	4000 K	76 lm/W	836 lm
911401721282	RS378B P15 927 PSU-E MB M55	-	2700 K	83 lm/W	500 lm
911401721292	RS378B P15 930 PSU-E MB M55	-	3000 K	91 lm/W	545 lm
911401721302	RS378B P15 940 PSU-E MB M55	-	4000 K	105 lm/W	630 lm
911401721312	RS378B P15 927 PSU-E WB M55	-	2700 K	90 lm/W	540 lm
911401721322	RS378B P15 930 PSU-E WB M55	-	3000 K	97 lm/W	580 lm
911401721332	RS378B P15 940 PSU-E WB M55	-	4000 K	87 lm/W	957 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401720892	RS378B P6 927 PSU-E NB M55	6 W	911401721432	RS378B P24 927 PSU-E NB M70	24 W
911401720902	RS378B P6 930 PSU-E NB M55	6 W	911401721442	RS378B P24 930 PSU-E NB M70	24 W
911401720912	RS378B P6 940 PSU-E NB M55	6 W	911401721452	RS378B P24 940 PSU-E NB M70	24 W
911401720922	RS378B P6 927 PSU-E MB M55	6 W	911401721472	RS378B P24 930 PSU-E MB M70	24 W
911401720932	RS378B P6 930 PSU-E MB M55	6 W	911401721482	RS378B P24 940 PSU-E MB M70	24 W
911401720942	RS378B P6 940 PSU-E MB M55	6 W	911401721492	RS378B P24 927 PSU-E WB M70	24 W
911401720952	RS378B P6 927 PSU-E WB M55	6 W	911401721502	RS378B P24 930 PSU-E WB M70	24 W
911401720962	RS378B P6 930 PSU-E WB M55	6 W	911401721512	RS378B P24 940 PSU-E WB M70	24 W
911401720972	RS378B P6 940 PSU-E WB M55	6 W	911401721522	RS378B P33 927 PSU-E NB M87	33 W
911401720982	RS378B P11 930 PSU-E NB M55	11 W	911401721532	RS378B P33 930 PSU-E NB M87	33 W
911401720992	RS378B P11 930 PSU-E NB M55	11 W	911401721542	RS378B P33 940 PSU-E NB M87	33 W
911401721002	RS378B P11 940 PSU-E NB M55	11 W	911401721562	RS378B P33 930 PSU-E MB M87	33 W
911401721012	RS378B P11 927 PSU-E MB M55	11 W	911401721572	RS378B P33 940 PSU-E MB M87	33 W
911401721022	RS378B P11 930 PSU-E MB M55	11 W	911401721592	RS378B P33 930 PSU-E WB M87	33 W
911401721032	RS378B P11 940 PSU-E MB M55	11 W	911401721602	RS378B P33 940 PSU-E WB M87	33 W
911401721042	RS378B P11 927 PSU-E WB M55	11 W	911401721252	RS378B P15 927 PSU-E NB M55	15 W
911401721052	RS378B P11 930 PSU-E WB M55	11 W	911401721262	RS378B P15 930 PSU-E NB M55	15 W
911401721062	RS378B P11 940 PSU-E WB M55	11 W	911401721272	RS378B P15 940 PSU-E NB M55	15 W
911401721622	RS378B P42 930 PSU-E NB M102	42 W	911401721282	RS378B P15 927 PSU-E MB M55	15 W
911401721632	RS378B P42 940 PSU-E NB M102	42 W	911401721292	RS378B P15 930 PSU-E MB M55	15 W
911401721642	RS378B P42 927 PSU-E MB M102	42 W	911401721302	RS378B P15 940 PSU-E MB M55	15 W
911401721652	RS378B P42 930 PSU-E MB M102	42 W	911401721312	RS378B P15 927 PSU-E WB M55	15 W
911401721662	RS378B P42 940 PSU-E MB M102	42 W	911401721322	RS378B P15 930 PSU-E WB M55	15 W
911401721682	RS378B P42 930 PSU-E WB M102	42 W	911401721332	RS378B P15 940 PSU-E WB M55	15 W
911401721692	RS378B P42 940 PSU-E WB M102	42 W			

