

Greenspace Flex

RS378B



It delivers super flexibility, a complete product range and seamless system integration for hospitality customers..

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Applications

- Guest room
- Bath room

- Corridor
- Lobby

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Versions

RS378B P11 M55



Greenspace Flex RS378B
P6&P11 M55



Greenspace Flex RS378B P42
M102



RS378B P24 M70



RS378B P33 M87



RS378B P42 M102



Greenspace Flex, Prof GCGM



RS378B P15 M55




RS378B P6 M43




Greenspace Flex RS378B P15
M55




Dimensional drawing



RS378B P42 940 PSU-E MB M102




RS378B P6 930 PSU-E NB M55




RS378B P33 927 PSU-E NB M87


Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116




RS378B



RS378B P24 930 PSD-E MB M70



RS378B P15 927 PSD-E NB M55



RS378B P6 930 PSU-E MB M43

General Information

Number of gear units	1 unit
Driver included	Yes

Light Technical

Color rendering index (CRI)	>90
Optic type	-

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class II

Mechanical and Housing

Housing Color	Grey
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	PMMA

Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	SDCM<3

Over Time Performance (IEC Compliant)

Median useful life L80B50	50,000 hour(s)
---------------------------	----------------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
911401536371	RS378B P11 930 PSD-E WB M55	957 lm	3000 K	87 lm/W	-
911401536571	RS378B P11 940 PSD-E MB M55	1,012 lm	4000 K	92 lm/W	-
911401720892	RS378B P6 927 PSU-E NB M55	3,864 lm	2700 K	92 lm/W	- degree(s)
911401720902	RS378B P6 930 PSU-E NB M55	1,305 lm	3000 K	87 lm/W	- degree(s)
911401720932	RS378B P6 930 PSU-E MB M55	4,074 lm	3000 K	97 lm/W	- degree(s)
911401720962	RS378B P6 930 PSU-E WB M55	1,500 lm	3000 K	100 lm/W	- degree(s)
911401720972	RS378B P6 940 PSU-E WB M55	1,400 lm	4000 K	93 lm/W	- degree(s)

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
911401720992	RS378B P11 930 PSU-E NB M55	510 lm	3000 K	85 lm/W	-
911401721002	RS378B P11 940 PSU-E NB M55	570 lm	4000 K	95 lm/W	-
911401721012	RS378B P11 927 PSU-E MB M55	957 lm	2700 K	87 lm/W	-
911401721022	RS378B P11 930 PSU-E MB M55	510 lm	3000 K	85 lm/W	-
911401721032	RS378B P11 940 PSU-E MB M55	540 lm	4000 K	90 lm/W	-
911401721042	RS378B P11 927 PSU-E WB M55	957 lm	2700 K	87 lm/W	-
911401721052	RS378B P11 930 PSU-E WB M55	540 lm	3000 K	90 lm/W	-
911401721062	RS378B P11 940 PSU-E WB M55	570 lm	4000 K	95 lm/W	-
911401721112	RS378B P6 930 PSR-E MB M55	450 lm	3000 K	75 lm/W	-
911401721622	RS378B P42 930 PSU-E NB M102	2,350 lm	3000 K	71 lm/W	-
911401721632	RS378B P42 940 PSU-E NB M102	2,400 lm	4000 K	73 lm/W	-
911401721642	RS378B P42 927 PSU-E MB M102	2,540 lm	2700 K	106 lm/W	-
911401721652	RS378B P42 930 PSU-E MB M102	2,350 lm	3000 K	71 lm/W	- degree(s)
911401721662	RS378B P42 940 PSU-E MB M102	2,400 lm	4000 K	73 lm/W	- degree(s)
911401721682	RS378B P42 930 PSU-E WB M102	2,350 lm	3000 K	71 lm/W	- degree(s)
911401721692	RS378B P42 940 PSU-E WB M102	2,400 lm	4000 K	73 lm/W	- degree(s)
911401538071	RS378B P24 930 PSD-E MB M70	2,350 lm	3000 K	98 lm/W	-
911401721482	RS378B P24 940 PSU-E MB M70	1,350 lm	4000 K	90 lm/W	-
911401538571	RS378B P33 927 PSD-E NB M87	2,540 lm	2700 K	106 lm/W	-
911401538671	RS378B P33 927 PSD-E MB M87	2,540 lm	2700 K	106 lm/W	23 degree(s)
911401538871	RS378B P33 930 PSD-E NB M87	2,350 lm	3000 K	71 lm/W	-
911401539171	RS378B P33 940 PSD-E NB M87	2,400 lm	4000 K	73 lm/W	-
911401721522	RS378B P33 927 PSU-E NB M87	1,500 lm	2700 K	100 lm/W	-
911401721532	RS378B P33 930 PSU-E NB M87	2,350 lm	3000 K	98 lm/W	-
911401721542	RS378B P33 940 PSU-E NB M87	2,400 lm	4000 K	100 lm/W	-
911401721562	RS378B P33 930 PSU-E MB M87	2,350 lm	3000 K	98 lm/W	23 degree(s)
911401721572	RS378B P33 940 PSU-E MB M87	2,400 lm	4000 K	100 lm/W	23 degree(s)
911401721592	RS378B P33 930 PSU-E WB M87	2,350 lm	3000 K	98 lm/W	35 degree(s)
911401721602	RS378B P33 940 PSU-E WB M87	2,400 lm	4000 K	100 lm/W	35 degree(s)
911401539571	RS378B P42 927 PSD-E MB M102	2,540 lm	2700 K	77 lm/W	-
911401539871	RS378B P42 930 PSD-E MB M102	3,864 lm	3000 K	92 lm/W	-
911401539971	RS378B P42 930 PSD-E WB M102	3,864 lm	3000 K	92 lm/W	-
911401540271	RS378B P42 940 PSD-E WB M102	4,074 lm	4000 K	97 lm/W	-
911401545571	RS378B P11 930 PSU-E WW S	540 lm	3000 K	90 lm/W	-
911401536771	RS378B P15 927 PSD-E NB M55	957 lm	2700 K	87 lm/W	-
911401537471	RS378B P15 940 PSD-E MB M55	1,410 lm	4000 K	94 lm/W	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	1,350 lm	3000 K	90 lm/W	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	1,350 lm	3000 K	90 lm/W	-
911401532371	RS378B P6 927 PSU-E MB M43	2,540 lm	2700 K	77 lm/W	-
911401532471	RS378B P6 927 PSU-E WB M43	3,864 lm	2700 K	92 lm/W	-
911401532571	RS378B P6 930 PSU-E NB M43	4,074 lm	3000 K	97 lm/W	-
911401532671	RS378B P6 930 PSU-E MB M43	4,074 lm	3000 K	97 lm/W	-

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
911401532771	RS378B P6 930 PSU-E WB M43	1,500 lm	3000 K	100 lm/W	-
911401532971	RS378B P6 940 PSU-E MB M43	800 lm	4000 K	73 lm/W	-
911401533071	RS378B P6 940 PSU-E WB M43	1,300 lm	4000 K	87 lm/W	-
911401721292	RS378B P15 930 PSU-E MB M55	545 lm	3000 K	91 lm/W	-
911401721302	RS378B P15 940 PSU-E MB M55	630 lm	4000 K	105 lm/W	-
911401721322	RS378B P15 930 PSU-E WB M55	580 lm	3000 K	97 lm/W	-
911401721422	RS378B P15 940 PSR-E WB M55	1,410 lm	4000 K	94 lm/W	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401536371	RS378B P11 930 PSD-E WB M55	11 W
911401536571	RS378B P11 940 PSD-E MB M55	11 W
911401720892	RS378B P6 927 PSU-E NB M55	6 W
911401720902	RS378B P6 930 PSU-E NB M55	6 W
911401720932	RS378B P6 930 PSU-E MB M55	6 W
911401720962	RS378B P6 930 PSU-E WB M55	6 W
911401720972	RS378B P6 940 PSU-E WB M55	6 W
911401720992	RS378B P11 930 PSU-E NB M55	11 W
911401721002	RS378B P11 940 PSU-E NB M55	11 W
911401721012	RS378B P11 927 PSU-E MB M55	11 W
911401721022	RS378B P11 930 PSU-E MB M55	11 W
911401721032	RS378B P11 940 PSU-E MB M55	11 W
911401721042	RS378B P11 927 PSU-E WB M55	11 W
911401721052	RS378B P11 930 PSU-E WB M55	11 W
911401721062	RS378B P11 940 PSU-E WB M55	11 W
911401721112	RS378B P6 930 PSR-E MB M55	6 W
911401721622	RS378B P42 930 PSU-E NB M102	42 W
911401721632	RS378B P42 940 PSU-E NB M102	42 W
911401721642	RS378B P42 927 PSU-E MB M102	42 W
911401721652	RS378B P42 930 PSU-E MB M102	42 W
911401721662	RS378B P42 940 PSU-E MB M102	42 W
911401721682	RS378B P42 930 PSU-E WB M102	42 W
911401721692	RS378B P42 940 PSU-E WB M102	42 W
911401538071	RS378B P24 930 PSD-E MB M70	24 W
911401721482	RS378B P24 940 PSU-E MB M70	24 W
911401538571	RS378B P33 927 PSD-E NB M87	33 W
911401538671	RS378B P33 927 PSD-E MB M87	33 W
911401538871	RS378B P33 930 PSD-E NB M87	33 W
911401539171	RS378B P33 940 PSD-E NB M87	33 W
911401721522	RS378B P33 927 PSU-E NB M87	33 W
911401721532	RS378B P33 930 PSU-E NB M87	33 W

Order Code	Full Product Name	Power Consumption
911401721542	RS378B P33 940 PSU-E NB M87	33 W
911401721562	RS378B P33 930 PSU-E MB M87	33 W
911401721572	RS378B P33 940 PSU-E MB M87	33 W
911401721592	RS378B P33 930 PSU-E WB M87	33 W
911401721602	RS378B P33 940 PSU-E WB M87	33 W
911401539571	RS378B P42 927 PSD-E MB M102	42 W
911401539871	RS378B P42 930 PSD-E MB M102	42 W
911401539971	RS378B P42 930 PSD-E WB M102	42 W
911401540271	RS378B P42 940 PSD-E WB M102	42 W
911401545571	RS378B P11 930 PSU-E WW S	11 W
911401536771	RS378B P15 927 PSD-E NB M55	15 W
911401537471	RS378B P15 940 PSD-E MB M55	15 W
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	15 W
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	15 W
911401532371	RS378B P6 927 PSU-E MB M43	6 W
911401532471	RS378B P6 927 PSU-E WB M43	6 W
911401532571	RS378B P6 930 PSU-E NB M43	6 W
911401532671	RS378B P6 930 PSU-E MB M43	6 W
911401532771	RS378B P6 930 PSU-E WB M43	6 W
911401532971	RS378B P6 940 PSU-E MB M43	6 W
911401533071	RS378B P6 940 PSU-E WB M43	6 W
911401721292	RS378B P15 930 PSU-E MB M55	15 W
911401721302	RS378B P15 940 PSU-E MB M55	15 W
911401721322	RS378B P15 930 PSU-E WB M55	15 W
911401721422	RS378B P15 940 PSR-E WB M55	15 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401536371	RS378B P11 930 PSD-E WB M55	DALI	-
911401536571	RS378B P11 940 PSD-E MB M55	DALI	-
911401720892	RS378B P6 927 PSU-E NB M55	No	Not applicable
911401720902	RS378B P6 930 PSU-E NB M55	No	Not applicable
911401720932	RS378B P6 930 PSU-E MB M55	No	Not applicable
911401720962	RS378B P6 930 PSU-E WB M55	No	Not applicable
911401720972	RS378B P6 940 PSU-E WB M55	No	Not applicable
911401720992	RS378B P11 930 PSU-E NB M55	No	Not applicable
911401721002	RS378B P11 940 PSU-E NB M55	No	Not applicable
911401721012	RS378B P11 927 PSU-E MB M55	No	Not applicable
911401721022	RS378B P11 930 PSU-E MB M55	No	Not applicable
911401721032	RS378B P11 940 PSU-E MB M55	No	Not applicable
911401721042	RS378B P11 927 PSU-E WB M55	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401721052	RS378B P11 930 PSU-E WB M55	No	Not applicable
911401721062	RS378B P11 940 PSU-E WB M55	No	Not applicable
911401721112	RS378B P6 930 PSR-E MB M55	TRIAC	10%
911401721622	RS378B P42 930 PSU-E NB M102	No	Not applicable
911401721632	RS378B P42 940 PSU-E NB M102	No	Not applicable
911401721642	RS378B P42 927 PSU-E MB M102	No	Not applicable
911401721652	RS378B P42 930 PSU-E MB M102	No	Not applicable
911401721662	RS378B P42 940 PSU-E MB M102	No	Not applicable
911401721682	RS378B P42 930 PSU-E WB M102	No	Not applicable
911401721692	RS378B P42 940 PSU-E WB M102	No	Not applicable
911401538071	RS378B P24 930 PSD-E MB M70	DALI	-
911401721482	RS378B P24 940 PSU-E MB M70	No	Not applicable
911401538571	RS378B P33 927 PSD-E NB M87	DALI	-
911401538671	RS378B P33 927 PSD-E MB M87	DALI	-
911401538871	RS378B P33 930 PSD-E NB M87	DALI	-
911401539171	RS378B P33 940 PSD-E NB M87	DALI	-
911401721522	RS378B P33 927 PSU-E NB M87	No	Not applicable
911401721532	RS378B P33 930 PSU-E NB M87	No	Not applicable
911401721542	RS378B P33 940 PSU-E NB M87	No	Not applicable
911401721562	RS378B P33 930 PSU-E MB M87	No	Not applicable
911401721572	RS378B P33 940 PSU-E MB M87	No	Not applicable
911401721592	RS378B P33 930 PSU-E WB M87	No	Not applicable
911401721602	RS378B P33 940 PSU-E WB M87	No	Not applicable
911401539571	RS378B P42 927 PSD-E MB M102	DALI	-
911401539871	RS378B P42 930 PSD-E MB M102	DALI	-
911401539971	RS378B P42 930 PSD-E WB M102	DALI	-
911401540271	RS378B P42 940 PSD-E WB M102	DALI	-
911401545571	RS378B P11 930 PSU-E WW S	No	-
911401536771	RS378B P15 927 PSD-E NB M55	DALI	-
911401537471	RS378B P15 940 PSD-E MB M55	DALI	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	1-10V	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	1-10V	-
911401532371	RS378B P6 927 PSU-E MB M43	No	-
911401532471	RS378B P6 927 PSU-E WB M43	No	-
911401532571	RS378B P6 930 PSU-E NB M43	No	-
911401532671	RS378B P6 930 PSU-E MB M43	No	-
911401532771	RS378B P6 930 PSU-E WB M43	No	-
911401532971	RS378B P6 940 PSU-E MB M43	No	-
911401533071	RS378B P6 940 PSU-E WB M43	No	-
911401721292	RS378B P15 930 PSU-E MB M55	No	Not applicable
911401721302	RS378B P15 940 PSU-E MB M55	No	Not applicable
911401721322	RS378B P15 930 PSU-E WB M55	No	Not applicable
911401721422	RS378B P15 940 PSR-E WB M55	TRIAC	10%

