



Powerful discreet spots with an accent on sustainability

LuxSpace Accent Performance Elbow

With LuxSpace Accent Performance Elbow, retailers and building operators can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a refined and neutral product design. Powerful and discreet, LuxSpace Accent combines a high luminous flux in a compact form factor. Design-in and installation are easy due to its small built-in dimensions. Maintenance and upgrades of the optics is fast and requires no tools. Furthermore, LuxSpace Accent Performance Elbow spots are certified as circular lighting and offer multiple system integration and dimming options, including wired as well as wireless. LuxSpace Accent Performance Elbow allows spot head rotation and can be angled out of the ceiling for maximum aiming flexibility. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

Benefits

- More sparkle and enhanced shopper eye comfort with PerfectAccent optics
- Best-in-class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors
- Easy maintenance and upgrades with tool-less access to driver and optics
- The clean and refined product design helps the spots blend in with ceilings

LuxSpace Accent Performance Elbow

Features

- RS782B offers high maximum flux (6000lm) in a very compact housing with limited built-in dimensions
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Can be fully rotated and angled out of the ceiling for great light control
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options available

Application

- Convenience stores
- Supermarkets & hypermarkets
- Offices and hospitality areas

Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions





RS782B LuxSpace Accent
Performance Elbow Black



RS782B LuxSpace Accent
Performance Elbow Silver

Dimensional drawing



LuxSpace Accent Performance Elbow

Product details



RS782B LuxSpace Accent Performance Elbow Back View



Step5 (optional): Add or remove the front glass



Step4: Replace the reflector



Step1: Press the button to unlock the front face



Step2: Remove the optical assembly from the luminaire



Step3: Pull the clip of the frontface to release the reflector



LuxSpace Accent Elbow luminaires offer great aiming flexibility



PerfectAccent reflector and front glass maintenance and upgrading is easy with an integrated button

LuxSpace Accent Performance Elbow

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Product Data	
Product family code	RS782B

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97958400	RS782B 39S/930 PSU-E WB BK	3000 K	>90	127 lm/W	3,900 lm
97883900	RS782B 39S/827 PSU-E NB WH	2700 K	>80	133 lm/W	3,800 lm
97954600	RS782B 39S/830 PSU-E MB WH	3000 K	>80	142 lm/W	4,100 lm
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	3000 K	>80	142 lm/W	4,200 lm
97956000	RS782B 39S/830 WIA-E MB WH	3000 K	>80	135 lm/W	4,100 lm
97957700	RS782B 39S/840 PSU-E WB WH	4000 K	>80	147 lm/W	4,200 lm
97959100	RS782B 39S/PW930 PSU-E HWB WH	3000 K	>90	136 lm/W	4,000 lm
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	2200 K	>80	93 lm/W	2,900 lm
97962100	RS782B 27S/FMT PSU-E HWB FG WH	3000 K	>90	81 lm/W	2,800 lm
97963800	RS782B 39S/CH PSU-E HWB FG WH	2700 K	>80	139 lm/W	4,000 lm
97966900	RS782B 49S/830 PSU-E WB WH	3000 K	>80	133 lm/W	5,000 lm
97967600	RS782B 49S/840 PSU-E WB WH	4000 K	>80	139 lm/W	5,200 lm
97968300	RS782B 49S/930 PSU-E OVL-H WH	3000 K	>90	132 lm/W	5,000 lm
97969000	RS782B 49S/PW930 PSU-E WB WH	3000 K	>90	132 lm/W	5,000 lm
97965200	RS782B 49S/827 PSU-E VWB SI	2700 K	>80	139 lm/W	5,200 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
97958400	RS782B 39S/930 PSU-E WB BK	Wide beam
97883900	RS782B 39S/827 PSU-E NB WH	Narrow beam
97954600	RS782B 39S/830 PSU-E MB WH	Medium beam
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
97956000	RS782B 39S/830 WIA-E MB WH	Medium beam
97957700	RS782B 39S/840 PSU-E WB WH	Wide beam
97959100	RS782B 39S/PW930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees
97962100	RS782B 27S/FMT PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees
97963800	RS782B 39S/CH PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees
97966900	RS782B 49S/830 PSU-E WB WH	Wide beam
97967600	RS782B 49S/840 PSU-E WB WH	Wide beam
97968300	RS782B 49S/930 PSU-E OVL-H WH	Oval horizontal beam
97969000	RS782B 49S/PW930 PSU-E WB WH	Wide beam
97965200	RS782B 49S/827 PSU-E VWB SI	Very wide beam

LuxSpace Accent Performance Elbow

Operating and Electrical

Order Code	Full Product Name	Power Consumption
97958400	RS782B 39S/930 PSU-E WB BK	31 W
97883900	RS782B 39S/827 PSU-E NB WH	29 W
97954600	RS782B 39S/830 PSU-E MB WH	29 W
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	29.5 W
97956000	RS782B 39S/830 WIA-E MB WH	30 W
97957700	RS782B 39S/840 PSU-E WB WH	29 W
97959100	RS782B 39S/PW930 PSU-E HWB WH	29 W
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	31 W

Order Code	Full Product Name	Power Consumption
97962100	RS782B 27S/FMT PSU-E HWB FG WH	35 W
97963800	RS782B 39S/CH PSU-E HWB FG WH	29 W
97966900	RS782B 49S/830 PSU-E WB WH	37.5 W
97967600	RS782B 49S/840 PSU-E WB WH	37.5 W
97968300	RS782B 49S/930 PSU-E OVL-H WH	38 W
97969000	RS782B 49S/PW930 PSU-E WB WH	38 W
97965200	RS782B 49S/827 PSU-E VWB SI	37.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
97958400	RS782B 39S/930 PSU-E WB BK	No	Not applicable
97883900	RS782B 39S/827 PSU-E NB WH	No	Not applicable
97954600	RS782B 39S/830 PSU-E MB WH	No	Not applicable
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	Yes	1%
97956000	RS782B 39S/830 WIA-E MB WH	Yes	Not applicable
97957700	RS782B 39S/840 PSU-E WB WH	No	Not applicable
97959100	RS782B 39S/PW930 PSU-E HWB WH	No	Not applicable
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
97962100	RS782B 27S/FMT PSU-E HWB FG WH	No	Not applicable
97963800	RS782B 39S/CH PSU-E HWB FG WH	No	Not applicable
97966900	RS782B 49S/830 PSU-E WB WH	No	Not applicable
97967600	RS782B 49S/840 PSU-E WB WH	No	Not applicable
97968300	RS782B 49S/930 PSU-E OVL-H WH	No	Not applicable
97969000	RS782B 49S/PW930 PSU-E WB WH	No	Not applicable
97965200	RS782B 49S/827 PSU-E VWB SI	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
97958400	RS782B 39S/930 PSU-E WB BK	Black
97883900	RS782B 39S/827 PSU-E NB WH	White
97954600	RS782B 39S/830 PSU-E MB WH	White
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	White
97956000	RS782B 39S/830 WIA-E MB WH	White
97957700	RS782B 39S/840 PSU-E WB WH	White
97959100	RS782B 39S/PW930 PSU-E HWB WH	White
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	White

Order Code	Full Product Name	Housing Color
97962100	RS782B 27S/FMT PSU-E HWB FG WH	White
97963800	RS782B 39S/CH PSU-E HWB FG WH	White
97966900	RS782B 49S/830 PSU-E WB WH	White
97967600	RS782B 49S/840 PSU-E WB WH	White
97968300	RS782B 49S/930 PSU-E OVL-H WH	White
97969000	RS782B 49S/PW930 PSU-E WB WH	White
97965200	RS782B 49S/827 PSU-E VWB SI	Silver


Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
97958400	RS782B 39S/930 PSU-E WB BK	(0.434,0.403)<2
97883900	RS782B 39S/827 PSU-E NB WH	(0.458,0.410)<3
97954600	RS782B 39S/830 PSU-E MB WH	(0.434,0.403)<3
97955300	RS782B 39S/830 DIA-VLC-E HMB WH	(0.434,0.403)<3
97956000	RS782B 39S/830 WIA-E MB WH	(0.434,0.403)<3
97957700	RS782B 39S/840 PSU-E WB WH	(0.382,0.380)<3
97959100	RS782B 39S/PW930 PSU-E HWB WH	(0.422,0.386)<2
97961400	RS782B 27S/ROSE PSU-E HWB FG WH	(0.478,0.382)<2


Order Code	Full Product Name	Initial chromaticity
97962100	RS782B 27S/FMT PSU-E HWB FG WH	(0.457,0.385)<3
97963800	RS782B 39S/CH PSU-E HWB FG WH	(0.458,0.410)<3
97966900	RS782B 49S/830 PSU-E WB WH	(0.434,0.403)<3
97967600	RS782B 49S/840 PSU-E WB WH	(0.382,0.380)<3
97968300	RS782B 49S/930 PSU-E OVL-H WH	(0.434,0.403)<2
97969000	RS782B 49S/PW930 PSU-E WB WH	(0.422,0.386)<2
97965200	RS782B 49S/827 PSU-E VWB SI	(0.458,0.410)<3

LuxSpace Accent Performance Elbow


Polar Wide Diagrams




Polar Normal (separate) - RS780BI - 910505101649




Polar Normal (separate) - RS780BI - 910505101648




Polar Normal (separate) - RS780BI - 910505101642




Polar Normal (separate) - RS780BI - 910505101640




Polar Normal (separate) - RS780BI - 910505101652




Polar Normal (separate) - RS780BI - 910505101645



Polar Normal (separate) - RS780BI - 910505101643




Polar Normal (separate) - RS780BI - 910505101653




Polar Normal (separate) - RS780BI - 910505101647

LuxSpace Accent Performance Elbow


Polar Wide Diagrams




Polar Normal (separate) - RS780BI - 910505101654




Polar Normal (separate) - RS780BI - 910505101651




Polar Normal (separate) - RS780BI - 910505101641



Polar Normal (separate) - RS780BI - 910505101659



Polar Normal (separate) - RS780BI - 910505101644



Polar Normal (separate) - RS780BI - 910505101655

