



A small and sustainable surface mounted cylinder in a sleek, subtle design

GreenSpace Evo Mini Cylinder

GreenSpace Evo Mini Cylinder is a sustainable lighting fixture that comes with a sleek and subtle design. This makes the Cylinder an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini Cylinder a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customization of colors and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Cylinder

Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth

Versions

SA332C GreenSpace Evo Mini
Cylinder PSU - Black



SA332C GreenSpace Evo Mini
Cylinder DIA-WIA - Grey




SA332C GreenSpace Evo Mini
Cylinder PSU - White



GreenSpace Evo Mini Cylinder

Dimensional drawing



General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.422, 0.386) SDCM <2
Luminous flux tolerance	+/-10%
Product Data	
Product family code	SA332C

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505104953	SA332C 10S/PC930 PSU HMB BK482	125 lm/W	1,021 lm	Medium beam
910505104954	SA332C 12S/PW930 PSU HWB BK482	126 lm/W	1,355 lm	Wide beam
910505104956	SA332C 10S/PC930 DIA HMB WH481	121 lm/W	1,021 lm	Medium beam
910505104957	SA332C 12S/PW930 DIA HWB WH481	122 lm/W	1,355 lm	Wide beam
910505104959	SA332C 10S/PC930 WIA HMB WH481	119 lm/W	1,021 lm	Medium beam
910505104958	SA332C 8S/PW930 WIA HNB BK482	111 lm/W	790 lm	Narrow beam
910505104960	SA332C 12S/PW930 WIA HWB BK482	122 lm/W	1,355 lm	Wide beam
910505104955	SA332C 8S/PW930 DIA HNB GR482	114 lm/W	790 lm	Narrow beam
910505104952	SA332C 8S/PW930 PSU HNB WH481	122 lm/W	790 lm	Narrow beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505104953	SA332C 10S/PC930 PSU HMB BK482	8.1 W	910505104954	SA332C 12S/PW930 PSU HWB BK482	10 W

GreenSpace Evo Mini Cylinder

Order Code	Full Product Name	Power Consumption
910505104956	SA332C 10S/PC930 DIA HMB WH481	8.5 W
910505104957	SA332C 12S/PW930 DIA HWB WH481	10.3 W
910505104959	SA332C 10S/PC930 WIA HMB WH481	8.6 W
910505104958	SA332C 8S/PW930 WIA HNB BK482	7.1 W

Order Code	Full Product Name	Power Consumption
910505104960	SA332C 12S/PW930 WIA HWB BK482	10.3 W
910505104955	SA332C 8S/PW930 DIA HNB GR482	6.9 W
910505104952	SA332C 8S/PW930 PSU HNB WH481	6.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104953	SA332C 10S/PC930 PSU HMB BK482	No
910505104954	SA332C 12S/PW930 PSU HWB BK482	No
910505104956	SA332C 10S/PC930 DIA HMB WH481	Yes
910505104957	SA332C 12S/PW930 DIA HWB WH481	Yes
910505104959	SA332C 10S/PC930 WIA HMB WH481	Yes


Order Code	Full Product Name	Dimmable
910505104958	SA332C 8S/PW930 WIA HNB BK482	Yes
910505104960	SA332C 12S/PW930 WIA HWB BK482	Yes
910505104955	SA332C 8S/PW930 DIA HNB GR482	Yes
910505104952	SA332C 8S/PW930 PSU HNB WH481	No

Mechanical and Housing


Order Code	Full Product Name	Housing Color
910505104953	SA332C 10S/PC930 PSU HMB BK482	Black
910505104954	SA332C 12S/PW930 PSU HWB BK482	Black
910505104956	SA332C 10S/PC930 DIA HMB WH481	White
910505104957	SA332C 12S/PW930 DIA HWB WH481	White
910505104959	SA332C 10S/PC930 WIA HMB WH481	White

Order Code	Full Product Name	Housing Color
910505104958	SA332C 8S/PW930 WIA HNB BK482	Black
910505104960	SA332C 12S/PW930 WIA HWB BK482	Black
910505104955	SA332C 8S/PW930 DIA HNB GR482	Gray
910505104952	SA332C 8S/PW930 PSU HNB WH481	White


Polar Wide Diagrams




Polar Normal (separate) - SA332CI - 910505104956




Polar Normal (separate) - SA332CI - 910505104952




Polar Normal (separate) - SA332CI - 910505104959



Polar Normal (separate) - SA332CI - 910505104958




Polar Normal (separate) - SA332CI - 910505104954




Polar Normal (separate) - SA332CI - 910505104955

GreenSpace Evo Mini Cylinder


Polar Wide Diagrams



Polar Normal (separate) - SA332CI -
910505104957



Polar Normal (separate) - SA332CI -
910505104953



Polar Normal (separate) - SA332CI -
910505104960

