



# Trusted performance. Every day.

## Ledinaire surface-mounted SM065C

The Philips Ledinaire surface-mounted (SM065C) range features a selection of popular off-the-shelf LED luminaires that offer Philips high quality at a competitive price. Reliable, energy-efficient and affordable, this latest generation of 600 x 600 mm Ledinaire LED surface-mounted lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications—just what you need.

### Benefits

- No risks, trusted performance
- Good quality, easy to use
- No confusion, easy product selection

### Features


- Surface-mounted versions
- Modern, unobtrusive design
- Energy efficient up to 120 lm/W
- Long lifetime of 75,000 hours @L70 and 50,000 hours @L80
- Office compliant (OC) and non-office compliant (NOC) versions available

### Application

- Offices
- Education
- Healthcare

## Ledinaire surface-mounted SM065C

### Dimensional drawing




### Product details

Ledinaire surface mounted  
SM065C back side DPP



Ledinaire-surface-mounted-  
SM065C-W60-L60-DPP



# Ledinaire surface-mounted SM065C

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Luminous Flux	4,100 lm
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	34 W
Suitable for random switching	Not applicable
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20/40
Emergency Operation	
Central Emergency	No
Approval and Application	
Ambient temperature range	-10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM ≤5
Luminous flux tolerance	-10% / +10%

## Light Technical

Order Code	Full Product Name	Beam angle of light source	Color rendering index (CRI)	Optic type
73684999	SM065C 41S/840 PSU W60L60 OC	90 degree(s)	80	Beam angle 90°
73685699	SM065C 41S/840 PSU W60L60 NOC	120 degree(s)	>80	Beam angle 120°
73690099	SM065C 41S/840 PSU W60L60 OC	90 degree(s) 4PK	>80	Beam angle 90°
73691799	SM065C 41S/840 PSU W60L60 NOC	120 degree(s) 4PK	>80	Beam angle 120°

## Ledinaire surface-mounted SM065C



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2025, December 13 - data subject to change