



CoreLine surface-mounted gen4: easy installation, excellent illumination

CoreLine surface mounted gen 4

Introducing Philips CoreLine surface-mounted gen4, a family of high-quality and innovative light fixtures designed to deliver energy-efficient and long-lasting illumination for your home or office. With higher lumen packages up to 6800 lm, improved efficiency of up to 160 lm/W, and a longer lifetime of L90@50K hrs/ L80@100K hrs, our CoreLine family provides bright and long-lasting illumination. Our surface-mounted light fixtures feature DC plugs in all versions, packaging from a single box to 4-in-1, and plastics-free packaging, making them eco-friendly and cost-effective. Our CoreLine surface-mounted gen4 features the same green quick connectors as the CoreLine panel, and is compatible with Wieland GSTi3 and GST/5 connectors. Upgrade your lighting today with Philips CoreLine surface-mounted gen4, a high-quality and innovative solution that delivers on the Philips promise of energy-efficient and long-lasting illumination.

CoreLine surface mounted gen 4

Benefits

- Energy-efficient: Our state-of-the-art LED technology ensures that CoreLine surface-mounted gen4 is both eco-friendly and cost-effective, saving you money on your energy bills while helping to reduce your carbon footprint.
- Bright and effective: With higher lumen packages up to 6800 lm, CoreLine surface-mounted gen4 provides bright and effective illumination for your home or office.
- Easy installation: Quick connectors make installation a breeze, ensuring a hassle-free and user-friendly experience.
- Modern design: With its sleek and modern design, CoreLine surface-mounted gen4 blends seamlessly with any interior décor, enhancing the atmosphere of any space.
- Long-lasting: Improved efficiency and lifetime ensure long-lasting and eco-friendly lighting that will last for years to come.



Features

- Higher lumen packages: up to 6800 lm (replacing 2 x 58W conventional light sources) for bright and effective illumination
- Improved efficiency: up to 160 lm/W for energy-saving and eco-friendly lighting
- Improved lifetime: L90@50K hrs/ L80@100K hrs for long-lasting and durable lighting
- Plastics-free packaging for an eco-friendly solution
- EPDs available for all listed products
- Improved all-in driver: more user-friendly, with no dipswitches for ease of use

Application

- Offices
- Healthcare
- Education

Dimensional drawing



CoreLine surface mounted gen 4

Product details



CoreLine surface mounted G4 NOC
Optical window



CoreLine surface mounted G4
W20L120 DPP



CoreLine surface mounted G4 PSU
back side



CoreLine surface mounted G4
SafetyCable



CoreLine surface mounted G4 WIA
back side-02



CoreLine surface mounted G4 OC
Optical window



CoreLine surface mounted G4 PSU
back side




CoreLine G4 PSU All in lumen
selectable side

CoreLine surface mounted gen 4

Product details




CoreLine surface mounted G4
W20L157 DPP



CoreLine surface mounted G4 PSD
back side detail dipswitches




CoreLine G4 PSD All in lumen
selectable back




CoreLine surface mounted G4 WIA
back side-01



CoreLine surface mounted G4 WIA
back side



CoreLine G4 PSU All in lumen
selectable back



CoreLine G4 PSD All in lumen
selectable side

CoreLine surface mounted gen 4

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20/44
Approval and Application	
Ambient temperature range	-10 to +40 °C
CE mark	Yes
ENEC mark	KEMA Netherlands
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Correlated Color	Luminous	Luminous Flux
			Temperature (Nom)	Efficacy (rated) (Nom)	
911401842087	SM136V G4 40S/830 WIA W20L120 OC	-	3000 K	145 lm/W	4,000 lm
911401842187	SM136V G4 43S/840 WIA W20L120 OC	-	4000 K	156 lm/W	4,300 lm
911401842687	SM136V G4 40S/830 WIA W20L157 OC	-	3000 K	145 lm/W	4,000 lm
911401842787	SM136V G4 43S/840 WIA W20L157 OC	-	4000 K	156 lm/W	4,300 lm
911401841687	SM136V G4 36_45_60S/840 PSU W20L120 NOC	All-in, Multi Lumen	4000 K	157 lm/W	3,600 lm
911401841787	SM136V G4 36_45_60S/840 PSU W20L120 OC	All-in, Multi Lumen	4000 K	157 lm/W	3,600 lm
911401841887	SM136V G4 34_43_57S/830 PSD W20L120 OC	All-in, Multi Lumen	3000 K	148 lm/W	3,400 lm
911401841987	SM136V G4 36_45_60S/840 PSD W20L120 OC	All-in, Multi Lumen	4000 K	157 lm/W	3,600 lm
911401842287	SM136V G4 36_45_68S/840 PSU W20L157 OC	All-in, Multi Lumen	4000 K	160 lm/W	3,600 lm
911401842387	SM136V G4 34_43_65S/830 PSU W20L157 OC	All-in, Multi Lumen	3000 K	151 lm/W	3,400 lm
911401842487	SM136V G4 36_45_68S/840 PSD W20L157 OC	All-in, Multi Lumen	4000 K	160 lm/W	3,600 lm
911401842587	SM136V G4 34_43_65S/830 PSD W20L157 OC	All-in, Multi Lumen	3000 K	151 lm/W	3,400 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
911401842087	SM136V G4 40S/830 WIA W20L120 OC	Wide beam office compliant	911401841887	SM136V G4 34_43_57S/830 PSD W20L120 OC	Wide beam office compliant
911401842187	SM136V G4 43S/840 WIA W20L120 OC	Wide beam office compliant	911401841987	SM136V G4 36_45_60S/840 PSD W20L120 OC	Wide beam office compliant
911401842687	SM136V G4 40S/830 WIA W20L157 OC	Wide beam office compliant	911401842287	SM136V G4 36_45_68S/840 PSU W20L157 OC	Wide beam office compliant
911401842787	SM136V G4 43S/840 WIA W20L157 OC	Wide beam office compliant	911401842387	SM136V G4 34_43_65S/830 PSU W20L157 OC	Wide beam office compliant
911401841687	SM136V G4 36_45_60S/840 PSU W20L120 NOC	Very wide beam	911401842487	SM136V G4 36_45_68S/840 PSD W20L157 OC	Wide beam office compliant
911401841787	SM136V G4 36_45_60S/840 PSU W20L120 OC	Wide beam office compliant	911401842587	SM136V G4 34_43_65S/830 PSD W20L157 OC	Wide beam office compliant

CoreLine surface mounted gen 4

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401842087	SM136V G4 40S/830 WIA W20L120 OC	27.5 W
911401842187	SM136V G4 43S/840 WIA W20L120 OC	27.5 W
911401842687	SM136V G4 40S/830 WIA W20L157 OC	27.5 W
911401842787	SM136V G4 43S/840 WIA W20L157 OC	27.5 W
911401841687	SM136V G4 36_45_60S/840 PSU W20L120 NOC	38.5 W
911401841787	SM136V G4 36_45_60S/840 PSU W20L120 OC	38.5 W

Order Code	Full Product Name	Power Consumption
911401841887	SM136V G4 34_43_57S/830 PSD W20L120 OC	38.5 W
911401841987	SM136V G4 36_45_60S/840 PSD W20L120 OC	38.5 W
911401842287	SM136V G4 36_45_68S/840 PSU W20L157 OC	43.5 W
911401842387	SM136V G4 34_43_65S/830 PSU W20L157 OC	43.5 W
911401842487	SM136V G4 36_45_68S/840 PSD W20L157 OC	43.5 W
911401842587	SM136V G4 34_43_65S/830 PSD W20L157 OC	43.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401842087	SM136V G4 40S/830 WIA W20L120 OC	Yes
911401842187	SM136V G4 43S/840 WIA W20L120 OC	Yes
911401842687	SM136V G4 40S/830 WIA W20L157 OC	Yes
911401842787	SM136V G4 43S/840 WIA W20L157 OC	Yes
911401841687	SM136V G4 36_45_60S/840 PSU W20L120 NOC	No
911401841787	SM136V G4 36_45_60S/840 PSU W20L120 OC	No


Order Code	Full Product Name	Dimmable
911401841887	SM136V G4 34_43_57S/830 PSD W20L120 OC	Yes
911401841987	SM136V G4 36_45_60S/840 PSD W20L120 OC	Yes
911401842287	SM136V G4 36_45_68S/840 PSU W20L157 OC	No
911401842387	SM136V G4 34_43_65S/830 PSU W20L157 OC	No
911401842487	SM136V G4 36_45_68S/840 PSD W20L157 OC	Yes
911401842587	SM136V G4 34_43_65S/830 PSD W20L157 OC	Yes

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
911401842087	SM136V G4 40S/830 WIA W20L120 OC	(0.44,0.40)SDCM<3
911401842187	SM136V G4 43S/840 WIA W20L120 OC	(0.38,0.38)SDCM<3
911401842687	SM136V G4 40S/830 WIA W20L157 OC	(0.44,0.40)SDCM<3
911401842787	SM136V G4 43S/840 WIA W20L157 OC	(0.38,0.38)SDCM<3
911401841687	SM136V G4 36_45_60S/840 PSU W20L120 NOC	(0.38,0.38)SDCM<3
911401841787	SM136V G4 36_45_60S/840 PSU W20L120 OC	(0.38,0.38)SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401841887	SM136V G4 34_43_57S/830 PSD W20L120 OC	(0.44,0.40)SDCM<3
911401841987	SM136V G4 36_45_60S/840 PSD W20L120 OC	(0.38,0.38)SDCM<3
911401842287	SM136V G4 36_45_68S/840 PSU W20L157 OC	(0.38,0.38)SDCM<3
911401842387	SM136V G4 34_43_65S/830 PSU W20L157 OC	(0.44,0.40)SDCM<3
911401842487	SM136V G4 36_45_68S/840 PSD W20L157 OC	(0.38,0.38)SDCM<3
911401842587	SM136V G4 34_43_65S/830 PSD W20L157 OC	(0.44,0.40)SDCM<3


Polar Wide Diagrams



Polar Normal (separate) - null - 911401842687




Polar Normal (separate) - null - 911401842487




Polar Normal (separate) - null - 911401842787

CoreLine surface mounted gen 4


Polar Wide Diagrams




Polar Normal (separate) - null - 911401841987




Polar Normal (separate) - null - 911401841787




Polar Normal (separate) - null - 911401841887




Polar Normal (separate) - null - 911401842087




Polar Normal (separate) - null - 911401842187




Polar Normal (separate) - null - 911401842387



Polar Normal (separate) - null - 911401841687



Polar Normal (separate) - null - 911401842287



Polar Normal (separate) - null - 911401842587

