



Setting the standard in Surface-mounted LED Downlight

GreenSpace Surface-mounted

Philips GreenSpace Surface-mounted LED Downlight delivers a superior LED alternative that's up to 66% more energy efficient than the conventional downlight retrofits. Blending seamlessly into its environment, GreenSpace Surface-mounted LED Downlight mimics the form of conventional recessed downlights minus the associated high energy and maintenance costs. Philips GreenSpace Surface-mounted LED Downlight is also ideal for all commercial lighting applications as well as public indoor space where there is limited space in the ceiling.

Benefits

- Lumen output: Different lumens in different sizes and mounting heights with options of 1000lm, 2000lm, 3800lm & 6600lm.
- Superior light performance: Colors rendered accurately(CRI>80) and high system efficacy(100lm/w)
- Varieties: IP20, IP65 version with choice of different lumen output, and option of black housing through tailor-made
- Long lifetime: 50,000 hour lifetime ensures more savings in the long run

Features

- System efficacy: 100lm/W, energy saving up to 66% vs conventional downlights
- Reliable performance: Lifetime 50,000hours (L70B50@Ta25°C)
- Excellent light quality - CRI>=80 @3000K,4000K and 6500K
- Integral lightweight design – Installation cost is significantly reduced

GreenSpace Surface-mounted


Application

- Shopping mall
- Station concourse
- Canopy
- Airport public area
- Stadium public area

Specifications

Mounting type	surface mounted	Power consumption	10W, 20W, 38W, 66W
Operating Temperature range	-20°C to +40°C	Luminaire efficacy	100lm/W @840
Light Source	LED module	Correlated color temperature - CCT	3000K,4000K,6500K
Mains Voltage	220-240V AC / 50-60Hz	Color Rendering index - CRI	80
Dimming	PSU: non-dimmable	Beam angle	LED10 & LED20: 90° LED40 & LED70: 60°
Material	Housing: Die-cast Aluminum	Protection Class	Class I
Main color of the luminaire	White Black (ETO available)	IEC61140	
Lumen maintenance at median useful life	L70 50.000h	Ingress protection	IP20 & IP65 for LED40 & LED70 only
Luminous flux	LED10: 1000lm LED20: 2000lm LED40: 3800lm LED70: 6600lm	Overall diameter	LED10/LED20: 160mm LED70: 200mm LED40: 160mm (IP20) & 200MM (IP65)
		Installation	Surface Mount

Dimensional drawing



GreenSpace Surface-mounted

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	- degree(s)
Color rendering index (CRI)	>80
Optic type	High-gloss mirror
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Reflector
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 750 °C, duration 5 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1.00 %
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401847299	SM291C LED10/840 PSU WH	4000 K	100 lm/W	1,000 lm
	GM			
911401847499	SM293C LED20/830 PSU WH	3000 K	105 lm/W	2,000 lm
	GM			
911401847599	SM293C LED20/840 PSU WH	4000 K	105 lm/W	2,000 lm
	GM			
911401847699	SM293C LED20/865 PSU WH	6500 K	105 lm/W	2,000 lm
	GM			
911401847999	SM294C LED40/840 PSU WP	4000 K	105 lm/W	3,800 lm
	WH GM			
911401848299	SM294C LED40/865 PSU WP	6500 K	105 lm/W	3,800 lm
	WH GM			
911401848399	SM294C LED40/830 PSU WP	3000 K	105 lm/W	3,800 lm
	WH GM			

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401847299	SM291C LED10/840 PSU WH GM	10 W
911401847499	SM293C LED20/830 PSU WH GM	19 W
911401847599	SM293C LED20/840 PSU WH GM	19 W
911401847699	SM293C LED20/865 PSU WH GM	19 W

Order Code	Full Product Name	Power Consumption
911401847999	SM294C LED40/840 PSU WP WH GM	36 W
911401848299	SM294C LED40/865 PSU WP WH GM	36 W
911401848399	SM294C LED40/830 PSU WP WH GM	36 W

Mechanical and Housing

GreenSpace Surface-mounted

Order Code	Full Product Name	Ingress protection code
911401847299	SM291C LED10/840 PSU WH GM	IP20
911401847499	SM293C LED20/830 PSU WH GM	IP20
911401847599	SM293C LED20/840 PSU WH GM	IP20
911401847699	SM293C LED20/865 PSU WH GM	IP20

Order Code	Full Product Name	Ingress protection code
911401847999	SM294C LED40/840 PSU WP WH GM	IP65
911401848299	SM294C LED40/865 PSU WP WH GM	IP65
911401848399	SM294C LED40/830 PSU WP WH GM	IP65

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401847299	SM291C LED10/840 PSU WH GM	(0.38, 0.38) SDCM <5
911401847499	SM293C LED20/830 PSU WH GM	(0.44, 0.40) SDCM <5
911401847599	SM293C LED20/840 PSU WH GM	(0.38, 0.38) SDCM <5
911401847699	SM293C LED20/865 PSU WH GM	(0.31, 0.32) SDCM <5

Order Code	Full Product Name	Initial chromaticity
911401847999	SM294C LED40/840 PSU WP WH GM	(0.38, 0.38) SDCM <5
911401848299	SM294C LED40/865 PSU WP WH GM	(0.31, 0.32) SDCM <5
911401848399	SM294C LED40/830 PSU WP WH GM	(0.44, 0.40) SDCM <5

