



Elegant, Comprehensive and Affordable

GreenSpace Surface Mount

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Benefits

- Elegant look & feel.
- Complete family with multiple installations and form factors.
- Good glare control with color rendering performance.
- Ensured quality and reliability.

Features

- Both round and square version available.
- Both suspension and surface mount version available.
- UGR19 & CRI90, SDCM \leq 3
- Wide range of lumen packages, beam angles and color temperatures available.

Application

- Retail
- Hospitality
- Fashion

GreenSpace Surface Mount

Versions



GreenUp Suspended Mount P6 P9



GreenUp Suspended Mount P6S P9S









GreenUp Surface Mount



GreenUp Surface Mount

Dimensional drawing



GreenSpace Surface Mount

Light Technical

Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401599412	SP303P P6S 930 PSU WB	3000 K	91 lm/W	550 lm
911401504322	SP303P P9S 940 PSU VWB	4000 K	87 lm/W	780 lm
911401516022	SM303C P28 940 PSU NB	4000 K	97 lm/W	2,720 lm
911401518022	SM304C P10 930 PSU MB	3000 K	76 lm/W	770 lm
911401518522	SM304C P10 940 PSU WB	4000 K	83 lm/W	860 lm
911401520722	SM304C P12 950 PSU WB	5000 K	86 lm/W	1,050 lm
911401522022	SM304C P15 930 PSU MB	3000 K	75 lm/W	1,130 lm
911401522122	SM304C P15 930 PSU WB	3000 K	78 lm/W	1,170 lm
911401522522	SM304C P15 940 PSU WB	4000 K	82 lm/W	1,230 lm
911401584312	SM303C P6S 940 PSU VWB	4000 K	91 lm/W	550 lm
911401588212	SM303C P9S 940 PSU WB	4000 K	90 lm/W	810 lm
911401507422	SM303C P20 930 PSU WB	3000 K	90 lm/W	1,800 lm
911401507522	SM303C P20 930 PSU VWB	3000 K	89 lm/W	1,780 lm
911401508122	SM303C P20 940 PSU MB	4000 K	99 lm/W	1,980 lm
911401508322	SM303C P20 940 PSU VWB	4000 K	100 lm/W	2,000 lm
911401574912	SM303C P6 927 PSU MB	2700 K	84 lm/W	500 lm
911401575112	SM303C P6 927 PSU VWB	2700 K	84 lm/W	500 lm
911401576312	SM303C P6 940 PSU VWB	4000 K	91 lm/W	550 lm
911401580312	SM303C P9 940 PSU VWB	4000 K	87 lm/W	780 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401599412	SP303P P6S 930 PSU WB	5.4 W
911401504322	SP303P P9S 940 PSU VWB	8.1 W
911401516022	SM303C P28 940 PSU NB	25.2 W
911401518022	SM304C P10 930 PSU MB	11 W
911401518522	SM304C P10 940 PSU WB	11 W
911401520722	SM304C P12 950 PSU WB	10.8 W
911401522022	SM304C P15 930 PSU MB	13.5 W
911401522122	SM304C P15 930 PSU WB	13.5 W
911401522522	SM304C P15 940 PSU WB	13.5 W
911401584312	SM303C P6S 940 PSU VWB	5.4 W

Order Code	Full Product Name	Power Consumption
911401588212	SM303C P9S 940 PSU WB	8.1 W
911401507422	SM303C P20 930 PSU WB	18 W
911401507522	SM303C P20 930 PSU VWB	18 W
911401508122	SM303C P20 940 PSU MB	18 W
911401508322	SM303C P20 940 PSU VWB	18 W
911401574912	SM303C P6 927 PSU MB	5.4 W
911401575112	SM303C P6 927 PSU VWB	5.4 W
911401576312	SM303C P6 940 PSU VWB	5.4 W
911401580312	SM303C P9 940 PSU VWB	8.1 W

