

FlexBlend, Surface Mounted

SM340C



FlexBlend heading the way to efficient and flexible furnished offices areas

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now, and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that

can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Benefits

- Return of investment less than 3 years
- A flexible office, with application flexibility to the choice of luminaires to fit many office areas
- Future ready: scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education
- Healthcare

Features

- Fully office compliant (UGR <19, L65 < 3000cd/sm) , light level according to office applications requirements
- Homogenous and uniform light effect

Versions

- Various mounting options, dimensional variety and local options
- Integrated sensors
- Ready to be connected to software based lighting systems such as Interact Office
- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void





FlexBlend Surface Mounted
SM340C MLO WH



FlexBlend Surface Mounted
SM340C PCS WH

Dimensional drawing



Product details



FlexBlend Surface Mounted
SM340C WH



FlexBlend Surface Mounted
SM340C WH



FlexBlend Suspended SP340P
WH



FlexBlend Surface Mounted
SM340C brackets

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes (relates to presence/ movement detection and daylight harvesting)
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3

Product Data

Product family code	SM340C [FLEXBLEND STAND-ALONE]
---------------------	--------------------------------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910925867136	SM340C 36S/940 DEIA MLO L120 WH	3,600 lm	95 lm/W
910925867099	SM340C 35S/940 DEIA PCS L150 WH	3,500 lm	140 lm/W
910925867134	SM340C 36S/940 DEIA PCS L120 WH	3,600 lm	138 lm/W
910925867865	SM340C 28S/940 DEIA PCS L120 WH	2,800 lm	136 lm/W


Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867136	SM340C 36S/940 DEIA MLO L120 WH	38 W
910925867099	SM340C 35S/940 DEIA PCS L150 WH	25 W
910925867134	SM340C 36S/940 DEIA PCS L120 WH	26 W
910925867865	SM340C 28S/940 DEIA PCS L120 WH	20.5 W

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925867136	SM340C 36S/940 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s
910925867099	SM340C 35S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s
910925867134	SM340C 36S/940 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s
910925867865	SM340C 28S/940 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s


Polar normal diagrams



SM340CI - 910925867099

SM340CI - 910925867134

SM340CI - 910925867865



SM340CI - 910925867136