



Maxos fusion Office: Flexible solution delivers ideal light output

Maxos fusion is an adaptable LED trunk mounted luminaire that offers an excellent quality of light. It's an efficient and flexible lighting solution that can be used in a variety of applications including industrial, commercial and office environments, offering a range of lighting options to meet different requirements. With the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- A flexible office, with application flexibility to the choice of luminaires to fit many office areas.
- Future ready: scalable and ready to be connected to controls and lighting systems.
- Homogenous and uniform light effect

Applications

- Offices
- Education
- Retail



Features

- Fully office compliant (UGR <19, L65 < 3000cd/m²), light level according to office application requirements
- Best-in-class efficacy > 140 lm/W

Versions



Dimensional drawing



SM970X 45S/840 DIA D/I MXO W19L114 WH

SM970X 56S/840 DIA D/I MXO W19L152 WH

Product details



Maxos fusion Office DPP optics



Maxos fusion Office DPP optics



Maxos fusion Office DPP 1



Maxos fusion Office DPP 2

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Ambient temperature range	0 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3

Product Data

Product family code	SM970X [Maxos fusion Office]
---------------------	------------------------------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
62222700	SM970X 45S/840 DIA D/I MXO W19L114 WH	4,500 lm	141 lm/W
62223400	SM970X 56S/840 DIA D/I MXO W19L152 WH	5,600 lm	144 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
62222700	SM970X 45S/840 DIA D/I MXO W19L114 WH	32 W
62223400	SM970X 56S/840 DIA D/I MXO W19L152 WH	39 W