



# Philips TrueLine suspended: True line of light

## TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

### Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

# TrueLine, suspended

## Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering
- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

## Application

- Offices
- Education
- Retail

## Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

## Versions



TrueLine-SP530 L570 BK



TrueLine-SP534P



SP530P with U4 BK sensor



TrueLine-SP530 L570 WH



TrueLine-SP530 L2810 BK




TrueLinesuspended-4FTALU-SENSOR



TrueLineSP-Black-sensor-RTP8ft


# TrueLine, suspended

## Dimensional drawing



# TrueLine, suspended

## Dimensional drawing



# TrueLine, suspended

## Product details



TrueLine\_Suspended-line-side-view



TrueLine\_Suspended-line-top-view



TrueLine Suspended black housing



TrueLine\_Suspended-top-view



TrueLine\_Suspended-U3



TrueLine\_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine-SP-line-U3

# TrueLine, suspended

## Product details



TrueLine Suspended black housing



SP530P U4 BK DPP



TrueLine\_SM\_SP-line-connectio-  
side-view-2

General Information	
Driver included	Yes
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Emergency Operation	
Emergency lighting	DC operated central emergency lighting
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Number of gear units
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	1 unit
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	1 unit
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	1 unit
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	1 unit
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	1 unit
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	1 unit
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	1 unit
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	1 unit
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	1 unit
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	1 unit
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	1 unit
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	1 unit
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	1 unit
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	1 unit
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	1 unit
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	1 unit
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	1 unit
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	1 unit
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	1 unit
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	1 unit
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	1 unit
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	1 unit
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	1 unit
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	1 unit
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	1 unit
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	1 unit
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	1 unit
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	1 unit
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	1 unit
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	1 unit
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	1 unit
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	2 units
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	1 unit
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	1 unit
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	1 unit
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	1 unit
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	1 unit
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	1 unit
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	1 unit
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	1 unit
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	1 unit
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	1 unit
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	1 unit
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	1 unit
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	2 units
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	2 units
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	1 unit
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	1 unit
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	1 unit
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	1 unit
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	1 unit

Order Code	Full Product Name	Number of gear units
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	1 unit
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	1 unit
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	1 unit
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	1 unit
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	1 unit
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	1 unit
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	1 unit
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	1 unit
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	1 unit
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	1 unit
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	1 unit
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	1 unit
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	1 unit
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	1 unit
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	1 unit
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	1 unit
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	1 unit
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	1 unit
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	1 unit
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	1 unit
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	1 unit
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	1 unit
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	1 unit
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	1 unit
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	1 unit
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	1 unit
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	1 unit
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	2 units
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	1 unit
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	1 unit
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	120 degree(s)	4000 K	>90	131 lm/W
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106189	SP534P 43S/940 DEIA	120 degree(s)	4000 K	>90	132 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	120 degree(s)	4000 K	>90	139 lm/W
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	120 degree(s)	3000 K	>90	125 lm/W
910505105969	SP530P 34S/ UE840 DEIA L1130 SM2 ALU	-	4000 K	>80	173 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	-	4000 K	>80	176 lm/W
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	-	4000 K	>80	137 lm/W
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	115 lm/W
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	139 lm/W
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	104 lm/W
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	141 lm/W
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	135 lm/W
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	120 degree(s)	4000 K	>90	136 lm/W
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	133 lm/W
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	139 lm/W
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	120 degree(s)	3000 K	>90	112 lm/W
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	120 degree(s)	3000 K	>90	134 lm/W
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	120 degree(s)	3000 K	>90	128 lm/W
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	129 lm/W
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	114 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	141 lm/W
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	118 lm/W
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	116 lm/W
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	143 lm/W
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	120 degree(s)	4000 K	>90	140 lm/W
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	120 degree(s)	4000 K	>90	130 lm/W
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	120 degree(s)	Tunable white 2700-6500 K	>90	116 lm/W
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	120 degree(s)	4000 K	>90	103 lm/W
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	120 degree(s)	3000 K	>90	109 lm/W
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	120 degree(s)	3000 K	>90	130 lm/W
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	116 lm/W
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	159 lm/W
910505106221	SP530P 50S/TW9 SEIA	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	U4 SM2 L1450 ALU				
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	91 lm/W
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	116 lm/W
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	100 lm/W
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	93 lm/W
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	120 degree(s)	3000 K	>90	103 lm/W
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	125 lm/W
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	121 lm/W
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	120 degree(s)	4000 K	>90	139 lm/W
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	120 degree(s)	4000 K	>90	138 lm/W
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	120 degree(s)	4000 K	>90	141 lm/W
910505106204	SP532P 72S/940 DEIA	120 degree(s)	4000 K	>90	138 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	SM2 L2250 ALU				
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	120 degree(s)	4000 K	>90	122 lm/W
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	120 degree(s)	4000 K	>90	119 lm/W
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	120 degree(s)	3000 K	>90	136 lm/W
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	120 degree(s)	3000 K	>90	132 lm/W
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	120 degree(s)	3000 K	>90	114 lm/W
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	120 degree(s)	4000 K	>90	133 lm/W
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	120 degree(s)	3000 K	>90	127 lm/W
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	120 degree(s)	4000 K	>90	138 lm/W
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	120 degree(s)	4000 K	>90	136 lm/W
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	120 degree(s)	3000 K	>90	112 lm/W
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	120 degree(s)	4000 K	>90	138 lm/W
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	120 degree(s)	4000 K	>90	138 lm/W
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	120 degree(s)	3000 K	>90	133 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	120 degree(s)	3000 K	>90	135 lm/W
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	120 degree(s)	4000 K	>90	140 lm/W
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	120 degree(s)	4000 K	>90	138 lm/W
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	120 degree(s)	4000 K	>90	104 lm/W
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	120 degree(s)	4000 K	>90	139 lm/W
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	120 degree(s)	3000 K	>90	132 lm/W
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	120 degree(s)	4000 K	>90	138 lm/W
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	120 degree(s)	4000 K	>90	136 lm/W
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	120 degree(s)	4000 K	>90	136 lm/W
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	120 degree(s)	4000 K	>90	132 lm/W
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	120 degree(s)	4000 K	>90	136 lm/W
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	124 lm/W
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	120 degree(s)	Tunable white 2700-6500 K	>90	100 lm/W
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	120 degree(s)	4000 K	>90	138 lm/W
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	120 degree(s)	4000 K	>90	143 lm/W
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	120 degree(s)	4000 K	>90	139 lm/W

### Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	4,700 lm	Wide beam
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	3,400 lm	Asymmetrical mirror
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	2,900 lm	Wide beam

Order Code	Full Product Name	Luminous Flux	Optic type
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	4,300 lm	Asymmetrical mirror
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	1,700 lm	Wide beam
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	2,400 lm	Wide beam

## TrueLine, suspended

Order Code	Full Product Name	Luminous Flux	Optic type	Order Code	Full Product Name	Luminous Flux	Optic type
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	3,400 lm	Wide beam office compliant	910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	700 lm	Wide beam
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	4,300 lm	Wide beam office compliant	910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	1,200 lm	Wide beam
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	4,300 lm	Wide beam office compliant	910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	3,000 lm	Wide beam
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	4,100 lm	Wide beam	910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	7,700 lm	Wide beam office compliant
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	5,000 lm	Wide beam	910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	5,400 lm	Wide beam
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	4,700 lm	Wide beam	910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	5,000 lm	Wide beam office compliant
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	1,500 lm	Wide beam	910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	3,100 lm	Wide beam
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	4,300 lm	Wide beam	910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	5,800 lm	Wide beam office compliant
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	7,700 lm	Wide beam	910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	4,100 lm	Wide beam
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	3,600 lm	Wide beam	910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	4,000 lm	Wide beam office compliant
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	5,800 lm	Wide beam	910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	2,500 lm	Wide beam
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	3,400 lm	Wide beam	910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	3,000 lm	Wide beam
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	3,300 lm	Wide beam	910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	5,000 lm	Wide beam
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	4,900 lm	Wide beam	910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	8,600 lm	Wide beam
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	7,700 lm	Wide beam	910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	5,000 lm	Wide beam
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	4,000 lm	Asymmetrical mirror	910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	9,800 lm	Wide beam
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	2,400 lm	Wide beam	910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	6,200 lm	Wide beam
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	2,100 lm	Wide beam	910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	7,200 lm	Wide beam
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	3,300 lm	Wide beam	910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	4,800 lm	Wide beam
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	2,900 lm	Wide beam	910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	8,200 lm	Wide beam
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	6,600 lm	Wide beam	910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	3,800 lm	Wide beam
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	5,400 lm	Wide beam	910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	5,800 lm	Wide beam
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	4,900 lm	Wide beam	910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	6,600 lm	Wide beam
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	4,000 lm	Wide beam	910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	700 lm	Wide beam
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	5,000 lm	Asymmetrical mirror	910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	1,000 lm	Wide beam
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	6,600 lm	Wide beam	910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	2,900 lm	Wide beam

## TrueLine, suspended

Order Code	Full Product Name	Luminous Flux	Optic type
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	3,600 lm	Wide beam
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	3,300 lm	Wide beam
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	6,600 lm	Wide beam
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	4,700 lm	Wide beam
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	5,000 lm	Wide beam
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	6,200 lm	Wide beam
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	9,400 lm	Wide beam
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	4,700 lm	Wide beam
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	1,500 lm	Wide beam
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	3,400 lm	Wide beam
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	2,900 lm	Wide beam
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	2,900 lm	Wide beam

Order Code	Full Product Name	Luminous Flux	Optic type
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	3,600 lm	Wide beam
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	2,900 lm	Wide beam
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	3,600 lm	Wide beam
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	2,900 lm	Wide beam
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	4,300 lm	Asymmetrical mirror
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	4,700 lm	Wide beam
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	3,600 lm	Wide beam
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	3,600 lm	Wide beam
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	3,300 lm	Wide beam
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	4,700 lm	Wide beam
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	4,000 lm	Wide beam
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	6,600 lm	Wide beam

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	34 W	No
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	26 W	No
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	21 W	No
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	32.5 W	No
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	12.2 W	No
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	18.6 W	No
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	19.6 W	No
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	24.5 W	No
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	31 W	No
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	35.5 W	No
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	36 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	34 W	No
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	14.4 W	No
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	30.5 W	No
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	57 W	No
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	26.5 W	No
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	44 W	No
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	24.5 W	No
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	29.5 W	No
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	38.5 W	No
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	60 W	No
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	31 W	No

## TrueLine, suspended

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	21 W	No
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	16.4 W	No
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	28 W	No
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	21 W	No
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	48 W	No
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	46.5 W	No
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	36.5 W	No
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	28.5 W	No
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	38.5 W	No
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	57 W	No
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	7.2 W	No
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	11 W	No
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	23 W	No
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	67 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	34 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	41.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	34 W	Yes (relates to presence/movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	49 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	41 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	33 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	27 W	Yes (relates to presence/movement detection and daylight harvesting)
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	29 W	No
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	40 W	No
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	71 W	No
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	36 W	No
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	71 W	No
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	44 W	No
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	52 W	No
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	39.5 W	No
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	69 W	No
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	28 W	No
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	44 W	No
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	58 W	No
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	6 W	No

## TrueLine, suspended

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	8.5 W	No
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	21 W	No
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	26.5 W	No
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	29.5 W	No
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	48 W	No
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	34 W	No
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	37.5 W	No
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	46 W	No
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	67 W	No
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	34 W	No
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	14.4 W	No
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	24.5 W	No
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	22 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	21 W	No
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	26.5 W	No
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	21 W	No
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	26.5 W	No
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	21 W	No
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	32.5 W	No
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	34 W	No
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	26.5 W	No
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	29 W	No
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	33 W	No
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	34 W	No
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	28 W	No
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	47.5 W	No

### Controls and Dimming

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	-	1%
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	-	1%
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	-	1%
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	-	1%
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	-	1%
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	-	1%
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	-	-
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	-	-
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	-	-

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	-	1%
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	-	1%
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	-	1%
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	-	1%
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	-	1%
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	-	1%
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	-	1%
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	-	1%
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	-	1%

## TrueLine, suspended

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	-	1%
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	-	1%
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	-	1%
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	-	1%
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	-	1%
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	-	1%
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	-	1%
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	-	1%
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	-	1%
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	-	1%
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	-	1%
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	-	1%
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	-	1%
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Upgradable sensor slot with SC200 sensor	1%
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	-	1%
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	-	1%
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	-	1%
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SC200 sensor	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Upgradable sensor slot with SC200 sensor	1%
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Upgradable sensor slot with SC200 sensor	1%
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Upgradable sensor slot with SC200 sensor	1%
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	-	1%
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	-	1%
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	-	1%
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	-	1%
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	-	1%
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	-	1%
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	-	1%
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	-	1%
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	-	1%
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	-	1%
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	-	1%
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	-	1%

## TrueLine, suspended

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	-	1%
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	-	1%
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	-	1%
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	-	1%
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	-	1%
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	-	1%
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	-	1%
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	-	1%
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	-	1%
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	-	1%
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	-	1%
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	-	1%
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	-	1%
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	-	1%
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	-	1%
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	-	1%
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	-	1%
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SC200 sensor	1%
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SC200 sensor	1%

## Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Aluminum
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	Black
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	Black
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	Aluminum
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	Aluminum
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	Aluminum
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	Aluminum
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	Aluminum
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	Aluminum
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	Aluminum
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	Aluminum
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	Aluminum
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	Aluminum
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	Aluminum
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	Aluminum
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	Aluminum
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	Aluminum
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	Aluminum
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	Aluminum
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	Aluminum
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	Aluminum
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	Aluminum
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	Aluminum
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	Aluminum
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	Aluminum
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	Aluminum
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	Aluminum
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Black
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	White
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	White
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	Black
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	Aluminum
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	Aluminum
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	Aluminum
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	Aluminum
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	Aluminum
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	Aluminum
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	Aluminum
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	Aluminum
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Aluminum
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Aluminum
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Aluminum

## TrueLine, suspended

Order Code	Full Product Name	Housing Color
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Black
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Black
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Black
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	Aluminum
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	Aluminum
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	Aluminum
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Aluminum
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Aluminum
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Aluminum
910505106193	SP530P 75/940 DEIA LE SM2 L570 ALU	Aluminum
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	Aluminum
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	White
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	White
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	White
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	White
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	White
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	White
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	White

Order Code	Full Product Name	Housing Color
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	White
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	Black
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	Black
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	Black
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Black
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Black
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Black
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Aluminum
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Aluminum
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Aluminum
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Aluminum
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Aluminum
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Aluminum
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Aluminum
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Aluminum

### Emergency Operation

Order Code	Full Product Name	Central Emergency
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Yes
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Yes
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Yes
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Yes
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	Yes
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	Yes
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	Yes
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	Yes
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	Yes
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	Yes
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	Yes
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	Yes
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	Yes
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	Yes
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	Yes
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	Yes
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	Yes
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	Yes
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	Yes
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	Yes
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	Yes
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	Yes
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	Yes
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	Yes
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	Yes
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	Yes
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	Yes
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	Yes
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	Yes
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	Yes

Order Code	Full Product Name	Central Emergency
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	Yes
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Yes
910505106194	SP531P 75/940 DEIA LE SM2 L570 WH	Yes
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	Yes
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	Yes
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	Yes
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	Yes
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	Yes
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	Yes
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	Yes
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	Yes
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	Yes
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	Yes
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Yes
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Yes
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Yes
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Yes
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Yes
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Yes
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	Yes
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	Yes
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	Yes
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Yes
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Yes
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Yes
910505106193	SP530P 75/940 DEIA LE SM2 L570 ALU	Yes
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	Yes
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	Yes
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	Yes
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	Yes

## TrueLine, suspended

Order Code	Full Product Name	Central Emergency
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	Yes
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	Yes
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	Yes
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	Yes
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	Yes
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	Yes
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	Yes
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	Yes
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Yes
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Yes
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Yes

Order Code	Full Product Name	Central Emergency
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Yes
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Yes
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Yes
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Yes
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Yes
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Yes
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	-
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	-
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Yes
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Yes
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Yes

## Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			Flickering value	Flickering value as per EN 61000-3-3	
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	+10 to +40 °C	1	0.4	0.4
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	+10 to +40 °C	1	0.4	0.4
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	+10 to +35 °C	-	-	-
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	+10 to +35 °C	-	-	-
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	+10 to +35 °C	-	-	-
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			Flickering value	Flickering value as per EN 61000-3-3	
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	+10 to +40 °C	1	0.4	0.4
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	+10 to +40 °C	1	0.4	0.4
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	+10 to +40 °C	1	0.4	0.4

## TrueLine, suspended

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1		0.4
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1		0.4
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1		0.4
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1		0.4
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	+10 to +40 °C	1		0.4
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	+10 to +40 °C	1		0.4
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	+10 to +40 °C	1		0.4
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	+10 to +40 °C	1		0.4
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	+10 to +40 °C	1		0.4
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	+10 to +40 °C	1		0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1		0.4
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1		0.4
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1		0.4
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1		0.4
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	+10 to +40 °C	1		0.4
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	+10 to +40 °C	1		0.4
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	+10 to +40 °C	1		0.4
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	+10 to +40 °C	1		0.4
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	+10 to +40 °C	1		0.4
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	+10 to +40 °C	1		0.4
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	+10 to +40 °C	1		0.4
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	+10 to +40 °C	1		0.4
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	+10 to +40 °C	1		0.4
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	+10 to +40 °C	1		0.4
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	+10 to +40 °C	1		0.4

## TrueLine, suspended

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	+10 to +40 °C	1	0.4
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	+10 to +40 °C	1	0.4
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	+10 to +40 °C	1	0.4
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	+10 to +40 °C	1	0.4
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	+10 to +40 °C	1	0.4
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	+10 to +40 °C	1	0.4
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	+10 to +40 °C	1	0.4
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	+10 to +40 °C	1	0.4
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	+10 to +40 °C	1	0.4
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	+10 to +40 °C	1	0.4
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	+10 to +40 °C	1	0.4
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	+10 to +40 °C	1	0.4
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	+10 to +40 °C	1	0.4
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	+10 to +40 °C	1	0.4
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	+10 to +40 °C	1	0.4
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	+10 to +40 °C	1	0.4
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	+10 to +40 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	+10 to +40 °C	1	0.4
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	+10 to +40 °C	1	0.4
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	+10 to +40 °C	1	0.4
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	+10 to +40 °C	1	0.4
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	+10 to +40 °C	1	0.4
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	+10 to +40 °C	1	0.4
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	+10 to +40 °C	1	0.4
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	+10 to +40 °C	1	0.4
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	+10 to +40 °C	1	0.4
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	+10 to +40 °C	1	0.4
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	+10 to +40 °C	1	0.4
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	+10 to +40 °C	1	0.4
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1	0.4
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	+10 to +40 °C	1	0.4
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	+10 to +40 °C	1	0.4

### Initial Performance (IEC Compliant)

# TrueLine, suspended

Order Code	Full Product Name	Initial chromaticity
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	(0.38, 0.38) SDCM <3
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	(0.43, 0.40) SDCM <3
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	(0.39, 0.38) SDCM <3
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	(0.39, 0.38) SDCM <3
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	(0.39, 0.38) SDCM <3
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	(0.38, 0.38) SDCM <3
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	(0.43, 0.40) SDCM <3
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	(0.43, 0.40) SDCM <3
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	(0.43, 0.40) SDCM <3
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	(0.38, 0.38) SDCM <3
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	(0.38, 0.38) SDCM <3
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	(0.43, 0.40) SDCM <3
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	(0.43, 0.40) SDCM <3
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	Tunable, SDCM ≤3
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	Tunable, SDCM ≤3
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	Tunable, SDCM ≤3
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	Tunable, SDCM ≤3
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	Tunable, SDCM ≤3
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	Tunable, SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	Tunable, SDCM ≤3
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	Tunable, SDCM ≤3
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	(0.43, 0.40) SDCM <3
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	(0.38, 0.38) SDCM <3
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	(0.38, 0.38) SDCM <3
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	(0.38, 0.38) SDCM <3
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	(0.38, 0.38) SDCM <3
910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	(0.38, 0.38) SDCM <3
910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	(0.38, 0.38) SDCM <3
910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	(0.38, 0.38) SDCM <3
910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	(0.38, 0.38) SDCM <3
910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	(0.43, 0.40) SDCM <3
910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	(0.43, 0.40) SDCM <3
910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	(0.43, 0.40) SDCM <3
910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	(0.38, 0.38) SDCM <3
910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	(0.43, 0.40) SDCM <3
910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	(0.38, 0.38) SDCM <3
910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	(0.38, 0.38) SDCM <3
910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	(0.43, 0.40) SDCM <3
910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	(0.38, 0.38) SDCM <3
910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	(0.38, 0.38) SDCM <3
910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	(0.43, 0.40) SDCM <3
910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	(0.43, 0.40) SDCM <3
910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	(0.38, 0.38) SDCM <3
910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	(0.38, 0.38) SDCM <3
910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	(0.38, 0.38) SDCM <3
910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	(0.38, 0.38) SDCM <3
910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	(0.43, 0.40) SDCM <3
910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	(0.38, 0.38) SDCM <3
910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	(0.38, 0.38) SDCM <3
910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	(0.38, 0.38) SDCM <3
910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	(0.38, 0.38) SDCM <3
910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	(0.38, 0.38) SDCM <3
910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	(0.38, 0.38) SDCM <3
910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	(0.38, 0.38) SDCM <3
910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	(0.38, 0.38) SDCM <3

## Product Data


Order Code	Full Product Name	Product family code
910505106179	SP532P 47S/940 DEIA LS SM2 L1410 ALU	SP532P
910505106182	SP534P 34S/940 DEIA LS SM2 L1130 ALU	SP534P
910505106186	SP532P 29S/940 DEIA LS SM2 L1410 ALU	SP532P
910505106189	SP534P 43S/940 DEIA LS SM2 L1410 ALU	SP534P
910505106195	SP530P 17S/940 DEIA LE SM2 L570 BK	SP530P
910505106197	SP532P 24S/930 DEIA LE SM2 L570 BK	SP532P
910505105969	SP530P 34S/UE840 DEIA L1130 SM2 ALU	SP530P

Order Code	Full Product Name	Product family code
910505105970	SP530P 43S/UE840 DEIA L1410 SM2 ALU	SP530P
910505105972	SP530P 43S/BU840 DEIA L1410 SM2 ALU	SP530P
910505106142	SP533P 41S/940 DEIA SM2 L1130 ALU	SP533P
910505106144	SP530P 50S/940 DEIA SM2 L1410 ALU	SP530P
910505106145	SP532P 47S/940 DEIA SM2 L1410 ALU	SP532P
910505106147	SP531P 15S/940 DEIA SM2 L1130 ALU	SP531P
910505106148	SP530P 43S/940 DEIA SM2 L1410 ALU	SP530P


## TrueLine, suspended

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
910505106149	SP532P 77S/940 DEIA SM2 L1410 ALU	SP532P	910505106209	SP530P 62S/940 SEIA U4 SM2 L2850 BK	SP530P
910505106150	SP532P 36S/940 DEIA L1130 SM2 ALU	SP532P	910505106204	SP532P 72S/940 DEIA SM2 L2250 ALU	SP532P
910505106151	SP532P 58S/940 DEIA SM2 L1130 ALU	SP532P	910505106205	SP533P 48S/940 DEIA SM2 L2250 ALU	SP533P
910505106152	SP530P 34S/940 DEIA SM2 L1130 ALU	SP530P	910505106207	SP533P 82S/940 DEIA SM2 L2250 ALU	SP533P
910505106153	SP533P 33S/930 DEIA SM2 L1410 ALU	SP533P	910505106208	SP530P 38S/930 DEIA LN SW2 L2810 ALU	SP530P
910505106154	SP532P 49S/930 DEIA SM2 L1130 ALU	SP532P	910505106212	SP532P 58S/930 DEIA LN SM2 L2810 ALU	SP532P
910505106155	SP532P 77S/930 DEIA SM2 L1410 ALU	SP532P	910505106213	SP533P 66S/930 DEIA LN SW2 L2810 ALU	SP533P
910505106158	SP534P 40S/940 DEIA SM2 L1130 ALU	SP534P	910505106193	SP530P 7S/940 DEIA LE SM2 L570 ALU	SP530P
910505106159	SP533P 24S/940 DEIA SM2 L1130 ALU	SP533P	910505106196	SP532P 10S/930 DEIA LE SM2 L570 ALU	SP532P
910505106160	SP532P 21S/940 DEIA SM2 L1130 ALU	SP532P	910505106143	SP532P 29S/940 DEIA SM2 L1410 WH	SP532P
910505106161	SP533P 33S/940 DEIA SM2 L1410 ALU	SP533P	910505106156	SP532P 36S/940 DEIA SM2 L1130 WH	SP532P
910505106162	SP532P 29S/940 DEIA SM2 L1410 ALU	SP532P	910505106157	SP533P 33S/930 DEIA SM2 L1410 WH	SP533P
910505106164	SP532P 66S/940 DEIA SM2 L1410 ALU	SP532P	910505106167	SP532P 66S/940 DEIA SM2 L1410 WH	SP532P
910505106165	SP533P 54S/940 DEIA SM2 L1410 ALU	SP533P	910505106168	SP532P 47S/940 DEIA SM2 L1410 WH	SP532P
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	SP532P	910505106203	SP530P 50S/930 DEIA SM2 L2250 WH	SP530P
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	SP530P	910505106210	SP531P 62S/930 DEIA SM2 L2810 WH	SP531P
910505106163	SP534P 50S/940 DEIA SM2 L1410 ALU	SP534P	910505106211	SP532P 94S/940 DEIA SM2 L2810 WH	SP532P
910505106216	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	SP532P	910505106174	SP532P 47S/940 DEIA SM2 L1410 BK	SP532P
910505106194	SP531P 7S/940 DEIA LE SM2 L570 WH	SP531P	910505106175	SP531P 15S/940 DEIA SM2 L1130 BK	SP531P
910505106198	SP533P 12S/930 DEIA LE SM2 L570 WH	SP533P	910505106176	SP530P 34S/940 DEIA SM2 L1130 BK	SP530P
910505106199	SP530P 30S/930 DEIA LN SM2 L2250 BK	SP530P	910505106177	SP532P 29S/930 DEIA LNP SM2 L1410 BK	SP532P
910505106219	SP532P 77S/TW9 SEIA U4 SM2 L1450 ALU	SP532P	910505106178	SP532P 29S/940 DEIA LNP SM2 L1410 BK	SP532P
910505106220	SP533P 54S/TW9 SEIA U4 SM2 L1450 ALU	SP533P	910505106183	SP532P 36S/940 DEIA LNP SM2T L1130 BK	SP532P
910505106221	SP530P 50S/TW9 SEIA U4 SM2 L1450 ALU	SP530P	910505106180	SP532P 29S/940 DEIA LN SW2 L1410 ALU	SP532P
910505106222	SP531P 31S/TW9 SEIA U4 SM2 L1450 ALU	SP531P	910505106181	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	SP532P
910505106223	SP532P 58S/TW9 SEIA U4 SM2 L1170 ALU	SP532P	910505106184	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	SP532P
910505106224	SP533P 41S/TW9 SEIA U4 SM2 L1170 ALU	SP533P	910505106185	SP534P 43S/940 DEIA LN SW2 L1410 ALU	SP534P
910505106225	SP530P 40S/TW9 SEIA U4 SM2 L1170 ALU	SP530P	910505106187	SP532P 47S/940 DEIA LN SW2 L1410 ALU	SP532P
910505106226	SP531P 25S/TW9 SEIA U4 SM2 L1170 ALU	SP531P	910505106188	SP532P 36S/940 DEIA LN SW2 L1130 ALU	SP532P
910505106201	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	SP531P	910505106214	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	SP532P
910505106217	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	SP530P	910505106215	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	SP533P
910505106218	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	SP530P	910505106190	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	SP532P
910505106202	SP530P 50S/940 SEIA U4 SM2 L2290 BK	SP530P	910505106191	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	SP530P
910505106206	SP532P 98S/940 SEIA U4 SM2 L2290 BK	SP532P	910505106192	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	SP532P


### Polar Wide Diagrams



Polar Normal (separate) - null - 910505105972




Polar Normal (separate) - null - 910505105970




Polar Normal (separate) - null - 910505105969


Polar Wide Diagrams




Polar Normal (separate) - SP530PI -  
910505106205




Polar Normal (separate) - SP530PI -  
910505106143




Polar Normal (separate) - SP530PI -  
910505106218




Polar Normal (separate) - SP530PI -  
910505106206




Polar Normal (separate) - SP530PI -  
910505106198




Polar Normal (separate) - SP530PI -  
910505106148



Polar Normal (separate) - SP530PI -  
910505106225




Polar Normal (separate) - SP530PI -  
910505106186




Polar Normal (separate) - SP530PI -  
910505106178


Polar Wide Diagrams




Polar Normal (separate) - SP530PI - 910505106185




Polar Normal (separate) - SP530PI - 910505106224




Polar Normal (separate) - SP530PI - 910505106217




Polar Normal (separate) - SP530PI - 910505106162




Polar Normal (separate) - SP530PI - 910505106219




Polar Normal (separate) - SP530PI - 910505106177



Polar Normal (separate) - SP530PI - 910505106183




Polar Normal (separate) - SP530PI - 910505106193




Polar Normal (separate) - SP530PI - 910505106197


Polar Wide Diagrams




Polar Normal (separate) - SP530PI -  
910505106145




Polar Normal (separate) - SP530PI -  
910505106150




Polar Normal (separate) - SP530PI -  
910505106203




Polar Normal (separate) - SP530PI -  
910505106164




Polar Normal (separate) - SP530PI -  
910505106152




Polar Normal (separate) - SP530PI -  
910505106149



Polar Normal (separate) - SP530PI -  
910505106201




Polar Normal (separate) - SP530PI -  
910505106144




Polar Normal (separate) - SP530PI -  
910505106174


Polar Wide Diagrams




Polar Normal (separate) - SP530PI -  
910505106155




Polar Normal (separate) - SP530PI -  
910505106196




Polar Normal (separate) - SP530PI -  
910505106212




Polar Normal (separate) - SP530PI -  
910505106191




Polar Normal (separate) - SP530PI -  
910505106176




Polar Normal (separate) - SP530PI -  
910505106158



Polar Normal (separate) - SP530PI -  
910505106222




Polar Normal (separate) - SP530PI -  
910505106207




Polar Normal (separate) - SP530PI -  
910505106220


Polar Wide Diagrams




Polar Normal (separate) - SP530PI - 910505106223




Polar Normal (separate) - SP530PI - 910505106180




Polar Normal (separate) - SP530PI - 910505106147




Polar Normal (separate) - SP530PI - 910505106216




Polar Normal (separate) - SP530PI - 910505106226




Polar Normal (separate) - SP530PI - 910505106199



Polar Normal (separate) - SP530PI - 910505106161




Polar Normal (separate) - SP530PI - 910505106215




Polar Normal (separate) - SP530PI - 910505106166


Polar Wide Diagrams




Polar Normal (separate) - SP530PI - 910505106159




Polar Normal (separate) - SP530PI - 910505106167




Polar Normal (separate) - SP530PI - 910505106194




Polar Normal (separate) - SP530PI - 910505106182




Polar Normal (separate) - SP530PI - 910505106192




Polar Normal (separate) - SP530PI - 910505106181



Polar Normal (separate) - SP530PI - 910505106189




Polar Normal (separate) - SP530PI - 910505106187




Polar Normal (separate) - SP530PI - 910505106195


Polar Wide Diagrams




Polar Normal (separate) - SP530PI - 910505106202




Polar Normal (separate) - SP530PI - 910505106214




Polar Normal (separate) - SP530PI - 910505106160




Polar Normal (separate) - SP530PI - 910505106209




Polar Normal (separate) - SP530PI - 910505106151




Polar Normal (separate) - SP530PI - 910505106179



Polar Normal (separate) - SP530PI - 910505106211




Polar Normal (separate) - SP530PI - 910505106163




Polar Normal (separate) - SP530PI - 910505106204


Polar Wide Diagrams




Polar Normal (separate) - SP530PI -  
910505106165




Polar Normal (separate) - SP530PI -  
910505106156




Polar Normal (separate) - SP530PI -  
910505106173




Polar Normal (separate) - SP530PI -  
910505106142




Polar Normal (separate) - SP530PI -  
910505106208




Polar Normal (separate) - SP530PI -  
910505106184



Polar Normal (separate) - SP530PI -  
910505106213




Polar Normal (separate) - SP530PI -  
910505106210




Polar Normal (separate) - SP530PI -  
910505106221


Polar Wide Diagrams




Polar Normal (separate) - SP530PI -  
910505106153




Polar Normal (separate) - SP530PI -  
910505106188




Polar Normal (separate) - SP530PI -  
910505106154




Polar Normal (separate) - SP530PI -  
910505106175



Polar Normal (separate) - SP530PI -  
910505106157



Polar Normal (separate) - SP530PI -  
910505106190



Polar Normal (separate) - SP530PI -  
910505106168

TrueLine, suspended



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2026, April 29 - data subject to change