



# Philips TrueLine suspended: True line of light

## TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

### Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

# TrueLine, suspended

## Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering
- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

## Application

- Offices
- Education
- Retail

## Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

## Versions



TrueLine-SP534P



SP530P with U4 BK sensor



TrueLine-SP530 L2810 BK




TrueLine-SP530 U3 SNS210 L2850 Alu



TrueLine Suspended-U3


# TrueLine, suspended

## Dimensional drawing



# TrueLine, suspended

## Dimensional drawing



# TrueLine, suspended

## Product details



TrueLine\_Suspended-line-side-view



TrueLine\_Suspended-line-top-view



TrueLine Suspended black housing



TrueLine\_Suspended-top-view



TrueLine\_Suspended-U3



TrueLine\_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine-SP-line-U3

# TrueLine, suspended

## Product details



TrueLine Suspended black housing



SP530P U4 BK DPP



TrueLine\_SM\_SP-line-connectio-  
side-view-2

# TrueLine, suspended

## General Information

Driver included	Yes
Light source replaceable	No
Service tag	Yes

## Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90

## Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

## Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

## Mechanical and Housing

Mech. impact protection code	IK03
Ingress protection code	IP20

## Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

## Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Number of gear units
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	1 unit
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	1 unit
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	1 unit
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	1 unit
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	1 unit
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	1 unit
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	1 unit
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	1 unit
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	1 unit
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	1 unit
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	1 unit
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	1 unit
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	1 unit
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	1 unit
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	1 unit
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	1 unit
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	1 unit
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	1 unit
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	1 unit
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	1 unit
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	1 unit
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	1 unit
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	1 unit
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	1 unit
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	1 unit
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	1 unit
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	1 unit
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	1 unit
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	1 unit
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	1 unit
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	1 unit
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	1 unit
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	1 unit
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	2 units
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	1 unit
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	1 unit
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	1 unit
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	2 units
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	2 units
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	1 unit
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	1 unit
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	1 unit
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	1 unit
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	1 unit
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	1 unit
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	1 unit
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	1 unit
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	1 unit
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	1 unit
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	1 unit
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	1 unit

Order Code	Full Product Name	Number of gear units
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	1 unit
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	1 unit
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	1 unit
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	1 unit
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	1 unit
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	1 unit
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	1 unit
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	1 unit
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	1 unit
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	1 unit
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	1 unit
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	1 unit
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	1 unit
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	1 unit
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	1 unit
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	1 unit
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	2 units
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	1 unit
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	1 unit
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	1 unit

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	4000 K	131 lm/W	3,400 lm	Asymmetrical mirror
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	4000 K	139 lm/W	1,700 lm	Wide beam
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	3000 K	125 lm/W	2,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	4000 K	115 lm/W	4,100 lm	Wide beam
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	2,900 lm	Wide beam
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	4000 K	139 lm/W	5,000 lm	Wide beam
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	4000 K	104 lm/W	1,500 lm	Wide beam
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
97265000	SP532P 77S/940 DEIA	4000 K	135 lm/W	7,700 lm	Wide beam

## TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	SM2 L1410 ALU				
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	4000 K	133 lm/W	5,800 lm	Wide beam
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	4000 K	139 lm/W	3,400 lm	Wide beam
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	3000 K	112 lm/W	3,300 lm	Wide beam
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	3000 K	134 lm/W	4,900 lm	Wide beam
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	3000 K	128 lm/W	7,700 lm	Wide beam
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	4000 K	136 lm/W	3,600 lm	Wide beam
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	3000 K	112 lm/W	3,300 lm	Wide beam
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	4000 K	129 lm/W	4,000 lm	Asymmetrical mirror
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	4000 K	114 lm/W	2,400 lm	Wide beam
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	4000 K	141 lm/W	2,100 lm	Wide beam
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	4000 K	118 lm/W	3,300 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	6,600 lm	Wide beam
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	4000 K	116 lm/W	5,400 lm	Wide beam
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	4000 K	143 lm/W	4,900 lm	Wide beam
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	6,600 lm	Wide beam
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	4,700 lm	Wide beam
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	4000 K	140 lm/W	4,000 lm	Wide beam
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	4000 K	130 lm/W	5,000 lm	Asymmetrical mirror
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Tunable white 2700-6500 K	116 lm/W	6,600 lm	Wide beam
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	4000 K	103 lm/W	700 lm	Wide beam
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	3000 K	109 lm/W	1,200 lm	Wide beam
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	3000 K	130 lm/W	3,000 lm	Wide beam
97318300	SP530P 50S/TW9	Tunable white 2700-6500 K	125 lm/W	5,000 lm	Wide beam

## TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	SEIA SM2 U4 L2290 ALU				
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Tunable white 2700–6500 K	121 lm/W	8,600 lm	Wide beam
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	3000 K	103 lm/W	3,000 lm	Wide beam
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	4000 K	138 lm/W	7,200 lm	Wide beam
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	4000 K	122 lm/W	4,800 lm	Wide beam
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	4000 K	119 lm/W	8,200 lm	Wide beam
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	3000 K	136 lm/W	3,800 lm	Wide beam
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	3000 K	132 lm/W	5,800 lm	Wide beam
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	3000 K	114 lm/W	6,600 lm	Wide beam
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	4000 K	139 lm/W	5,000 lm	Wide beam
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	4000 K	138 lm/W	9,800 lm	Wide beam
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	4000 K	141 lm/W	6,200 lm	Wide beam
97280300	SP530P 7S/940 DEIA	4000 K	133 lm/W	700 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	LE SM2 L570 ALU				
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	3000 K	127 lm/W	1,000 lm	Wide beam
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	3000 K	133 lm/W	5,000 lm	Wide beam
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	3000 K	135 lm/W	6,200 lm	Wide beam
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	4000 K	140 lm/W	9,400 lm	Wide beam
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	4000 K	138 lm/W	4,700 lm	Wide beam
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	4000 K	104 lm/W	1,500 lm	Wide beam
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	4000 K	139 lm/W	3,400 lm	Wide beam
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	3000 K	132 lm/W	2,900 lm	Wide beam
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	4000 K	138 lm/W	2,900 lm	Wide beam
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	4000 K	136 lm/W	3,600 lm	Wide beam
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
97242100	SP532P 29S/940 DEIA	4000 K	138 lm/W	2,900 lm	Wide beam

## TrueLine, suspended

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		Temperature (Nom)	(Nom)		
	LNP SM2 L1410 ALU				
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
97315200	SP532P 36S/TW9	Tunable white 2700-6500 K	124 lm/W	3,600 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		Temperature (Nom)	(Nom)		
	DEIA LN SW2 L1130 ALU				
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Tunable white 2700-6500 K	100 lm/W	3,300 lm	Wide beam
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	4000 K	139 lm/W	6,600 lm	Wide beam

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	34 W
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	26 W
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	21 W
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	32.5 W
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	12.2 W
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	18.6 W
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	35.5 W
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	21 W
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	36 W
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	34 W
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	14.4 W
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	30.5 W
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	57 W
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	26.5 W
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	44 W
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	24.5 W
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	29.5 W
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	38.5 W
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	60 W
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	26.5 W
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	29.5 W
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	31 W
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	21 W
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	16.4 W
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	28 W
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	21 W
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	48 W

Order Code	Full Product Name	Power Consumption
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	46.5 W
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	36.5 W
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	48 W
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	34 W
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	28.5 W
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	38.5 W
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	57 W
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	7.2 W
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	11 W
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	23 W
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	40 W
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	71 W
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	29 W
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	52 W
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	39.5 W
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	69 W
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	28 W
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	44 W
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	58 W
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	36 W
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	71 W
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	44 W
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	6 W
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	8.5 W
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	37.5 W
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	46 W
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	67 W

## TrueLine, suspended

Order Code	Full Product Name	Power Consumption
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	34 W
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	14.4 W
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	24.5 W
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	22 W
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	21 W
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	26.5 W
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	21 W
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	26.5 W
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	21 W

Order Code	Full Product Name	Power Consumption
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	32.5 W
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	34 W
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	26.5 W
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	29 W
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	33 W
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	34 W
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	28 W
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	47.5 W

### Controls and Dimming

Order Code	Full Product Name	Embedded control
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	-
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	-
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	-
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	-
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	-
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	-
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	-
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	-
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	-
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	-
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	-
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	-
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	-
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	-
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	-
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	-
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	-
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	-
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	-
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	-
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	-
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	-
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	-
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	-
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	-
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	-
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	-
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	-
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	-
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	-
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	-
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	-
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	-
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Upgradable sensor slot with SNS210 sensor
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	-
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	-
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	-

Order Code	Full Product Name	Embedded control
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Upgradable sensor slot with SNS210 sensor
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Upgradable sensor slot with SNS210 sensor
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Upgradable sensor slot with SNS210 sensor
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	-
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	-
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	-
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	-
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	-
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	-
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Upgradable sensor slot with SNS210 sensor
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Upgradable sensor slot with SNS210 sensor
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Upgradable sensor slot with SNS210 sensor
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	-
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	-
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	-
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	-
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	-
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	-
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	-
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	-
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	-
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	-
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	-
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	-
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	-
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	-
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	-
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	-
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	-
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	-
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	-
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SNS210 sensor

## TrueLine, suspended

Order Code	Full Product Name	Embedded control
97232200	SP530P 40S/940 DEIA U4 SM2 L1170 ALU	Upgradable sensor slot with SNS210 sensor

Order Code	Full Product Name	Embedded control
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Upgradable sensor slot with SNS210 sensor

### Mechanical and Housing

Order Code	Full Product Name	Housing Color
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Aluminum
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Aluminum
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Aluminum
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Aluminum
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	Black
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	Black
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	Aluminum
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	White
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	Aluminum
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	Aluminum
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	Aluminum
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	Aluminum
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	Aluminum
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	Aluminum
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	Aluminum
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	Aluminum
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	Aluminum
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	Aluminum
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	Aluminum
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	White
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	White
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	Aluminum
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	Aluminum
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	Aluminum
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	Aluminum
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	Aluminum
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	Aluminum
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	Aluminum
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	Aluminum
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	White
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	White
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	Aluminum
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	Aluminum
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Black
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	White
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	White

Order Code	Full Product Name	Housing Color
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	Black
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Aluminum
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Aluminum
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Aluminum
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	Aluminum
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	Aluminum
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	Aluminum
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Aluminum
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Aluminum
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Aluminum
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Black
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Black
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Black
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	Aluminum
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	Aluminum
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	White
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	White
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	White
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	Black
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	Black
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	Black
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Black
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Black
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Black
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Aluminum
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Aluminum
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Aluminum
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Aluminum
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Aluminum
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Aluminum
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Aluminum
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Aluminum
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Aluminum
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Aluminum
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Aluminum

### Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting

## TrueLine, suspended

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	Yes	DC operated central emergency lighting
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	Yes	DC operated central emergency lighting
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	Yes	DC operated central emergency lighting
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	-	-
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	Yes	DC operated central emergency lighting
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	Yes	DC operated central emergency lighting
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	Yes	DC operated central emergency lighting
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	-	-
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	-	-
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	-	-
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Yes	DC operated central emergency lighting
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Yes	DC operated central emergency lighting
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Yes	DC operated central emergency lighting
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	-	-
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	-	-
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	-	-
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	Yes	DC operated central emergency lighting
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	Yes	DC operated central emergency lighting
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	Yes	DC operated central emergency lighting
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	Yes	DC operated central emergency lighting
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	Yes	DC operated central emergency lighting

## TrueLine, suspended

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	Yes	DC operated central emergency lighting
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	Yes	DC operated central emergency lighting
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	Yes	DC operated central emergency lighting
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Yes	DC operated central emergency lighting
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Yes	DC operated central emergency lighting
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Yes	DC operated central emergency lighting
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Yes	DC operated central emergency lighting
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Yes	DC operated central emergency lighting
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	-	-
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	-	-
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	-	-
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	-	-
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	-	-

### Product Data

Order Code	Full Product Name	Product family code
97252000	SP532P 47S/940 DEIA LS SM2 L1410 ALU	SP532P
97272800	SP534P 34S/940 DEIA LS SM2 L1130 ALU	SP534P
97240700	SP532P 29S/940 DEIA LS SM2 L1410 ALU	SP532P
97274200	SP534P 43S/940 DEIA LS SM2 L1410 ALU	SP534P
97282700	SP530P 17S/940 DEIA LE SM2 L570 BK	SP530P
97284100	SP532P 24S/930 DEIA LE SM2 L570 BK	SP532P
97270400	SP533P 41S/940 DEIA SM2 L1130 ALU	SP533P
97246900	SP532P 29S/940 DEIA SM2 L1410 WH	SP532P
97236000	SP530P 50S/940 DEIA SM2 L1410 ALU	SP530P
97254400	SP532P 47S/940 DEIA SM2 L1410 ALU	SP532P
97237700	SP531P 15S/940 DEIA SM2 L1130 ALU	SP531P
97233900	SP530P 43S/940 DEIA SM2 L1410 ALU	SP530P
97265000	SP532P 77S/940 DEIA SM2 L1410 ALU	SP532P
97250600	SP532P 36S/940 DEIA SM2 L1130 ALU	SP532P
97260500	SP532P 58S/940 DEIA SM2 L1130 ALU	SP532P
97227800	SP530P 34S/940 DEIA SM2 L1130 ALU	SP530P
97267400	SP533P 33S/930 DEIA SM2 L1410 ALU	SP533P
97258200	SP532P 49S/930 DEIA SM2 L1130 ALU	SP532P
97264300	SP532P 77S/930 DEIA SM2 L1410 ALU	SP532P
97251300	SP532P 36S/940 DEIA SM2 L1130 WH	SP532P
97268100	SP533P 33S/930 DEIA SM2 L1410 WH	SP533P
97273500	SP534P 40S/940 DEIA SM2 L1130 ALU	SP534P
97266700	SP533P 24S/940 DEIA SM2 L1130 ALU	SP533P
97239100	SP532P 21S/940 DEIA SM2 L1130 ALU	SP532P
97269800	SP533P 33S/940 DEIA SM2 L1410 ALU	SP533P
97245200	SP532P 29S/940 DEIA SM2 L1410 ALU	SP532P
97261200	SP532P 66S/940 DEIA SM2 L1410 ALU	SP532P
97271100	SP533P 54S/940 DEIA SM2 L1410 ALU	SP533P
97259900	SP532P 49S/940 DEIA SM2 L1130 ALU	SP532P


Order Code	Full Product Name	Product family code
97262900	SP532P 66S/940 DEIA SM2 L1410 WH	SP532P
97256800	SP532P 47S/940 DEIA SM2 L1410 WH	SP532P
97231500	SP530P 40S/940 DEIA SM2 L1130 ALU	SP530P
97276600	SP534P 50S/940 DEIA SM2 L1410 ALU	SP534P
97317600	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	SP532P
97281000	SP531P 7S/940 DEIA LE SM2 L570 WH	SP531P
97285800	SP533P 12S/930 DEIA LE SM2 L570 WH	SP533P
97292600	SP530P 30S/930 DEIA LN SM2 L2250 BK	SP530P
97318300	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	SP530P
97319000	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	SP532P
97293300	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	SP531P
97296400	SP532P 72S/940 DEIA SM2 L2250 ALU	SP532P
97297100	SP533P 48S/940 DEIA SM2 L2250 ALU	SP533P
97299500	SP533P 82S/940 DEIA SM2 L2250 ALU	SP533P
97305300	SP530P 38S/930 DEIA LN SW2 L2810 ALU	SP530P
97309100	SP532P 58S/930 DEIA LN SM2 L2810 ALU	SP532P
97310700	SP533P 66S/930 DEIA LN SW2 L2810 ALU	SP533P
97294000	SP530P 50S/940 SEIA U4 SM2 L2290 BK	SP530P
97298800	SP532P 98S/940 SEIA U4 SM2 L2290 BK	SP532P
97306000	SP530P 62S/940 SEIA U4 SM2 L2850 BK	SP530P
97280300	SP530P 7S/940 DEIA LE SM2 L570 ALU	SP530P
97283400	SP532P 10S/930 DEIA LE SM2 L570 ALU	SP532P
97295700	SP530P 50S/930 DEIA SM2 L2250 WH	SP530P
97307700	SP531P 62S/930 DEIA SM2 L2810 WH	SP531P
97308400	SP532P 94S/940 DEIA SM2 L2810 WH	SP532P
97255100	SP532P 47S/940 DEIA SM2 L1410 BK	SP532P
97238400	SP531P 15S/940 DEIA SM2 L1130 BK	SP531P
97228500	SP530P 34S/940 DEIA SM2 L1130 BK	SP530P
97243800	SP532P 29S/930 DEIA LNP SM2 L1410 BK	SP532P

# TrueLine, suspended


Order Code	Full Product Name	Product family code
97244500	SP532P 29S/940 DEIA LNP SM2 L1410 BK	SP532P
97249000	SP532P 36S/940 DEIA LNP SM2T L1130 BK	SP532P
97241400	SP532P 29S/940 DEIA LN SW2 L1410 ALU	SP532P
97248300	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	SP532P
97242100	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	SP532P
97275900	SP534P 43S/940 DEIA LN SW2 L1410 ALU	SP534P
97253700	SP532P 47S/940 DEIA LN SW2 L1410 ALU	SP532P

Order Code	Full Product Name	Product family code
97247600	SP532P 36S/940 DEIA LN SW2 L1130 ALU	SP532P
97315200	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	SP532P
97316900	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	SP533P
97257500	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	SP532P
97232200	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	SP530P
97263600	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	SP532P


## Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103202




Polar Normal (separate) - SM530CI - 910505103257




Polar Normal (separate) - SM530CI - 910505103162




Polar Normal (separate) - SM530CI - 910505103262




Polar Normal (separate) - SM530CI - 910505103197




Polar Normal (separate) - SM530CI - 910505103203



Polar Normal (separate) - SM530CI - 910505103205




Polar Normal (separate) - SM530CI - 910505103214




Polar Normal (separate) - SM530CI - 910505103249


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103283




Polar Normal (separate) - SM530CI - 910505103189




Polar Normal (separate) - SM530CI - 910505103248




Polar Normal (separate) - SM530CI - 910505103207




Polar Normal (separate) - SM530CI - 910505103183




Polar Normal (separate) - SM530CI - 910505103206



Polar Normal (separate) - SM530CI - 910505103247




Polar Normal (separate) - SM530CI - 910505103180




Polar Normal (separate) - SM530CI - 910505103273


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103161




Polar Normal (separate) - SM530CI - 910505103201




Polar Normal (separate) - SM530CI - 910505103263




Polar Normal (separate) - SM530CI - 910505103212




Polar Normal (separate) - SM530CI - 910505103172




Polar Normal (separate) - SM530CI - 910505103208



Polar Normal (separate) - SM530CI - 910505103246




Polar Normal (separate) - SM530CI - 910505103177




Polar Normal (separate) - SM530CI - 910505103174


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103245




Polar Normal (separate) - SM530CI - 910505103279




Polar Normal (separate) - SM530CI - 910505103199




Polar Normal (separate) - SM530CI - 910505103261




Polar Normal (separate) - SM530CI - 910505103274




Polar Normal (separate) - SM530CI - 910505103169



Polar Normal (separate) - SM530CI - 910505103166




Polar Normal (separate) - SM530CI - 910505103184




Polar Normal (separate) - SM530CI - 910505103216


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103271




Polar Normal (separate) - SM530CI - 910505103280




Polar Normal (separate) - SM530CI - 910505103210




Polar Normal (separate) - SM530CI - 910505103211




Polar Normal (separate) - SM530CI - 910505103256




Polar Normal (separate) - SM530CI - 910505103281



Polar Normal (separate) - SM530CI - 910505103244




Polar Normal (separate) - SM530CI - 910505103173




Polar Normal (separate) - SM530CI - 910505103258


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103259




Polar Normal (separate) - SM530CI - 910505103182




Polar Normal (separate) - SM530CI - 910505103196




Polar Normal (separate) - SM530CI - 910505103209




Polar Normal (separate) - SM530CI - 910505103188




Polar Normal (separate) - SM530CI - 910505103186



Polar Normal (separate) - SM530CI - 910505103215




Polar Normal (separate) - SM530CI - 910505103187




Polar Normal (separate) - SM530CI - 910505103163


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103204




Polar Normal (separate) - SM530CI - 910505103185




Polar Normal (separate) - SM530CI - 910505103176




Polar Normal (separate) - SM530CI - 910505103260




Polar Normal (separate) - SM530CI - 910505103269




Polar Normal (separate) - SM530CI - 910505103282



Polar Normal (separate) - SM530CI - 910505103164




Polar Normal (separate) - SM530CI - 910505103167




Polar Normal (separate) - SM530CI - 910505103168


## Polar Wide Diagrams




**Polar Normal (separate) - SM530CI - 910505103170**




**Polar Normal (separate) - SM530CI - 910505103171**




**Polar Normal (separate) - SM530CI - 910505103181**




**Polar Normal (separate) - SM530CI - 910505103175**




**Polar Normal (separate) - SM530CI - 910505103198**



**Polar Normal (separate) - SM530CI - 910505103213**



**Polar Normal (separate) - SM530CI - 910505103270**



**Polar Normal (separate) - SM530CI - 910505103272**

TrueLine, suspended



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)

2025, December 13 - data subject to change