

TrueLine, suspended

SP530P



Philips TrueLine suspended: True line of light

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

Applications

- Offices
- Education
- Retail

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering


- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories
- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

Versions



TrueLine suspended-SP530P
SP532P L1130 ALU

Dimensional drawing



SP532P 49S/940 DEIA SM2 L1130 ALU

Product details



TrueLine_Suspended-line-
side-view



TrueLine_Suspended-line-top-
view



TrueLine_Suspended-top-view



TrueLine_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine_SM_SP-line-connectio-side-view-2

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]

Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	4,900 lm	143 lm/W
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	4,000 lm	140 lm/W


Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	36.5 W
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	28.5 W

Product Data

Order Code	Full Product Name	Product family code
910505106166	SP532P 49S/940 DEIA SM2 L1130 ALU	SP532P
910505106173	SP530P 40S/940 DEIA SM2 L1130 ALU	SP530P

Polar normal diagrams



SP530PI - 910505106166

SP530PI - 910505106173

