



A small and sustainable projector in a sleek, subtle design

GreenSpace Evo Mini Semi Recessed

GreenSpace Evo Mini Semi Recessed is a sustainable lighting projector for recessed installation that comes with a sleek and subtle design. This makes the projector an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini Semi Recessed a sustainable projector choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customization of cutout dimensions, colors and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Semi Recessed

Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove


Versions

ST332B GreenSpace Evo Mini
Semi-recessed - black - cutout 68



Dimensional drawing

Type	A (mm)	B (mm)	C (mm)	Cutout (mm)
RD68	68	78	126	68
RD125	125	135	183	125



GreenSpace Evo Mini Semi Recessed

Product details



ST332B GreenSpace Evo Mini
Semi-recessed - white - cutout 68



ST332B GreenSpace Evo Mini
Semi-recessed - black - cutout 125



ST332B GreenSpace Evo Mini
Semi-recessed - black - cutout 68



ST332B GreenSpace Evo Mini
Semi-recessed - white - cutout 125

GreenSpace Evo Mini Semi Recessed

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Emergency Operation	
Central Emergency	No
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated				Optic type
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux		
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	3000 K	109 lm/W	1,200 lm	High-reflective metal reflector Narrow beam 10 to 20 degrees	
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	4000 K	136 lm/W	1,700 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	3000 K	128 lm/W	1,100 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	3000 K	124 lm/W	2,500 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	4000 K	128 lm/W	2,600 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	3000 K	109 lm/W	1,200 lm	High-reflective metal reflector Narrow beam 10 to 20 degrees	
910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	4000 K	136 lm/W	1,700 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	3000 K	128 lm/W	1,100 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	3000 K	124 lm/W	2,500 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	
910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	4000 K	128 lm/W	2,600 lm	High-reflective metal reflector Medium beam 20 to 40 degrees	

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	10.7 W	910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	10.7 W
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	12.1 W	910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	12.1 W
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	8.6 W	910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	8.6 W
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	20.1 W	910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	20.1 W
910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	20.1 W	910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	20.1 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	No	910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	No
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	Yes	910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	No
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	No	910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	Yes
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	No	910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	No

GreenSpace Evo Mini Semi Recessed

Order Code	Full Product Name	Dimmable
910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	No

Order Code	Full Product Name	Dimmable
910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	Black
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	Black
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	White
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	White
910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	White

Order Code	Full Product Name	Housing Color
910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	Black
910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	Black
910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	White
910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	White
910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	(0.422,0.386)
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	(0.374,0.364)
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	(0.422,0.386)
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	(0.422,0.386)
910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	(0.374,0.364)




Order Code	Full Product Name	Initial chromaticity
910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	(0.422,0.386)
910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	(0.374,0.364)
910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	(0.422,0.386)
910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	(0.422,0.386)
910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	(0.374,0.364)

Product Data

Order Code	Full Product Name	Product family code
910505104627	ST332B 12S/PC930 PSU-E HNB BK482 68	-
910505104628	ST332B 17S/PW940 DIA-E HWB BK482 68	ST332B
910505104626	ST332B 12S/PW930 PSU-E HMB WH481 68	ST332B
910505104629	ST332B 27S/PW930 PSU-E HMB WH481 68	-
910505104630	ST332B 27S/PW940 PSU-E HMB WH481 68	-

Order Code	Full Product Name	Product family code
910505104632	ST332B 12S/PC930 PSU-E HNB BK482 125	-
910505104633	ST332B 17S/PW940 DIA-E HWB BK482 125	ST332B
910505104631	ST332B 12S/PW930 PSU-E HMB WH481 125	ST332B
910505104634	ST332B 27S/PW930 PSU-E HMB WH481 125	-
910505104635	ST332B 27S/PW940 PSU-E HMB WH481125	-

Polar Wide Diagrams




Polar Normal (separate) - ST332BI -
910505104628

Polar Normal (separate) - ST332BI -
910505104626


Polar Normal (separate) - ST332BI -
910505104633

GreenSpace Evo Mini Semi Recessed


Polar Wide Diagrams




Polar Normal (separate) - ST332BI - 910505104632




Polar Normal (separate) - ST332BI - 910505104631




Polar Normal (separate) - ST332BI - 910505104629




Polar Normal (separate) - ST332BI - 910505104630



Polar Normal (separate) - ST332BI - 910505104635



Polar Normal (separate) - ST332BI - 910505104627



Polar Normal (separate) - ST332BI - 910505104634

GreenSpace Evo Mini Semi Recessed

