



# A small and sustainable projector in a sleek, subtle design

## GreenSpace Evo Mini

GreenSpace Evo Mini is a sustainable lighting projector that comes with a sleek and subtle design. This makes the projector an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini a sustainable projector choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customisation of colours and textures is possible via Philips MyCreation

### Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

# GreenSpace Evo Mini

## Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Very broad aiming flexibility, including upward lighting
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

## Application

- Fashion
- Hospitality
- Residential

## Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

## Versions



ST332T GreenSpace Evo Mini  
black



ST332X2 GreenSpace Evo Mini  
double spothead for Coreline  
trunking, white






ST332T GreenSpace Evo Mini  
white



ST332X2 GreenSpace Evo Mini  
double spothead for Maxos fusion,  
white

# GreenSpace Evo Mini

## Dimensional drawing



## Product details



GreenSpace Evo Mini is fully serviceable



ST332T GreenSpace Evo Mini white



ST332T GreenSpace Evo Mini black

# GreenSpace Evo Mini

## General Information

Driver included	Yes
<b>Light Technical</b>	
Optic type	High-reflective metal reflector Medium beam 20 to 40 degrees
<b>Operating and Electrical</b>	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
<b>Mechanical and Housing</b>	
Mech. impact protection code	IK02
Ingress protection code	IP20
<b>Emergency Operation</b>	
Central Emergency	No
<b>Approval and Application</b>	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Number of gear units	Service Tag
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	Unit	Yes
910505104527	ST332T 27S/PW930 PSU HWB BK482	Unit	Yes
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	2 units	-
910505104525	ST332T 27S/830 PSU HWB WH481	Unit	Yes
910505104529	ST332T 27S/PW930 WIA HMB WH481	Unit	Yes
910505104532	ST332X2 27S/PW940 PSU HWB WH481	2 units	-

## Light Technical

Order Code	Full Product Name	Correlated Colour		Luminous efficacy (rated) (nom.)	Luminous Flux
		Temperature (Nom)	rendering index (CRI)		
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	3000 K	>90	118 lm/W	2,200 lm
910505104527	ST332T 27S/PW930 PSU HWB BK482	3000 K	>90	121 lm/W	2,700 lm
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	3000 K	>90	121 lm/W	5,400 lm

Order Code	Full Product Name	Correlated Colour		Luminous efficacy (rated) (nom.)	Luminous Flux
		Temperature (Nom)	rendering index (CRI)		
910505104525	ST332T 27S/830 PSU HWB WH481	3000 K	>80	126 lm/W	2,800 lm
910505104529	ST332T 27S/PW930 WIA HMB WH481	3000 K	>90	112 lm/W	2,700 lm
910505104532	ST332X2 27S/PW940 PSU HWB WH481	4000 K	>90	124 lm/W	5,600 lm

## Operating and Electrical

# GreenSpace Evo Mini

Order Code	Full Product Name	Power Consumption
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	18.8 W
910505104527	ST332T 27S/PW930 PSU HWB BK482	20.7 W
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	44.6 W

Order Code	Full Product Name	Power Consumption
910505104525	ST332T 27S/830 PSU HWB WH481	20.7 W
910505104529	ST332T 27S/PW930 WIA HMB WH481	24 W
910505104532	ST332X2 27S/PW940 PSU HWB WH481	44.6 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	No
910505104527	ST332T 27S/PW930 PSU HWB BK482	No
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	No

Order Code	Full Product Name	Dimmable
910505104525	ST332T 27S/830 PSU HWB WH481	No
910505104529	ST332T 27S/PW930 WIA HMB WH481	Yes
910505104532	ST332X2 27S/PW940 PSU HWB WH481	No

## Mechanical and Housing

Order Code	Full Product Name	Housing Colour
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	Black
910505104527	ST332T 27S/PW930 PSU HWB BK482	Black
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	White

Order Code	Full Product Name	Housing Colour
910505104525	ST332T 27S/830 PSU HWB WH481	White
910505104529	ST332T 27S/PW930 WIA HMB WH481	White
910505104532	ST332X2 27S/PW940 PSU HWB WH481	White

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	(0.422, 0.386) SDCM <2
910505104527	ST332T 27S/PW930 PSU HWB BK482	(0.422, 0.386) SDCM <2
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	(0.422, 0.386) SDCM <2




Order Code	Full Product Name	Initial chromaticity
910505104525	ST332T 27S/830 PSU HWB WH481	(0.434, 0.403) SDCM <3
910505104529	ST332T 27S/PW930 WIA HMB WH481	(0.422, 0.386) SDCM <2
910505104532	ST332X2 27S/PW940 PSU HWB WH481	(0.374, 0.364) SDCM <2

## Product Data

Order Code	Full Product Name	Product family code
910505104524	ST332T 22S/PC930 PSU HMB FG BK482	ST332T
910505104527	ST332T 27S/PW930 PSU HWB BK482	ST332T
910505104535	ST332Y2 27S/PW930 PSU HWB WH481	ST332Y2

Order Code	Full Product Name	Product family code
910505104525	ST332T 27S/830 PSU HWB WH481	ST332T
910505104529	ST332T 27S/PW930 WIA HMB WH481	ST332T
910505104532	ST332X2 27S/PW940 PSU HWB WH481	ST332X2

## Polar Wide Diagrams




Polar Normal (separate) - ST332TI -  
910505104529


Polar Normal (separate) - ST332TI -  
910505104527

Polar Normal (separate) - ST332TI -  
910505104525


## Polar Wide Diagrams



**Polar Normal (separate) - ST332TI - 910505104524**



**Polar Normal (separate) - ST332TI - 910505104535**



**Polar Normal (separate) - ST332TI - 910505104532**

