



Elegant outlook design projector for the retail segment

Truefashion Projector GCGM

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Benefits

- Slim and compact outlook design with inside track driver.
- Excellent light quality of punch effect.
- Dedicated light recipe for fashion and food.
- System connectivity with Dali-VLC.

Features

- Lumen packages (1000/2000/3000/4000lm).
- 3 beams options (NB/MB/WB).
- Dali-VLC Control.
- Track version available in 1C, 3C.
- CB, EMC, CCC, ACC.
- Lifetime 50K Hours.

Application

- Retail fashion store
- Shopping mall
- Food & large retail

Warnings and Safety

- 3 years

Truefashion Projector GCGM

Specifications

Type	ST700T: Tracklight
	RS700B: recessed round
	GD700B: recessed square
Mounting type	Track installation
	Recessed
Operating Temperature range	-15 to +35°C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Dimming	PSD: Dimmable via Dali protocol
Control system input	DALI
Material	Housing: die-cast aluminum
Main color of the luminaire	White RAL9003 / Black RAL9011
Lumen maintenance at median useful life	L70 50.000h

Luminous flux	1000lm - 4000lm
Power consumption	8.2W - 40.3W
Correlated color temperature - CCT	3000K,4000K,Premium White, Premium Color
Color Rendering index - CRI	80/90
Beam angle	VNB(Very Narrow Beam): 11° NB (Narrow Beam): 13-19° MB (Medium Beam): 23-24° WB (Wide Beam): 30-34°
Protection Class	Class II
IEC61140	
Ingress protection	IP20
Installation	Track Recessed

Versions



RS700B LED10 LED20 BK



GD700B 1 head WH





GD700B 2 heads WH









GD700B 2 heads BK

Dimensional drawing



Truefashion Projector GCGM

Dimensional drawing



Truefashion Projector GCGM

General Information	
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Mech. impact protection code	-
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
ENEC mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Driver included	Light source replaceable	Number of gear units
01520171	RS700B LED20 930PW PSU NB BK	-	-	-
52115500	GD700B LED10 830 PSU MB WH	-	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-	-
01518471	GD700B LED10 830 PSU MB BK	-	-	-
73101100	GD700B LED20 930PW PSU MB BK	-	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-	-
01522171	RS700B LED40 930PC PSU MB WH	-	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	Yes	No	1 unit
01546761	ST700T LED20 930PC PSU MB 1C WH	Yes	No	1 unit
01546861	ST700T LED20 930PC PSU WB 1C WH	Yes	No	1 unit
01547061	ST700T LED20 930PC PSU MB 1C BK	Yes	No	1 unit
01547261	ST700T LED30 930PC PSU MB 1C WH	Yes	No	1 unit
01547361	ST700T LED30 930PC PSU WB 1C WH	Yes	No	1 unit
01547461	ST700T LED30 930PC PSU MB 1C BK	Yes	No	1 unit
01547661	ST700T LED40 930PC PSU MB 1C WH	Yes	No	1 unit
01547761	ST700T LED40 930PC PSU WB 1C WH	Yes	No	1 unit
01547861	ST700T LED40 930PC PSU MB 1C BK	Yes	No	1 unit
01561761	ST700T LED10 830 PSU WB 1C WH	Yes	No	1 unit
01561961	ST700T LED10 830 PSU WB 1C BK	Yes	No	1 unit
01562161	ST700T LED20 830 PSU WB 1C WH	Yes	No	1 unit
52111700	GD700B 2XLED10 830 PSU MB WH	-	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-	-
51947300	GD700B 2XLED10 830 PSU MB BK	-	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01520171	RS700B LED20 930PW PSU NB BK	-	3000 K	>90	79 lm/W
52115500	GD700B LED10 830 PSU MB WH	-	3000 K	>80	115 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01518571	GD700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W
01530571	GD700B LED20 940PW PSU MB WH HB	-	4000 K	>90	56 lm/W

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01575561	ST700T LED30 930PW PSU MB 3C BK	-	3000 K	>90	94 lm/W
01576061	ST700T LED30 930PW PSD VLC WB BK	-	3000 K	>90	91 lm/W
01576261	ST700T LED30 930PW PSD VLC WB WH	-	3000 K	>90	91 lm/W
01518471	GD700B LED10 830 PSU MB BK	-	3000 K	>80	115 lm/W
73101100	GD700B LED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W
01520771	RS700B LED30 930PW PSU MB WH	-	3000 K	>90	92 lm/W
01520871	RS700B LED30 930PW PSU WB WH	-	3000 K	>90	91 lm/W
01520971	RS700B LED30 940PW PSU MB WH	-	4000 K	>90	100 lm/W
01521471	RS700B LED30 930PC PSU MB WH	-	3000 K	>90	87 lm/W
01521771	RS700B LED40 940PW PSU MB WH	-	4000 K	>90	100 lm/W
01522171	RS700B LED40 930PC PSU MB WH	-	3000 K	>90	85 lm/W
01519471	RS700B LED10 830 PSU MB WH	-	3000 K	>80	114 lm/W
01519571	RS700B LED10 830 PSU WB WH	-	3000 K	>80	108 lm/W
01519871	RS700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W
01519971	RS700B LED20 930PW PSU WB WH	-	3000 K	>90	75 lm/W
01520071	RS700B LED20 940PW PSU MB WH	-	4000 K	>90	86 lm/W
01546661	ST700T LED20 930PC PSU NB 1C WH	120 degree(s)	3000 K	>90	76 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01546761	ST700T LED20 930PC PSU MB 1C WH	120 degree(s)	3000 K	>90	76 lm/W
01546861	ST700T LED20 930PC PSU WB 1C WH	120 degree(s)	3000 K	>90	72 lm/W
01547061	ST700T LED20 930PC PSU MB 1C BK	120 degree(s)	3000 K	>90	76 lm/W
01547261	ST700T LED30 930PC PSU MB 1C WH	120 degree(s)	3000 K	>90	83 lm/W
01547361	ST700T LED30 930PC PSU WB 1C WH	120 degree(s)	3000 K	>90	82 lm/W
01547461	ST700T LED30 930PC PSU MB 1C BK	120 degree(s)	3000 K	>90	83 lm/W
01547661	ST700T LED40 930PC PSU MB 1C WH	120 degree(s)	3000 K	>90	83 lm/W
01547761	ST700T LED40 930PC PSU WB 1C WH	120 degree(s)	3000 K	>90	80 lm/W
01547861	ST700T LED40 930PC PSU MB 1C BK	120 degree(s)	3000 K	>90	83 lm/W
01561761	ST700T LED10 830 PSU WB 1C WH	120 degree(s)	3000 K	>80	107 lm/W
01561961	ST700T LED10 830 PSU WB 1C BK	120 degree(s)	3000 K	>80	107 lm/W
01562161	ST700T LED20 830 PSU WB 1C WH	120 degree(s)	3000 K	>80	92 lm/W
52111700	GD700B 2XLED10 830 PSU MB WH	-	3000 K	>80	114 lm/W
01518971	GD700B 2XLED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W
51947300	GD700B 2XLED10 830 PSU MB BK	-	3000 K	>80	114 lm/W

Light Technical (2/2)

Truefashion Projector GCGM

Order Code	Full Product Name	Luminous Flux	Optic type
01520171	RS700B LED20 930PW PSU NB BK	1,685 lm	-
52115500	GD700B LED10 830 PSU MB WH	942 lm	-
01518571	GD700B LED20 930PW PSU MB WH	1,685 lm	-
01530571	GD700B LED20 940PW PSU MB WH HB	1,184 lm	-
01575561	ST700T LED30 930PW PSU MB 3C BK	3,294 lm	-
01576061	ST700T LED30 930PW PSD VLC WB BK	3,168 lm	-
01576261	ST700T LED30 930PW PSD VLC WB WH	3,168 lm	-
01518471	GD700B LED10 830 PSU MB BK	942 lm	-
73101100	GD700B LED20 930PW PSU MB BK	1,685 lm	-
01520771	RS700B LED30 930PW PSU MB WH	2,844 lm	-
01520871	RS700B LED30 930PW PSU WB WH	2,809 lm	-
01520971	RS700B LED30 940PW PSU MB WH	3,076 lm	-
01521471	RS700B LED30 930PC PSU MB WH	2,669 lm	-
01521771	RS700B LED40 940PW PSU MB WH	4,025 lm	-
01522171	RS700B LED40 930PC PSU MB WH	3,429 lm	-
01519471	RS700B LED10 830 PSU MB WH	942 lm	-
01519571	RS700B LED10 830 PSU WB WH	886 lm	-
01519871	RS700B LED20 930PW PSU MB WH	1,685 lm	-

Order Code	Full Product Name	Luminous Flux	Optic type
01519971	RS700B LED20 930PW PSU WB WH	1,586 lm	-
01520071	RS700B LED20 940PW PSU MB WH	1,829 lm	-
01546661	ST700T LED20 930PC PSU NB 1C WH	1,605 lm	Beam angle 15°
01546761	ST700T LED20 930PC PSU MB 1C WH	1,605 lm	Beam angle 24°
01546861	ST700T LED20 930PC PSU WB 1C WH	1,510 lm	Beam angle 30°
01547061	ST700T LED20 930PC PSU MB 1C BK	1,605 lm	Beam angle 24°
01547261	ST700T LED30 930PC PSU MB 1C WH	2,939 lm	Beam angle 23°
01547361	ST700T LED30 930PC PSU WB 1C WH	2,902 lm	Beam angle 33°
01547461	ST700T LED30 930PC PSU MB 1C BK	2,939 lm	Beam angle 23°
01547661	ST700T LED40 930PC PSU MB 1C WH	3,429 lm	Beam angle 24°
01547761	ST700T LED40 930PC PSU WB 1C WH	3,299 lm	Beam angle 34°
01547861	ST700T LED40 930PC PSU MB 1C BK	3,429 lm	Beam angle 24°
01561761	ST700T LED10 830 PSU WB 1C WH	1,079 lm	Beam angle 30°
01561961	ST700T LED10 830 PSU WB 1C BK	1,079 lm	Beam angle 30°
01562161	ST700T LED20 830 PSU WB 1C WH	1,930 lm	Beam angle 30°
52111700	GD700B 2XLED10 830 PSU MB WH	1,884 lm	-
01518971	GD700B 2XLED20 930PW PSU MB WH	3,369 lm	-
51947300	GD700B 2XLED10 830 PSU MB BK	1,884 lm	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
01520171	RS700B LED20 930PW PSU NB BK	21.2 W	-
52115500	GD700B LED10 830 PSU MB WH	8.2 W	-
01518571	GD700B LED20 930PW PSU MB WH	21.2 W	-
01530571	GD700B LED20 940PW PSU MB WH HB	21.2 W	-
01575561	ST700T LED30 930PW PSU MB 3C BK	35 W	-
01576061	ST700T LED30 930PW PSD VLC WB BK	35 W	-
01576261	ST700T LED30 930PW PSD VLC WB WH	35 W	-
01518471	GD700B LED10 830 PSU MB BK	8.2 W	-
73101100	GD700B LED20 930PW PSU MB BK	21.2 W	-
01520771	RS700B LED30 930PW PSU MB WH	30.8 W	-
01520871	RS700B LED30 930PW PSU WB WH	30.8 W	-
01520971	RS700B LED30 940PW PSU MB WH	30.8 W	-
01521471	RS700B LED30 930PC PSU MB WH	30.8 W	-
01521771	RS700B LED40 940PW PSU MB WH	40.3 W	-
01522171	RS700B LED40 930PC PSU MB WH	40.3 W	-
01519471	RS700B LED10 830 PSU MB WH	8.2 W	-
01519571	RS700B LED10 830 PSU WB WH	8.2 W	-
01519871	RS700B LED20 930PW PSU MB WH	21.2 W	-
01519971	RS700B LED20 930PW PSU WB WH	21.2 W	-
01520071	RS700B LED20 940PW PSU MB WH	21.2 W	-
01546661	ST700T LED20 930PC PSU NB 1C WH	21 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
01546761	ST700T LED20 930PC PSU MB 1C WH	21 W	No
01546861	ST700T LED20 930PC PSU WB 1C WH	21 W	No
01547061	ST700T LED20 930PC PSU MB 1C BK	21 W	No
01547261	ST700T LED30 930PC PSU MB 1C WH	35.4 W	No
01547361	ST700T LED30 930PC PSU WB 1C WH	35.4 W	No
01547461	ST700T LED30 930PC PSU MB 1C BK	35.4 W	No
01547661	ST700T LED40 930PC PSU MB 1C WH	41.2 W	No
01547761	ST700T LED40 930PC PSU WB 1C WH	41.2 W	No
01547861	ST700T LED40 930PC PSU MB 1C BK	41.2 W	No
01561761	ST700T LED10 830 PSU WB 1C WH	10.1 W	No
01561961	ST700T LED10 830 PSU WB 1C BK	10.1 W	No
01562161	ST700T LED20 830 PSU WB 1C WH	21 W	No
52111700	GD700B 2XLED10 830 PSU MB WH	16.5 W	-
01518971	GD700B 2XLED20 930PW PSU MB WH	42.4 W	-
51947300	GD700B 2XLED10 830 PSU MB BK	16.5 W	-

Controls and Dimming

Truefashion Projector GCGM

Order Code	Full Product Name	Maximum dim level
01520171	RS700B LED20 930PW PSU NB BK	-
52115500	GD700B LED10 830 PSU MB WH	-
01518571	GD700B LED20 930PW PSU MB WH	-
01530571	GD700B LED20 940PW PSU MB WH HB	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-
01518471	GD700B LED10 830 PSU MB BK	-
73101100	GD700B LED20 930PW PSU MB BK	-
01520771	RS700B LED30 930PW PSU MB WH	-
01520871	RS700B LED30 930PW PSU WB WH	-
01520971	RS700B LED30 940PW PSU MB WH	-
01521471	RS700B LED30 930PC PSU MB WH	-
01521771	RS700B LED40 940PW PSU MB WH	-
01522171	RS700B LED40 930PC PSU MB WH	-
01519471	RS700B LED10 830 PSU MB WH	-
01519571	RS700B LED10 830 PSU WB WH	-
01519871	RS700B LED20 930PW PSU MB WH	-

Order Code	Full Product Name	Maximum dim level
01519971	RS700B LED20 930PW PSU WB WH	-
01520071	RS700B LED20 940PW PSU MB WH	-
01546661	ST700T LED20 930PC PSU NB 1C WH	Not applicable
01546761	ST700T LED20 930PC PSU MB 1C WH	Not applicable
01546861	ST700T LED20 930PC PSU WB 1C WH	Not applicable
01547061	ST700T LED20 930PC PSU MB 1C BK	Not applicable
01547261	ST700T LED30 930PC PSU MB 1C WH	Not applicable
01547361	ST700T LED30 930PC PSU WB 1C WH	Not applicable
01547461	ST700T LED30 930PC PSU MB 1C BK	Not applicable
01547661	ST700T LED40 930PC PSU MB 1C WH	Not applicable
01547761	ST700T LED40 930PC PSU WB 1C WH	Not applicable
01547861	ST700T LED40 930PC PSU MB 1C BK	Not applicable
01561761	ST700T LED10 830 PSU WB 1C WH	Not applicable
01561961	ST700T LED10 830 PSU WB 1C BK	Not applicable
01562161	ST700T LED20 830 PSU WB 1C WH	Not applicable
52111700	GD700B 2XLED10 830 PSU MB WH	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-
51947300	GD700B 2XLED10 830 PSU MB BK	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover	
		type	Housing Color
01520171	RS700B LED20 930PW PSU NB BK	Lens	Black
52115500	GD700B LED10 830 PSU MB WH	Lens	White RAL 9003
01518571	GD700B LED20 930PW PSU MB WH	Lens	White RAL 9003
01530571	GD700B LED20 940PW PSU MB WH HB	Lens	White RAL 9003
01575561	ST700T LED30 930PW PSU MB 3C BK	Fashion proof optic beam angle 24°	White and black
01576061	ST700T LED30 930PW PSD VLC WB BK	Fashion proof optic beam angle 36°	White and black
01576261	ST700T LED30 930PW PSD VLC WB WH	Fashion proof optic beam angle 36°	White and black
01518471	GD700B LED10 830 PSU MB BK	Lens	Black
73101100	GD700B LED20 930PW PSU MB BK	Lens	Black
01520771	RS700B LED30 930PW PSU MB WH	Lens	White RAL 9003
01520871	RS700B LED30 930PW PSU WB WH	Lens	White RAL 9003
01520971	RS700B LED30 940PW PSU MB WH	Lens	White RAL 9003
01521471	RS700B LED30 930PC PSU MB WH	Lens	White RAL 9003
01521771	RS700B LED40 940PW PSU MB WH	Lens	White RAL 9003
01522171	RS700B LED40 930PC PSU MB WH	Lens	White RAL 9003

Order Code	Full Product Name	Optical cover	
		type	Housing Color
01519471	RS700B LED10 830 PSU MB WH	Lens	White RAL 9003
01519571	RS700B LED10 830 PSU WB WH	Lens	White RAL 9003
01519871	RS700B LED20 930PW PSU MB WH	Lens	White RAL 9003
01519971	RS700B LED20 930PW PSU WB WH	Lens	White RAL 9003
01520071	RS700B LED20 940PW PSU MB WH	Lens	White RAL 9003
01546661	ST700T LED20 930PC PSU NB 1C WH	Lens	White
01546761	ST700T LED20 930PC PSU MB 1C WH	Lens	White
01546861	ST700T LED20 930PC PSU WB 1C WH	Lens	White
01547061	ST700T LED20 930PC PSU MB 1C BK	Lens	Black
01547261	ST700T LED30 930PC PSU MB 1C WH	Lens	White
01547361	ST700T LED30 930PC PSU WB 1C WH	Lens	White
01547461	ST700T LED30 930PC PSU MB 1C BK	Lens	Black
01547661	ST700T LED40 930PC PSU MB 1C WH	Lens	White
01547761	ST700T LED40 930PC PSU WB 1C WH	Lens	White
01547861	ST700T LED40 930PC PSU MB 1C BK	Lens	Black
01561761	ST700T LED10 830 PSU WB 1C WH	Lens	White
01561961	ST700T LED10 830 PSU WB 1C BK	Lens	Black
01562161	ST700T LED20 830 PSU WB 1C WH	Lens	White
52111700	GD700B 2XLED10 830 PSU MB WH	Lens	White RAL 9003
01518971	GD700B 2XLED20 930PW PSU MB WH	Lens	White RAL 9003
51947300	GD700B 2XLED10 830 PSU MB BK	Lens	Black

Approval and Application

Order Code	Full Product Name	Ambient temperature range
01520171	RS700B LED20 930PW PSU NB BK	-15 to +35 °C
52115500	GD700B LED10 830 PSU MB WH	-15 to +35 °C
01518571	GD700B LED20 930PW PSU MB WH	-15 to +35 °C

Order Code	Full Product Name	Ambient temperature range
01530571	GD700B LED20 940PW PSU MB WH HB	-15 to +35 °C
01575561	ST700T LED30 930PW PSU MB 3C BK	-20 to +35 °C
01576061	ST700T LED30 930PW PSD VLC WB BK	-20 to +35 °C

Truefashion Projector GCGM

Order Code	Full Product Name	Ambient temperature range
01576261	ST700T LED30 930PW PSD VLC WB WH	-20 to +35 °C
01518471	GD700B LED10 830 PSU MB BK	-15 to +35 °C
73101100	GD700B LED20 930PW PSU MB BK	-15 to +35 °C
01520771	RS700B LED30 930PW PSU MB WH	-15 to +35 °C
01520871	RS700B LED30 930PW PSU WB WH	-15 to +35 °C
01520971	RS700B LED30 940PW PSU MB WH	-15 to +35 °C
01521471	RS700B LED30 930PC PSU MB WH	-15 to +35 °C
01521771	RS700B LED40 940PW PSU MB WH	-15 to +35 °C
01522171	RS700B LED40 930PC PSU MB WH	-15 to +35 °C
01519471	RS700B LED10 830 PSU MB WH	-15 to +35 °C
01519571	RS700B LED10 830 PSU WB WH	-15 to +35 °C
01519871	RS700B LED20 930PW PSU MB WH	-15 to +35 °C
01519971	RS700B LED20 930PW PSU WB WH	-15 to +35 °C
01520071	RS700B LED20 940PW PSU MB WH	-15 to +35 °C
01546661	ST700T LED20 930PC PSU NB 1C WH	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
01546761	ST700T LED20 930PC PSU MB 1C WH	-20 to +35 °C
01546861	ST700T LED20 930PC PSU WB 1C WH	-20 to +35 °C
01547061	ST700T LED20 930PC PSU MB 1C BK	-20 to +35 °C
01547261	ST700T LED30 930PC PSU MB 1C WH	-20 to +35 °C
01547361	ST700T LED30 930PC PSU WB 1C WH	-20 to +35 °C
01547461	ST700T LED30 930PC PSU MB 1C BK	-20 to +35 °C
01547661	ST700T LED40 930PC PSU MB 1C WH	-20 to +35 °C
01547761	ST700T LED40 930PC PSU WB 1C WH	-20 to +35 °C
01547861	ST700T LED40 930PC PSU MB 1C BK	-20 to +35 °C
01561761	ST700T LED10 830 PSU WB 1C WH	-20 to +35 °C
01561961	ST700T LED10 830 PSU WB 1C BK	-20 to +35 °C
01562161	ST700T LED20 830 PSU WB 1C WH	-20 to +35 °C
52111700	GD700B 2XLED10 830 PSU MB WH	-15 to +35 °C
01518971	GD700B 2XLED20 930PW PSU MB WH	-15 to +35 °C
51947300	GD700B 2XLED10 830 PSU MB BK	-15 to +35 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01520171	RS700B LED20 930PW PSU NB BK	-
52115500	GD700B LED10 830 PSU MB WH	-
01518571	GD700B LED20 930PW PSU MB WH	-
01530571	GD700B LED20 940PW PSU MB WH HB	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-
01518471	GD700B LED10 830 PSU MB BK	-
73101100	GD700B LED20 930PW PSU MB BK	-
01520771	RS700B LED30 930PW PSU MB WH	-
01520871	RS700B LED30 930PW PSU WB WH	-
01520971	RS700B LED30 940PW PSU MB WH	-
01521471	RS700B LED30 930PC PSU MB WH	-
01521771	RS700B LED40 940PW PSU MB WH	-
01522171	RS700B LED40 930PC PSU MB WH	-
01519471	RS700B LED10 830 PSU MB WH	-
01519571	RS700B LED10 830 PSU WB WH	-
01519871	RS700B LED20 930PW PSU MB WH	-

Order Code	Full Product Name	Initial chromaticity
01519971	RS700B LED20 930PW PSU WB WH	-
01520071	RS700B LED20 940PW PSU MB WH	-
01546661	ST700T LED20 930PC PSU NB 1C WH	(0.422, 0.386) SDCM<3
01546761	ST700T LED20 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01546861	ST700T LED20 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547061	ST700T LED20 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01547261	ST700T LED30 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01547361	ST700T LED30 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547461	ST700T LED30 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01547661	ST700T LED40 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01547761	ST700T LED40 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547861	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01561761	ST700T LED10 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3
01561961	ST700T LED10 830 PSU WB 1C BK	(0.434, 0.403) SDCM<3
01562161	ST700T LED20 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3
52111700	GD700B 2XLED10 830 PSU MB WH	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-
51947300	GD700B 2XLED10 830 PSU MB BK	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver	Median	Median
		failure rate at 5000 h	useful life L80B50	useful life L90B50
01520171	RS700B LED20 930PW PSU NB BK	-	-	-
52115500	GD700B LED10 830 PSU MB WH	-	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-	-

Order Code	Full Product Name	Driver	Median	Median
		failure rate at 5000 h	useful life L80B50	useful life L90B50
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-	-
01518471	GD700B LED10 830 PSU MB BK	-	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
73101100	GD700B LED20 930PW PSU MB BK	-	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-	-
01522171	RS700B LED40 930PC PSU MB WH	-	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01546761	ST700T LED20 930PC PSU MB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
01546861	ST700T LED20 930PC PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01547061	ST700T LED20 930PC PSU MB 1C BK	0.14 %	50,000 hour(s)	32,600 hour(s)
01547261	ST700T LED30 930PC PSU MB 1C WH	0.14 %	45,000 hour(s)	21,200 hour(s)
01547361	ST700T LED30 930PC PSU WB 1C WH	0.14 %	45,000 hour(s)	21,200 hour(s)
01547461	ST700T LED30 930PC PSU MB 1C BK	0.14 %	45,000 hour(s)	21,200 hour(s)
01547661	ST700T LED40 930PC PSU MB 1C WH	0.23 %	38,700 hour(s)	18,200 hour(s)
01547761	ST700T LED40 930PC PSU WB 1C WH	0.23 %	38,700 hour(s)	18,200 hour(s)
01547861	ST700T LED40 930PC PSU MB 1C BK	0.23 %	38,700 hour(s)	18,200 hour(s)
01561761	ST700T LED10 830 PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01561961	ST700T LED10 830 PSU WB 1C BK	0.14 %	50,000 hour(s)	32,600 hour(s)
01562161	ST700T LED20 830 PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
52111700	GD700B 2XLED10 830 PSU MB WH	-	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-	-
51947300	GD700B 2XLED10 830 PSU MB BK	-	-	-

