



StoreFlow: a new concept in high-contrast aisle lighting

StoreFlow

Philips StoreFlow is designed to provide an optimal light effect for shelf lighting or aisle lighting, so retailers can create an appealing ambience in-store. The organic, natural design of the luminaire blends easily into the shop environment, while the indirect PerfectAccent optics avoid glare and support a highly energy-efficient lighting installation. StoreFlow shelf lighting is made using bio-based plastics and offers easy serviceability of the LED, driver and optic, resulting in a low carbon footprint, thus meeting the requirements of a circular product. This high-contrast lighting is available with a single-spot head (ST761T) that's ideal for the peripheral areas of the shop, or as a double-spot head (ST762T) version, which is perfect for aisle lighting.

Benefits

- Optimal light effect for shelves and aisles: eye-level products stand out while the rest of the shelf is evenly lit with no unnecessary light on the floor
- Avoids shopper distraction with PerfectAccent indirect optics to reduce glare
- The compact luminaire design blends easily into store layouts
- StoreFlow can reduce your carbon footprint: the housing is made of bio-based plastics, and easy component replacement and system integration supports circular lighting

StoreFlow

Features

- 340° rotation and +/- 15° tilt (with angle indication) for perfect, consistent light targeting
- Single or double spot head versions to light peripheral areas of the shop as well as general aisles in the centre
- High luminaire efficacy – even with CRI 90 LEDs
- Removable covers for easy maintenance and optic, driver and LED upgrades
- Wireless or DALI-based controls to fine-tune light levels

Application

- Convenience stores
- Supermarkets and hypermarkets
- Large retail formats

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove
- With regards to damage factor, LED luminaires offer an improvement over conventional light sources, but may still cause colour fading because even with no IR or UV in the light beam, light itself is a source of energy. To minimise the risk, avoid light levels over 1000 lx.
- ST761T Storeflow with 1 spothead should always be installed in line with the track if a suspension wire is used. Installation under an angle is only allowed on a track with rigid suspension to avoid tilting the track

Versions



StoreFlow Single Spothead ST761T
in silver







StoreFlow Single Spothead ST761T
in black



StoreFlow Double Spothead
ST762T in silver

StoreFlow

Dimensional drawing



Product details



StoreFlow Single Spothead ST761T
sideview silver



StoreFlow Single Spothead ST761T
frontview silver



StoreFlow Double Spothead
ST762T frontview black



StoreFlow Double Spothead
ST762T sideview silver



StoreFlow Double Spothead
ST762T frontview silver



StoreFlow is easy to service due to
its removable covers

StoreFlow

Product details



StoreFlow Single Spothead ST761T
sideview black



Tilt indications make consistent
aiming of multiple spotheads easy



StoreFlow Single Spothead ST761T
frontview black



StoreFlow Double Spothead
ST762T sideview black

General Information	
Driver included	Yes
Light source replaceable	No
Service Tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Colour rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM)	1
Stroboscopic effect	0.5
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Colour (Nom)	Luminous efficacy (rated) (nom.)	Luminous	
				Flux	Optic type
01434300	ST762T 49S/ PW930 DIA	3000 K	123 lm/W	9,400 lm	Double asymmetric optic
01168700	ST762T 39S/ PW930 DIA	3000 K	128 lm/W	8,200 lm	Double asymmetric optic
01156400	ST761T 39S/ PW930 WIA	3000 K	126 lm/W	4,100 lm	Assymmetric beam angle SI

General Information

Order Code	Full Product Name	Number of gear units
01434300	ST762T 49S/PW930 DIA BK	2 units
01168700	ST762T 39S/PW930 DIA BK	2 units
01156400	ST761T 39S/PW930 WIA SI	Unit
01433600	ST761T 49S/PW930 DIA BK	Unit
01158800	ST761T 49S/PW935 DIA BK	Unit
01169400	ST762T 39S/PW935 WIA SI	2 units

Order	Full Product Code	Temperature (Nom.)	Correlated Colour	Luminous efficacy (rated)	Luminous Flux	Optic type
			Temperature (Nom.)	Luminous efficacy (nom.)	Flux	Optic type
01169400	ST762T 39S/PW935 WIA SI	3500 K	129 lm/W	8,400 lm	Double asymmetric optic	

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01434300	ST762T 49S/PW930 DIA BK	77 W
01168700	ST762T 39S/PW930 DIA BK	64 W
01156400	ST761T 39S/PW930 WIA SI	32.5 W

Order Code	Full Product Name	Power Consumption
01433600	ST761T 49S/PW930 DIA BK	38.5 W
01158800	ST761T 49S/PW935 DIA BK	38.5 W
01169400	ST762T 39S/PW935 WIA SI	65 W

Mechanical and Housing

Order Code	Full Product Name	Housing Colour
01434300	ST762T 49S/PW930 DIA BK	Black
01168700	ST762T 39S/PW930 DIA BK	Black
01156400	ST761T 39S/PW930 WIA SI	Silver

Order Code	Full Product Name	Housing Colour
01433600	ST761T 49S/PW930 DIA BK	Black
01158800	ST761T 49S/PW935 DIA BK	Black
01169400	ST762T 39S/PW935 WIA SI	Silver

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01434300	ST762T 49S/PW930 DIA BK	(0.422,0.386)<2
01168700	ST762T 39S/PW930 DIA BK	(0.422,0.386)<2
01156400	ST761T 39S/PW930 WIA SI	(0.422,0.386)<2


Order Code	Full Product Name	Initial chromaticity
01433600	ST761T 49S/PW930 DIA BK	(0.422,0.386)<2
01158800	ST761T 49S/PW935 DIA BK	(0.398,0.376)<2
01169400	ST762T 39S/PW935 WIA SI	(0.398,0.376)<2

Product Data


Order Code	Full Product Name	Product family code
01434300	ST762T 49S/PW930 DIA BK	ST762T
01168700	ST762T 39S/PW930 DIA BK	ST762T
01156400	ST761T 39S/PW930 WIA SI	ST761T

Order Code	Full Product Name	Product family code
01433600	ST761T 49S/PW930 DIA BK	ST761T
01158800	ST761T 49S/PW935 DIA BK	ST761T
01169400	ST762T 39S/PW935 WIA SI	ST762T


Polar Wide Diagrams



Polar Normal (separate) - ST760TI -
910505102518




Polar Normal (separate) - ST760TI -
910505102414




Polar Normal (separate) - ST760TI -
910505102531


Polar Wide Diagrams



Polar Normal (separate) - ST760TI -
910505102415



Polar Normal (separate) - ST760TI -
910505102530



Polar Normal (separate) - ST760TI -
910505102520

