



# Product Description

## Ecoclick Starters

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

### Benefits

- The only starter that offers fast, easy installation with no need to use any extra tools
- No irritation – even firmly stuck starters can be removed easily
- Eco-friendly, recyclable concept (free of lead and radioactivity)
- More than 25% longer lamp life; lower maintenance costs compared with lower-quality, non-IEC-compliant starters
- Optimal connectivity through brass components and oxidation-resistant brass pins
- Flame-retardant components and UV-resistant canister for additional safety and secure ignition (validated by Underwriters Laboratories UL)

### Features

- Redesigned canister top with two installation notches into which the pins of another starter fit perfectly (patented innovation)
- Radioactive-free (patented) and lead-free (RoHS-compliant)
- Premium reliability with more than 10,000 safe switches
- 2-pin igniter in plastic (flame-retardant polycarbonate) canister with high-quality radio-interference suppression capacitor
- Well-defined preheat and peak voltage ensure proper ignition

## Ecoclick Starters

### Application

- Ignition of fluorescent lamps of all brands with conventional electromagnetic ballasts using TL-D (T8), TL (T12), TL mini and PL-L lamps
- S2 starters are suitable for 110/130 V 4-22 W single applications, 220/240 V 4-6-8-15-18-22 W single applications and 220/240 V 4-22 W series applications. It is recommended for 220/240 V 18 W single applications for optimal performance
- S10 starters are suitable for 220/240 V 13 4-65 W single applications. It is required for 220/240 V 13 W single applications

### Versions




LPPR STARTER PHL 0003



LPPR STARTER PHL 0004

### Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/12X25CT	40.3 mm	21.5 mm
S2 4-22W SER 220-240V WH EUR/12X25CT	40.3 mm	21.5 mm
S2 4-22W SER 220-240V WH EUR/32X25CT	40.3 mm	21.5 mm



## Ecoclick Starters

### Operating and Electrical

Voltage (nom.) 220-240 V

### Mechanical and Housing

Housing Colour White

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
928392220230	S10 4-65W SIN 220-240V WH EUR/12X25CT	4 W
928390720230	S2 4-22W SER 220-240V WH EUR/12X25CT	22 W

Order Code	Full Product Name	Power Consumption
928390720247	S2 4-22W SER 220-240V WH EUR/32X25CT	22 W

