



Product Description

Ecoclick Starters

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Benefits

- The only starter that offers fast, easy installation with no need to use any extra tools
- No irritation – even firmly stuck starters can be removed easily
- Eco-friendly, recyclable concept (free of lead and radioactivity)
- More than 25% longer lamp life; lower maintenance costs compared with lower-quality, non-IEC-compliant starters
- Optimal connectivity through brass components and oxidation-resistant brass pins
- Flame-retardant components and UV-resistant canister for additional safety and secure ignition (validated by Underwriters Laboratories UL)

Features

- Redesigned canister top with 2 installation notches into which the pins of another starter fit perfectly (patented innovation)
- Radioactive-free (patented) and lead-free (RoHS-compliant)
- Premium reliability with 10,000 safe switches
- 2-pin igniter in plastic (flame-retardant polycarbonate) canister with high-quality radio-interference suppression capacitor
- Well-defined preheat and peak voltage ensure proper ignition

Ecoclick Starters

Application


- Ignite fluorescent lamps of all brands with conventional electromagnetic ballast using TL-D (T8), TL (T12), TL mini and PL-L lamps
- S2 Ecoclick starters are suitable for:
 - 110/130V, 4-22W single applications
 - 220/240V, 4-6-8-15-18-22W single applications
 - 220/240V, 4-22W series applications
- S10 Ecoclick starters are suitable for 220/240V, 4-65W single applications
- S10 Ecoclick starter is required for 220/240V, 13W single application
- S2 Ecoclick starter is recommended for 220/240V, 18W single application for optimum performance

Versions



LPPR STARTER PHL 0004

Dimensional drawing



Product	C (max)	E (max)
S2 4-22W SER 220-240V WH Eur/20X25CT	40.3 mm	21.5 mm

