

DRUM

TCKT



DRUM – Illuminate your open ceiling with a versatile and efficient downlight

Bring a new level of sophistication and elegance to your open ceiling. Philips Drum downlights are designed with 3D printing technology and available in multiple installation options, surface-mounted, track-mounted and pendant. Philips Drum has an easy-to-use configurator where end-users can mix and match the options they need. Digitally manufactured light-weight housing provides a distinctive aesthetic to a wide range of applications, making them a perfect fit for any indoor space. High efficiency, perfect color rendering and various light output options, Philips Drum downlights deliver a truly exceptional lighting experience.

Benefits

- Low return of investment years due to high efficiency and long lifetime
- Wide range of mounting options with low weight
- Various light output choices to suit different application need
- Office-compliant, with stable color performance and wide light distribution

Applications

- Offices
- Retail
- Hospitality
- Healthcare

Features


- One size diameter with surface, track mounted and pendant options
- 3D printed parts with at least 55% recycled or mass balanced bio-circular material

- High system efficacy: up to 144 lm/w
- UGR19 version with anti-glare ring
- Available between 1100-3000 lumen to cover various applications
- Various housing colors as a standard part of the configurator
- DALI dimming and wireless driver options available
- IP54 version with a front cover

Versions



Dimensional drawing



TC KT PS 20S/840 PSE WH401 T102

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Luminous Flux	2,279 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	90 degree(s)
Optic type	Beam angle 90°

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Power Consumption	16.5 W
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	No
Embedded control	-

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting

Approval and Application

Glow-wire test	Temperature 750 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM < 5

Product Data

Product family code

TCKTT [Drum]