



## Signify myCreation Smooth Track – Designed to edge out the ordinary

Are you looking for a sustainable, stylish, and functional lighting solution that complements any hospitality & Residential environment? Meet Smooth, the ultimate spotlight that allows you to perfectly match any ambiance. Mix and match color and texture options for the front ring and housing for a unique and luxurious effect. This lighting solution comes in different light recipes to suit your needs and offers a honeycomb accessory for reduced glare and better light distribution. Smooth is an eco-friendly choice, with printed parts made from at least 65% recycled and ISCC Plus-certified bio-circular materials. The heatsink of Smooth is made with 85% recycled aluminum, making it durable and long-lasting. Additionally, due to its circular design, Smooth is upgradeable during its long lifetime.

### Benefits

- Circular design
- Fulfills all accent lighting needs
- Consistent and best in class lighting technology
- Sustainably 3D printed

### Applications

- Fashion Retail
- Retail
- Hospitality
- Offices

## Features

- Rich pallet of housing & front ring colors


- Textured front ring for the luxurious effect
- Various light recipes to choose from - 3000K, 4000K, Premium White, Premium Color

## Versions



Smooth Track -  
TCST65-12S-830-PSU-  
HNB-BK482-BS-T304

## Dimensional drawing



TCST65 12S/830 PSU HNB BK482 BS T304

### General Information

Number of gear units	1 unit
Driver included	Yes

## Light Technical

Luminous Flux	1,119 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color rendering index (CRI)	≥80
Optic type	High-reflective metal reflector Narrow beam 10 to 20 degrees

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	10.1 W
Suitable for random switching	Yes
Protection class IEC	Safety class I

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Housing Color	Black RAL 9004
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.434,0.403) SDCM<2