



LEDINAIRE – simply great LED

Ledinaire Waterproof

Uncomplicated, off-the-shelf quality and reliability – that's the beauty of LEDINAIRE. LEDINAIRE keeps it simple, delivering the essentials and nothing more. We don't spend money on things you don't need: no flashy packaging, no unnecessary brochures. We offer a selection of popular, low-cost LED solutions, ensuring that LED lighting is within your price range, and that our products always meet the highest possible standard. This no-nonsense approach to lighting means that you get exactly what it says on the box – reliability, affordability, and energy efficiency. Designed for mainstream applications, the sturdy LEDINAIRE WT060C Waterproof is a cost-effective, energy-saving LED solution for use in wet and dusty environments.

Benefits

- Minimalistic sealed-for-life tubular housing
- Comfortable diffuse light
- Up to 40% energy saving

Features

- Professional product quality and reliability
- Sturdy, waterproof luminaire
- Choice of luminous flux: 3600 and 5500 lm
- Impact resistance: IK08
- Ingress protection: IP65
- Mounting brackets can be positioned over the full length of the luminaire

Application

- Covered car parks
- Industrial halls (up to 4 m in height)
- (Cold) storage rooms

Ledinaire Waterproof


Versions



Ledinaire Waterproof


Dimensional drawing

WT060C



VERSION	A	B	C	D	E	F	G
L1800	18	18	24	1800	1620	1800	18
L1200	12	12	24	1200	1080	1200	12
L900	9	9	24	900	810	900	9
L600	6	6	24	600	540	600	6

WT060C TW



VERSION	A	B	C	D	E	F
L1800	18	18	24	1800	1620	1800
L1200	12	12	24	1200	1080	1200

Product details



Ledinaire waterproof, WT060C



Ledinaire waterproof, WT060C



Ledinaire waterproof, WT060C



Ledinaire waterproof, WT060C



Ledinaire waterproof, WT060C



Ledinaire waterproof, WT060C

Ledinaire Waterproof

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	No
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Optic type	Symmetrical
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Controls and Dimming	
Dimmable	No
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP66
Approval and Application	
Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Flickering value (PstLM) – Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Initial Performance (IEC Compliant)	
Initial chromaticity	<5
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
36009699	WT060C LED36S/840 PSU L1200 BN	4000 K	120 lm/W	3,600 lm
36010299	WT060C LED36S/840 PSU TW1 L1200 BN	4000 K	120 lm/W	3,600 lm
36015799	WT060C LED36S/865 PSU L1200 BN	6500 K	120 lm/W	3,600 lm
36291599	WT060C LED25S/840 PSU L1200 BN	4000 K	125 lm/W	2,500 lm
36292299	WT060C LED25S/840 PSU TW1 L1200 BN	4000 K	125 lm/W	2,500 lm
36011999	WT060C LED56S/840 PSU L1500 BN	4000 K	121 lm/W	5,600 lm
36012699	WT060C LED56S/840 PSU TW1 L1500 BN	4000 K	121 lm/W	5,600 lm
36017199	WT060C LED56S/865 PSU L1500 BN	6500 K	121 lm/W	5,600 lm
36293999	WT060C LED34S/840 PSU L1500 BN	4000 K	121 lm/W	3,400 lm
36294699	WT060C LED34S/840 PSU TW1 L1500 BN	4000 K	121 lm/W	3,400 lm
36295399	WT060C LED80S/840 PSU L1800 BN	4000 K	123 lm/W	8,000 lm
36007299	WT060C LED18S/840 PSU L600 BN	4000 K	120 lm/W	1,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
36009699	WT060C LED36S/840 PSU L1200 BN	30 W
36010299	WT060C LED36S/840 PSU TW1 L1200 BN	30 W
36015799	WT060C LED36S/865 PSU L1200 BN	30 W
36291599	WT060C LED25S/840 PSU L1200 BN	20 W
36292299	WT060C LED25S/840 PSU TW1 L1200 BN	20 W

Order Code	Full Product Name	Power Consumption
36011999	WT060C LED56S/840 PSU L1500 BN	46 W
36012699	WT060C LED56S/840 PSU TW1 L1500 BN	46 W
36017199	WT060C LED56S/865 PSU L1500 BN	46 W
36293999	WT060C LED34S/840 PSU L1500 BN	28 W
36294699	WT060C LED34S/840 PSU TW1 L1500 BN	28 W

Ledinaire Waterproof

Order Code	Full Product Name	Power Consumption
36295399	WT060C LED80S/840 PSU L1800 BN	65 W

Order Code	Full Product Name	Power Consumption
36007299	WT060C LED18S/840 PSU L600 BN	15 W



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2025, December 13 - data subject to change