



GreenPerform Waterproof Tubular G2: An easily installed, reliable waterproof luminaire

GreenPerform Waterproof Tubular G2

GreenPerform Waterproof Tubular G2 delivers on the GreenPerform promise of innovative, high-quality luminaires. A reliable, efficient luminaire with long lifetime, GreenPerform Waterproof Tubular G2 comes in two versions to meet various applications needs. The ammonia-resistant and sealed luminaire (PMMA) is suitable for animal lighting, livestock and food applications, while the PC version offers a modern and industrial design that is suitable for a wide range of general lighting applications. Both versions come with significant dust, water and impact protection

Benefits

- Enhanced energy saving and TCO
- Reliable and ideal for animal farms or food processing (PMMA version), industrial application (PC version), and parking or high rank waterproof applications
- Quick installation and flexible mounting (rotatable)

Features

- Up to 161lm/W, and 100khrs L70 lifetime
- High water, dust and impact protection: IP67/IP69K/IK06 (PMMA), IP68/IP69K/IK10 (PC)
- Through wiring installed with external push in connector

GreenPerform Waterproof Tubular G2

Application

- Food Processing
- Parking Garages
- Manufacturing
- Poultry or farms

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.



Versions



RTP-OF-GreenPerform-
Waterproof-Tubular-G2

RTP-OF-GreenPerform-
Waterproof-Tubular-G2

Dimensional drawing



GreenPerform Waterproof Tubular G2

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Luminous Efficacy (rated) (Nom)	161 lm/W

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Housing Color	White RAL 9003
---------------	----------------

Approval and Application

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux
911401834388	WT238C G2 LED50S/840 PSU L1200 TW GM	5,000 lm
911401834588	WT228C G2 LED50S/840 PSU L1200 TW	5,000 lm
911401834788	WT238C G2 LED50S/840 PSD L1200 TW GC	5,000 lm
911401834988	WT238C G2 LED50S/840 PSD L1200 TW GM	5,000 lm
911401835188	WT228C G2 LED50S/840 PSD L1200 TW	5,000 lm
911401835388	WT238C G2 LED50S/840 PSU L1200 TW GC	5,000 lm
911401834288	WT238C G2 LED70S/840 PSU L1500 TW GC	7,000 lm
911401834488	WT238C G2 LED70S/840 PSU L1500 TW GM	7,000 lm
911401834688	WT228C G2 LED70S/840 PSU L1500 TW	7,000 lm
911401834888	WT238C G2 LED70S/840 PSD L1500 TW GC	7,000 lm
911401835088	WT238C G2 LED70S/840 PSD L1500 TW GM	7,000 lm
911401835288	WT228C G2 LED70S/840 PSD L1500 TW	7,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401834388	WT238C G2 LED50S/840 PSU L1200 TW GM	31 W
911401834588	WT228C G2 LED50S/840 PSU L1200 TW	31 W
911401834788	WT238C G2 LED50S/840 PSD L1200 TW GC	31 W
911401834988	WT238C G2 LED50S/840 PSD L1200 TW GM	31 W
911401835188	WT228C G2 LED50S/840 PSD L1200 TW	31 W
911401835388	WT238C G2 LED50S/840 PSU L1200 TW GC	31 W

Order Code	Full Product Name	Power Consumption
911401834288	WT238C G2 LED70S/840 PSU L1500 TW GC	43.5 W
911401834488	WT238C G2 LED70S/840 PSU L1500 TW GM	43.5 W
911401834688	WT228C G2 LED70S/840 PSU L1500 TW	43.5 W
911401834888	WT238C G2 LED70S/840 PSD L1500 TW GC	43.5 W
911401835088	WT238C G2 LED70S/840 PSD L1500 TW GM	43.5 W
911401835288	WT228C G2 LED70S/840 PSD L1500 TW	43.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401834388	WT238C G2 LED50S/840 PSU L1200 TW GM	No
911401834588	WT228C G2 LED50S/840 PSU L1200 TW	No
911401834788	WT238C G2 LED50S/840 PSD L1200 TW GC	Yes
911401834988	WT238C G2 LED50S/840 PSD L1200 TW GM	Yes
911401835188	WT228C G2 LED50S/840 PSD L1200 TW	Yes
911401835388	WT238C G2 LED50S/840 PSU L1200 TW GC	No

Order Code	Full Product Name	Dimmable
911401834288	WT238C G2 LED70S/840 PSU L1500 TW GC	No
911401834488	WT238C G2 LED70S/840 PSU L1500 TW GM	No
911401834688	WT228C G2 LED70S/840 PSU L1500 TW	No
911401834888	WT238C G2 LED70S/840 PSD L1500 TW GC	Yes
911401835088	WT238C G2 LED70S/840 PSD L1500 TW GM	Yes
911401835288	WT228C G2 LED70S/840 PSD L1500 TW	Yes

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
911401834388	WT238C G2 LED50S/840 PSU L1200 TW GM	Polycarbonate Diffuser	IK10	IP68
911401834588	WT228C G2 LED50S/840 PSU L1200 TW	Polymethyl methacrylate bowl/cover	IK06	IP67

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
911401834788	WT238C G2 LED50S/840 PSD L1200 TW GC	Polycarbonate Diffuser	IK10	IP67
911401834988	WT238C G2 LED50S/840 PSD L1200 TW GM	Polycarbonate Diffuser	IK10	IP68

GreenPerform Waterproof Tubular G2

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
911401835188	WT228C G2 LED50S/840 PSD L1200 TW	Polymethyl methacrylate bowl/cover	IK06	IP67
911401835388	WT238C G2 LED50S/840 PSU L1200 TW GC	Polycarbonate Diffuser	IK10	IP67
911401834288	WT238C G2 LED70S/840 PSU L1500 TW GC	Polycarbonate Diffuser	IK10	IP67
911401834488	WT238C G2 LED70S/840 PSU L1500 TW GM	Polycarbonate Diffuser	IK10	IP68

Order Code	Full Product Name	Optical cover type	Mech. impact protection code	Ingress protection code
911401834688	WT228C G2 LED70S/840 PSU L1500 TW	Polymethyl methacrylate bowl/cover	IK06	IP67
911401834888	WT238C G2 LED70S/840 PSD L1500 TW GC	Polycarbonate Diffuser	IK10	IP67
911401835088	WT238C G2 LED70S/840 PSD L1500 TW GM	Polycarbonate Diffuser	IK10	IP68
911401835288	WT228C G2 LED70S/840 PSD L1500 TW	Polymethyl methacrylate bowl/cover	IK06	IP67

Approval and Application

Order Code	Full Product Name	CE mark
911401834388	WT238C G2 LED50S/840 PSU L1200 TW GM	Yes
911401834588	WT228C G2 LED50S/840 PSU L1200 TW	Yes
911401834788	WT238C G2 LED50S/840 PSD L1200 TW GC	No
911401834988	WT238C G2 LED50S/840 PSD L1200 TW GM	Yes
911401835188	WT228C G2 LED50S/840 PSD L1200 TW	Yes
911401835388	WT238C G2 LED50S/840 PSU L1200 TW GC	No

Order Code	Full Product Name	CE mark
911401834288	WT238C G2 LED70S/840 PSU L1500 TW GC	No
911401834488	WT238C G2 LED70S/840 PSU L1500 TW GM	Yes
911401834688	WT228C G2 LED70S/840 PSU L1500 TW	Yes
911401834888	WT238C G2 LED70S/840 PSD L1500 TW GC	No
911401835088	WT238C G2 LED70S/840 PSD L1500 TW GM	Yes
911401835288	WT228C G2 LED70S/840 PSD L1500 TW	Yes

