

**PHILIPS**

**Lighting**



# **MSR Gold™ FastFit – easy lamp replacement in seconds**

## **MSR Gold™ FastFit**

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold<sup>TM</sup> 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### **Benefits**

- Lamp replacement in just seconds, exchangeable with halogen lamp
- High beam intensity
- Easy handling, smaller and lighter fixtures possible
- Boostable light levels
- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Reduces early lamp or lamp holder failures. Excellent current transfer
- Pure, white light; colour point close to black body line

# MSR Gold™ FastFit

## Features

- Philips FastFit
- Very short arc
- Compact design
- Flexible power range
- Philips pinch protection
- Innovative gold plated pins
- MSR filling


## Application

- Entertainment

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm
1CT/4							
MSR Gold 700/2 FastFit	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm
1CT/8							

## General Information

Cap-Base	PGJX50
Operating Position	UNIVERSAL

## Controls and Dimming

Dimmable	Yes
----------	-----

## Light Technical

Order Code	Full Product Name	Correlated Color		Color		Luminous Flux
		Temperature (Nom)	rendering index (CRI)	Color Code	Luminous Flux	
928106205114	MSR Gold 700/2 FastFit 1CT/8	7500 K	73	2	46,000 lm	

Order Code	Full Product Name	Correlated Color		Color		Luminous Flux
		Temperature (Nom)	rendering index (CRI)	Color Code	Luminous Flux	
928175005115	MSR Gold 1200 FastFit 1CT/4	6000 K	80	-	92,000 lm	

## Operating and Electrical

Order Code	Full Product Name	Lamp Current		Power Consumption
		(Nom)		
928106205114	MSR Gold 700/2 FastFit 1CT/8	10.2 A		700 W

## MSR Gold™ FastFit

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
92817500515	MSR Gold 1200 FastFit 1CT/4	15 A	1,200 W

