



## MSR – bright vivid colors, always

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Benefits

- Optimal light collection
- Excellent color characteristics
- Brightness on stage

### Applications

- Theatre stages
- Discos
- Events
- Shows

Features

- Single ended lamp concept
- High CRI
- Daylight Color Temperatures

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions




XPPR\_XDMSR\_0018-Product photo




XPPR XDMSR 0025

Dimensional drawing



| Product         | D (max) | O      | L (min) | L (max) | L     | C (max) | F     |
|-----------------|---------|--------|---------|---------|-------|---------|-------|
| MSR 700/2 1CT/8 | 30 mm   | 8.0 mm | 74 mm   | 76 mm   | 75 mm | 152 mm  | 42 mm |



| Product             | D (max) | O      | L (min) | L (max) | L     | C (max) | F (max) | F     | F (min) |
|---------------------|---------|--------|---------|---------|-------|---------|---------|-------|---------|
| MSR 575/2 10H 1CT/4 | 30 mm   | 7.0 mm | 64 mm   | 66 mm   | 65 mm | 125 mm  | 36 mm   | 35 mm | 34 mm   |

### General Information

Operating Position UNIVERSAL [Any or Universal (U)]

### Light Technical

Color Code 2

### Controls and Dimming

Dimmable No

## General Information

| Order Code   | Full Product Name   | Cap-Base |
|--------------|---------------------|----------|
| 928171505114 | MSR 700/2 1CT/8     | G22      |
| 928171605115 | MSR 575/2 10H 1CT/4 | GX9.5    |

## Light Technical

| Order Code   | Full Product Name   | Luminous Flux | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---------------------|---------------|------------------------------------|-----------------------------|
| 928171505114 | MSR 700/2 1CT/8     | 55,000 lm     | 7200 K                             | 80                          |
| 928171605115 | MSR 575/2 10H 1CT/4 | 47,000 lm     | 6990 K                             | 73                          |

## Operating and Electrical

| Order Code   | Full Product Name   | Power Consumption | Lamp Current (Nom) |
|--------------|---------------------|-------------------|--------------------|
| 928171505114 | MSR 700/2 1CT/8     | 700 W             | 11 A               |
| 928171605115 | MSR 575/2 10H 1CT/4 | 575 W             | 6.75 A             |