



# Halogen non-reflector lamps – high-quality light and easy to use

## Halogen non-reflector

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Benefits

- Optimal beam performance
- 100% Color Rendering Index (CRI)
- Constant light output throughout lifetime

### Features

- Distortion-free, quartz bulb and precisely defined filament position
- Lamp replacement without adjustment
- XHP version with xenon gas for maximum light output
- Flat filament available

# Halogen non-reflector

## Application


- Studio, film, theatre and disco lighting
- Slide, overhead, profile and 8/16 mm film projectors
- Microscopes
- Optical equipment
- Slide and film viewers
- Surgery lamps
- Microfilm readers
- Dental lamps
- Spectrography

## Versions



XPPR XHMPSEFF 0003

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14623 95W	11.5 mm	31.5 mm	32.25	32	1.05 mm	1 mm	0.95	50 mm
G6.35 17V			mm	mm			mm	
1CT/10X10F								
7023 100W	11.5 mm	29.75	30.25	30	1.30 mm	1.25	1.20	44 mm
GY6.35 12V		mm	mm	mm		mm	mm	
1CT/10X10F								
7027 50W	11.5 mm	29.75	30.25	30	1.05 mm	1 mm	0.95	44 mm
G6.35 12V		mm	mm	mm			mm	
1CT/10X10F								
7724 EVA	10.7 mm	29.65	30.25	30	1.30 mm	1.25	1.20	44 mm
100W GY6.35		mm	mm	mm		mm	mm	
12V								
7724I 100W	10.7 mm	29.65	30.25	30	1.30 mm	1.25	1.20	44 mm
GY6.35 12V		mm	mm	mm		mm	mm	

### General Information

Operating Position	S90
--------------------	-----

### Mechanical and Housing

Bulb Material	Quartz-UV Open
---------------	----------------

## General Information

## Halogen non-reflector

Order Code	Full Product Name	Cap-Base
923870217103	7027 50W G6.35 12V 1CT/10X10F	G6.35
924049819103	14623 95W G6.35 17V 1CT/10X10F	G6.35
923870017103	7023 100W GY6.35 12V 1CT/10X10F	GY6.35

Order Code	Full Product Name	Cap-Base
923872517103	7724 EVA 100W GY6.35 12V	GY6.35
923875717103	7724I 100W GY6.35 12V	GY6.35

### Light Technical

Order Code	Full Product Name	Correlated Color	Color rendering
		Temperature (Nom)	index (CRI)
923870217103	7027 50W G6.35 12V 1CT/10X10F	-	100
924049819103	14623 95W G6.35 17V 1CT/10X10F	-	-

Order Code	Full Product Name	Correlated Color	Color rendering
		Temperature (Nom)	index (CRI)
923870017103	7023 100W GY6.35 12V 1CT/10X10F	3450 K	100
923872517103	7724 EVA 100W GY6.35 12V	3300 K	100
923875717103	7724I 100W GY6.35 12V	3100 K	100

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
923870217103	7027 50W G6.35 12V 1CT/10X10F	50 W
924049819103	14623 95W G6.35 17V 1CT/10X10F	95 W
923870017103	7023 100W GY6.35 12V 1CT/10X10F	100 W

Order Code	Full Product Name	Power Consumption
923872517103	7724 EVA 100W GY6.35 12V	100 W
923875717103	7724I 100W GY6.35 12V	100 W

