



# UVA PL-L - the compact alternative to UVA TL

## UV-A(-1) PL-L

Philips offers highly reliable PL-L lamps emitting UV-A in a spectral distribution wavelength of between 315 to 380 nm. This makes these lamps suitable for various applications such as phototherapy, curing, Insect trap and Photocatalytic oxidation

### Benefits

- Optimal spectrum for various applications

### Features

- Emission peak at 350 nm

### Application

- Phototherapy
- Curing
- Insect Trap
- Photocatalytic Oxidation

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take them to your local waste facilities for recycling. Do not use a vacuum cleaner.


# UV-A(-1) PL-L

## Versions



XPPR\_XURPLL\_0001-Product photo

## Dimensional drawing



Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/09/4P	18 mm	39 mm	20.0 mm	384.2 mm	410 mm	416.6 mm
PL-L 36W/09/4P 1CT/25	18 mm	39 mm	20.0 mm	384.2 mm	410 mm	416.6 mm

