



# UVA TL – high quality multipurpose UVA lamps

## UVA TL

Philips offers highly quality TL lamps emitting UV-A in a spectral distribution wavelength of between 315 to 380 nm. This makes these lamps suitable for various applications such as phototherapy, curing & Photocatalytic oxidation

### Benefits

- Optimal spectrum for various applications

### Features

- Emission peak at 350 nm

### Application

- Phototherapy
- Curing
- Photocatalytic Oxidation

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take them to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Photobiological safety – IEC 62471 – Risk Group 2. CAUTION – UV Emitted from these products.


UVA TL

Versions



XPPR\_XUVATL\_G13\_--Product photo

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F7IT12 UVA 100W	40.5 mm	1,763.8 mm	1,770.9 mm	1,768.5 mm	1,778 mm

