



# Product Description

## UV-B Narrowband TL

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

### Benefits

- Minimum side effects like redness, itching and burns
- Minimum side effects like redness, itching and burns
- Shorter period of exposure and less erythema radiation than conventional UVB lamps
- Shorter period of exposure and less erythema radiation than conventional UVB lamps
- Optimal therapeutic effect with minimum side effects
- Optimal therapeutic effect with minimum side effects
- Proven to be most effective on the skin
- Proven to be most effective on the skin

### Features

- Emission peak at 311 nm
- Emit radiation for therapeutic and other applications
- Narrowband
- Special developed phosphor and glass
- World wide tested in more than 400 clinical tests

### Application

- Psoriasis, Vitiligo
- Phototherapy in dermatology (psoriasis, SUP)
- These lamps produce UV-B radiation which is harmful to human skin and eyes. They are therefore only available for medical and industrial applications

# UV-B Narrowband TL

## Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



XPPR\_XUMTL\_0002-Product photo

## Dimensional drawing



| Product           | D (max) | A (max)    | B (max)    | B (min)    | C (max)    |
|-------------------|---------|------------|------------|------------|------------|
| TL 100W/01 SLV/10 | 40.5 mm | 1,763.8 mm | 1,770.9 mm | 1,768.5 mm | 1,782.2 mm |

