



Specification Sheet

EcoSet Basic Control OccuSwitch surface mounting PIR sensor

EcoSet SES LSM1010

The EcoSet OccuSwitch is a movement detector with a build-in switch. It will switch off the lights in a room or area when it is vacated, and its single target is to achieve incremental energy saving in a simple, reliable and affordable way. The OccuSwitch can control an office area up to 28m².

EcoSet SES LSM1010

Functions

Automatic control

The Occuswitch sensor switches the lights on automatically when presence is detected and switches the lights off after the area is vacated (after 2 to 30 minutes depending on the settings).

Daylight override

It is possible to prevent the automatic switch-on when sufficient daylight is available in order to create additional savings.


Fixing

The OccuSwitch surface mounting PIR sensor is suitable for both surfaced mounting.

When selecting a location for the OccuSwitch, avoid obvious cold spots so that condensation does not occur.

Electrical installation

The Occuswitch surface mounting PIR sensor can be installed with the conventional wiring as shown in the diagram.



Installation (conventional wiring)


Features

Smart timer

The smart timer will extend the delay time by the set delay time if movement is detected shortly after switch-off, assuming that the area is still in use, but very little movement is made.

Applications

The Occuswitch is designed for use in offices and similar applications, including conference rooms, toilets, storage and break areas, etc. It is optimized for both surface and recessed ceiling mounting and for mounting heights between 2.5 and 4 meter.



Installation (cable wiring)

EcoSet SES LSM1010

Daylight control

Daylight override

The daylight override function prevents the lights from switching on when sufficient daylight is available. To enable this function it is necessary to set the required light level by turn the dial away from the '-' position. To disable this function, turn the dial into the '-' position.

Warnings



The Occuswitch should not be used in the following situations:

- Environmental conditions other than in a normal of fierce environment (temperature, humidity).
- In applications with heat sources like electrical heaters, within the detection range of the Occuswitch.
- In combination with lighting sources, or other devices, that can be damaged if they are switched off and on in a short period of time.
- It should not be mounted in direct line of air flow like in front of Air Conditioning vent.

Technical data

Environmental conditions

Storage conditions

Temperature -25 to +85°C

Relative humidity 0% to 90%; no condensation

Operating conditions

Temperature -20 to +55°C

Relative humidity 0 to 90%; no condensation

Mains connection Voltage Mains surge immunity 220-240VAC; 50/60Hz

1kV/2kV

Power consumption

Stand-by <1W

Maximum load 3 A (Resistive load)

Load peak inrush current <70A

Applicable wire range 0.75 to 1.5mm²

Switch off delay Light levels 2(default)/5/15/30minutes

Disable/10/30/100lux


Detection range See diagram


Protection Class

Lifetime

IP20 30,000hrs

Detection range diagram *Testing @ 3m installation height @25°C





Packing data

Туре	Box dimensions	Qty	Material	Weight (Kg)	_	
	(mm)			net	gross	
SES LSM1010 Unit box	105 x 75 x 105	1	cardboard	0.13	0.18	
SES LSM1010 Outer bo	ox 550 x 400 x 450	100	cardboard	12.50	17.47	

Ordering Data

Type Ordering	QTY	Ordering number
SES LSM1010 Occ PIR WH	In Multiples of Outer Box	9114 0154 2702

