

PHILIPS

Fortimo

LED

Fortimo LED Strip 2ft LF
8xx LV6



Datasheet

The Fortimo LED Strip is a uniquely wide portfolio which can be used in all kind of linear indoor luminaire types. Its form factor makes it easy to design-in and handle in production as it complies to Zhaga standards. Due to the availability from 0.25ft up to 5ft lengths only one product family is needed to cover a wide range of needs.

Key features and benefits

- Typical module efficiency of 186 lm/W (at 4000K CRI80)
- CRI90 High Efficiency typical performance of 174 lm/W (at 4000K CRI90)
- Long life-time: >72,000 hours
- Excellent color consistency of 3 SDCM
- Two lumen packages per length available: LF (650 lm/ft) and MF (1100 lm/ft)
- Wide range of CCTs available: 2700K, 3000K, 3500K, 4000K, 5000K and 6500K
- Available in High Voltage (HV) and Low Voltage (LV)
- Options in front connector (FC) or back connector (BC)
- Small LED module width of only 20mm
- Available lengths: 0.25ft / 0.5ft / 1ft / 2ft / 4ft (1120mm) / 4ft extended (1150mm) / 5ft (1400mm) / 5ft extended 1450mm)
- Wide temperature (Tc) range -40°C to +80°C
- Five year system warranty

March 2023



Ordering data

Commercial product name	EOC	12NC	EPREL registration #	Box quantity
Fortimo LED Strip 2ft LF 830 FC LV6	8719514 488847 00	9290 029 44206	1413428	110
Fortimo LED Strip 2ft LF 840 FC LV6	8719514 488861 00	9290 029 44306	1413429	110

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED Strip 2ft LF 8xx LV6	181	480	480	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	45	75	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)


Fortimo LED Strip 2ft LF 830 FC LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	1190	1228	1310	lm
Efficacy	167	175	198	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.433, 0.400)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photometric code		830/339		
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	830	lm	lm/W
80% I-nom 145mA	Tc 25 °C	1021	183
	Tc-nom 45 °C	995	179
	Tc-max 85 °C	935	171
I-nom 181mA	Tc 25 °C	1259	178
	Tc-nom 45 °C	1228	175
	Tc-max 85 °C	1154	167
I-max 480mA	Tc 25 °C	3077	154
	Tc-nom 45 °C	2999	151
	Tc-max 85 °C	2813	144




Fortimo LED Strip 2ft LF 840 FC LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	1260	1300	1430	lm
Efficacy	177	186	216	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.381, 0.377)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photometric code		840/339		
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	840	lm	lm/W
80% I-nom 145mA	Tc 25 °C	1081	193
	Tc-nom 45 °C	1053	190
	Tc-max 85 °C	988	181
I-nom 181mA	Tc 25 °C	1335	189
	Tc-nom 45 °C	1300	186
	Tc-max 85 °C	1220	177
I-max 480mA	Tc 25 °C	3276	164
	Tc-nom 45 °C	3190	161
	Tc-max 85 °C	2989	153



Electrical characteristics


Parameter	Min	Typ	Max	Unit
Forward voltage	36.6	38.7	39.4	V
Power consumption	6.6	7.0	7.1	W = kWh/1000h
Number of modules per chain			2	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
480	244	86
330	174	92
181	100	100
145	81	102
90	51	106



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	94	95
45	100	100
25	103	102
0	105	104




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% Inom=145mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>68	>68	>68
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>68	67	66
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	47	45	45
Inom=181mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>68	>68	>68
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>68	67	66
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	47	45	45
Ilife=480mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>41	>41	>41
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>41	>41	>41
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	41	40	39

Lifetime

Parameter	Value	Unit
M70F50 nominal	>72000	hours
M70F50 life	>72000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.25...0.75	mm ²	solid wire
	18...24	AWG	solid wire
Input wire strip length	7.5...8.5	mm	
Input wire cross-section	0.33...0.5	mm ²	stranded wire
	20...22	AWG	stranded wire
Input wire strip length	7.5...8.5	mm	

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	558.9	559.2	559.5	mm
Width	19.8	20	20.6	mm
Height PCB	1.45	1.6	1.75	mm
Height Total		4.3		mm
Product mass		34.5		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		480	mA
Case temperature (Tc-max)		85	°C
ESD (direct contact)	8		kV
Working voltage		350	V _{dc}

Application information

Certificates and Standards

CE
ENEC
ENEC+
cULus

Environmental

RoHS/REACH

Application

Dimming	Yes
---------	-----



© 2023 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

02/03/2023