

LED Office Lum./LED办公灯具

RC420V Coreview G4

Mounting instructions/安装说明书

444100009541

GB
7000

IEC
60598

IP20

$t_a 25^{\circ}\text{C}$



Product Type/产品型号	Voltage/电压	Frequency 频率	Power/功率	CCT(K)/色温	lm/流明输出	Control/控制	kg
RC420V G4 W30L30	220-240V~	50/60Hz	Max 25W	3000/4000/5000/6500	Max 1800	PSU/PSD/IAO/IAP/SW	1.22
RC420V G4 W30L120	220-240V~	50/60Hz	Max 37W	3000/4000/5000/6500	Max 4000	PSU/PSD/IAO/IAP/SW/TNW	3.66
RC420V G4 W30L120 AS	220-240V~	50/60Hz	Max 37W	3000/4000/5000/6500	Max 4000	PSU/PSD/IAO/IAP/SW/TNW	3.32
RC420V G4 W60L60	220-240V~	50/60Hz	Max 40W	3000/4000/5000/6500	Max 4000	PSU/PSD/IAO/IAP/SW/TNW	3.34
RC420V G4 W60L60 AS	220-240V~	50/60Hz	Max 40W	3000/4000/5000/6500	Max 4000	PSU/PSD/IAO/IAP/SW/TNW	3.26
RC420V G4 W60L120	220-240V~	50/60Hz	Max 49W	3000/4000/5000/6500	Max 5000	PSU/PSD/IAO/IAP/SW/TNW	5.81
RC420V G4 W60L120 AS	220-240V~	50/60Hz	Max 49W	3000/4000/5000/6500	Max 5000	PSU/PSD/IAO/IAP/SW/TNW	5.88
RC420V G4 W603L603	110-240V~	50/60Hz	Max 37W	3000/4000/5000/6500	Max 3800	PSU/PSD	3.45

Caution: The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
本灯具光源为不可替换，当光源寿命终止时，请整体更换本灯具。

Type	L(mm)	W(mm)	H(mm)	Sort
RC420V G4 W30L30 PSU	295	295	90	I
RC420V G4 W30L120	1195	295	90	I
RC420V G4 W30L120 AS	1200	300	58.5	II
RC420V G4 W60L60	595	595	90	I
RC420V G4 W60L60 AS	600	600	90	II
RC420V G4 W60L120	1195	595	90	I
RC420V G4 W60L120 AS	1200	600	90	II
RC420V G4 W603L603	603	603	90	I

Inrush current	Type	Run Current (A) (@220V)	Start (Inrush) Current(A) / Ipeak (A)	Start Current Duration (μs) /T(@50% of Ipeak) (μs)	* Touch current or protective conductor current (mA)	Maximum Number of Luminaire on MCB 16A Type B (pcs)	Maximum Number of Luminaire on MCB 16A Type C (pcs)
	RC420V G4 W30L30 PSU	0.101	4.5	65	<0.5	34	58
	RC420V G4 W30L30 PSD	0.101	20.4	195	<0.7	24	41
	RC420V G4 W60L60 PSU/RC420V G4 W30L120 PSU	0.187	19.5	258	<0.7	40	68
	RC420V G4 W60L60 PSD/RC420V G4 W30L120 PSD	0.182	20.4	195	<0.7	24	41
	RC420V G4 W30L30 IAP/RC420V G4 W60L60 IAP	0.167	12	250	<0.7	24	41
	RC420V G4 W30L30 IAO/RC420V G4 W60L60 IAO	0.192	26	140	<0.4	24	41
	RC420V G4 W30L120 IAO/RC420V G4 W30L30 SW	0.177	15.2	292	<0.4	24	41
	RC420V G4 W60L60 SW/RC420V G4 W30L120 SW	0.212	30	250	<0.7	16	27
	RC420V G4 W603L603 PSD	0.247	19.5	258	<0.7	40	68
	RC420V G4 W603L603 PSU	0.212	15.2	200	<0.7	46	78
	RC420V G4 W60L120 PSD	0.258	24.9	186	<0.7	27	46
	RC420V G4 W60L120 IAP	0.242	22	270	<0.7	24	41
	RC420V G4 W60L120 IAO/RC420V G4 W60L120 SW	0.222	21	280	<0.5	21	36
	RC420V G4 W60L120 TW	0.253	19.6	356	<0.4	18	31

The leakage current *(touch current or protective conductor current) of electrical circuit may be greatly dependent upon electrical supply cables used such as its rating and length, proper connection of electrical supply cables to luminaires and wiring connection topology of luminaires to the supply electrical circuit amongst other site conditions.
* In some cases referred to as Earth Leakage Current.

电路的漏电流*(接触电流和保护导体电流，很大程度取决于导线，如导线的规格长度。在现场使用时，电源线到灯具的接法，灯具电源线的排布也有影响。
*在有些场合也称作对地漏电流。

Signify (China) Investment Co., Ltd.
Address: Building 9 #, Lane 888, Tianlin Road, Minhang District,
Shanghai City Zip Code: 200233
昕诺飞(中国)投资有限公司
地址: 上海市闵行区田林路888弄9号楼
邮编: 200233

PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.



