



Daylight W120L120 3000 K

This Daylight panel provides high quality light, high CRI (95), 3000 K, dimmable with DALI controls.

Operating and Electrical

Input voltage	220–240 V
Input frequency	50 to 60 Hz
Input current	0.31 A
Inrush current	50 A
Inrush time	330 us
Products per MCB (type B 16A)	10
Power factor (min.)	0.9
Surge protection	1 kV DM and 2 kV CM

Controls and User Interface

Lighting control	DALI 2
Number of DALI addresses	2

Mechanical and Housing

Dimensions (LxWxH)	1195 x 1195 x 81 mm
Housing material	Steel
Housing color	Black RAL 9004
Optical cover/lens type	Polystyrene
Optical cover/lens finish	Opal
Net weight product	23 kg

General Information

Light source	Non-replaceable LED module
Light source colour	White 3000 K
Driver included	Yes
Driver/power unit/transformer	PSD (Power supply unit with DALI interface)
Maximum electrical power	73 W
Max light output	8000 lm
Efficacy	110 lm/W
CCT	3000 K
Color point SDCM	3
CRI	95
R9	> 50
UGR	19
Luminaire beam angle	100°
Lifetime	50 khrs B50L90 100 khrs B50L80
Control interface	DALI
Connector	5 pole push-in connector
Protection class IEC	Safety class I
Ambient temperature range	0 to +35 °C
Performance ambient temp. Tq	25 °C
Storage temperature	-20 to +60 °C
Ingress protection code	IP44 (bottom), IP20 (top)
Mech. impact protection code	IK02
Glow-wire test	650 °C

Daylight W120L120 3000 K


Product data

910505106619

LP911P NC2 DAYLIGHT 930 W120L120 BLK




Dimensional drawing




Dimensions in mm

Installation options


Suspended recessed



Suspended surface mounted



Suspended in open ceiling



In the box

