


PHILIPS

Xitanium

LED driver



Datasheet

Xitanium non-isolated Dip Switch driver

Xitanium 100W 350-500mA 200V DS 230V

9290 038 74280

Philips Xitanium non-isolated Dip Switch Linear LED drivers provide 4 output currents by dip switch, and 50,000 hours lifetime at T_c max 85°C. These drivers offer the same level of performance as Xitanium adjustable output current linear drivers to ensure high quality of light. They are ideal for high volume applications while delivering to quality requirements that you can expect from the Philips brand.

Features

- Class I application
- Low Ripple less than 4%
- 4 output currents by Dip switch
- High efficiency
- 50,000 hours lifetime @ T_c -max 85°C

Benefits

- Provides options for different luminaire designs
- Comfortable for the eyes
- Selectable output current enables flexibility and SKU reduction
- Energy saving
- Peace of mind with proven reliability

Application

- Waterproof lighting
- Linear High Bay

Logistical data

Specification item	Value
Product name	Xitanium 100W 350-500mA 200V DS 230V
Logistic code 12NC	9290 038 74280
Pieces per box	50

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.5	A	@ full output power @ rated input voltage
Rated input power	104.0	W	@ full output power @ rated input voltage
Power factor performance range	≥ 0.9 C		
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	≥ 94.0	%	@ full output power @ rated input voltage @ max. U _{out}
Input voltage AC	198...264	V _{ac}	Operational range
Input frequency AC	45...66	Hz	Operational range
Isolation input to output	No		

Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	100...200	V _{dc}	
Output voltage max.	250	V	Maximum output voltage (rms)
Output current	350 / 400 / 450 / 500	mA	
Output current tolerance ±	8	%	@full load
Output current ripple LF	≤ 4	%	Ripple = peak / average, < 3kHz
Output current ripple HF	≤ 15	%	
Output P _{st} ^{LM}	≤ 0.1		In entire operating window
Output SVM	≤ 0.1		In entire operating window
Output power	35.0...100.0	W	
Rated output power	100.0	W	

Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		See design-in guide at www.philips.com/oem for more controllability details.
Isolation controls input to output	No		acc. IEC61347-1

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.5...1.5 / 20...16	mm ² / AWG	solid / stranded wire
Input wire strip length	8.5...9.5	mm	
Output wire cross-section	0.5...1.5 / 20...16	mm ² / AWG	solid / stranded wire
Output wire strip length	8.5...9.5	mm	
Maximum cable length	2	m	Total length of wiring including LED module, one way




Isolation

Insulation per IEC61347-1	Input	Output
Input	-	No
Output	No	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	210	mm	
Mounting hole distance (A2)	200	mm	
Width (B1)	30	mm	
Height (C1)	21	mm	
Mounting hole diameter (D1)	4.1	mm	
Mounting hole diameter (D2)	4.1	mm	
Weight	165	gram	
Housing color	white		




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	85	°C	Maximum temperature measured at Tcase-point
Tcase-life	75	°C	Measured at Tcase-point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	100,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum failures = 10%



Maximum failures = 10%

Temperature [°C]	Lifetime	Unit	Condition
85	50000	hr	
80	71000	hr	
75	100000	hr	Temperature measured @Tc point
70	>100000	hr	
65	>100000	hr	

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+85	°C	
Relative humidity	5...95	%	Non-condensing

Programmable features

Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	DipSwitch	500 mA	

Non-programmable features


Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Suitable for fixtures with protection class	I	per IEC60598

Inrush current

Specification item	Value	Unit	Condition
Inrush current	58	A	Input voltage 230V
Inrush peak width	156	μs	Input voltage 230 V, measured at 50% height
Drivers / MCB 16A type B	≤ 12	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces) a correction factor of 80% has to be applied to the rated current



Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.5	mA rms	Acc. IEC60598-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Application Info (Approbation)


Specification item	Value
Approval marks and Certifications	CB / CCC / CE / EAC / ENEC / RCM / UA / UKCA
Ingress Protection classification (IP)	20
Application	Indoor Linear
Mounting Type	Built-in

Graphs


Operating window




Power factor versus output power



Efficiency versus output power



THD versus output power



Notes

Electrical Specifications:
All the specifications are typical and at 25°C Ta unless specified otherwise.



©2024 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.
UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: March 22, 2024 v1

www.philips.com/oem