

Day-Brite



by Signify

Special Application

Kleenseal LED KTR 100

Recessed cleanroom
4,000 to 13,000 lumens



Day-Brite / CFI Kleenseal KTR 100 LED recessed is a cleanroom luminaire well suited for laboratories and dirty areas such as locker rooms.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

Example: K12490L840G6AP3U

Family	Size	Lumens	CRI/CCT	Ceiling Type	Door Frame	Lens Type	Voltage	Options
<input type="text" value="K1"/>					<input type="text" value="6"/>		-	
K1 Kleenseal KTR100	14 1x4	40L 4,000 nominal delivered lumens (1x4, 2x2)	835 3500K (CRI 80)	G 1",1-1/2" Grid T 2G 2" Grid T F Flange	6 Aluminum 4-piece flush white	AP3 .125" acrylic prismatic Other lenses available	U Universal voltage, 120-277V 1 120V 2 277V	DN Lens furnished prisms down SSD Stainless steel inset door
	22 2x2	60L 6,000 nominal delivered lumens (1x4, 2x2)	840 4000K (CRI 80)					
	24 2x4	64L 6,400 nominal delivered lumens (2x4)	850 5000K (CRI 80)					
		75L 7,500 nominal delivered lumens (2x4)						
		87L 8,700 nominal delivered lumens (2x4)						
		90L 9,000 nominal delivered lumens (2x4)						
		110L 11,000 nominal delivered lumens (2x4)						
		130L 13,000 nominal delivered lumens (2x4)						

General Notes

- Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

Predicted L70 Lifetime

- 25°C ambient >100,000 hours (based upon LED manufacturer's supplied LM-80 data and in-situ laboratory testing).

K1 Kleenseal LED KTR100 recessed

Cleanroom luminaire, 4,000, 6,000, 9,000, 11,000, or 13,000 lumens

Standards


- Certified to meet UL 1598 standards for wet location.

Construction/Finish

- Sealed aluminum housing resists corrosion and is lightweight which speeds installation.
- Fits 1", 1-1/2", 2", and Tall 2" grid or flange mountings.
- Top and end 1/2" conduit K.O.s for easy thru wiring.
- Seismic support mounting is standard.
- Removable sealed wiring access plate.

- Door is secured to housing with captive stainless steel screws.
- Door frame is retained to housing when opened for safety and ease during re-lamping.
- .125" prismatic acrylic lens is silicone sealed to flush aluminum door frame.
- Class 100-100,000 cleanrooms.

Dimensions



Note: For technical information or codes and classifications, see PDFs Tech1-Tech5 online.

Ceiling Opening Flange Type	Grid Type	A	B	C
1X4 10-3/4" X 48-1/8"	1" or 1-1/2" Grid	23-3/4" (603.3 mm)	47-3/4" (1212.9 mm)	1-11/16"
2X2 22-3/4" X 24-1/8"	2" Grid	23-3/4" (603.3 mm)	47" (1194 mm)	1-11/16"
2X4 22-3/4" x 48-1/8"				



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.