

# Day-Brite

## CFI

by Signify

### Recessed

### DuaLED 1x4

1DLG up to 4700 lumens



Day-Brite / CFI DuaLED recessed is a highly efficient, visually comfortable, architecturally styled recessed LED luminaire, designed with a minimalistic strategy to achieve sustainable objectives. Its clean, modern design offers a fresh variation on the popular dual chamber theme and provides architectural styling compatible with virtually any area. SpaceWise Technology for selected applications is optional for additional energy savings and control.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide - standard & wireless controls

Standard configurations available with all choices, unless otherwise noted. Base configurations selections indicated by blue.

example: 1DLG41L840-4-D-UNV-DIM

Width	Family	Ceiling Type	Lumen Package	Color	Length	Center Diffuser	Voltage	Driver	Options
1	DL	G		-	4	D	-	-	
1	DL DualLED	G Grid	<b>Base configuration</b> <b>37B</b> 3700 nominal delivered lumens  <b>Standard configurations</b> <b>27L</b> 2700 nominal delivered lumens <b>36L</b> 3600 nominal delivered lumens <b>41L</b> 4100 nominal delivered lumens <b>47L</b> 4700 nominal delivered lumens  Other lumen packages may be ordered in increments of 100lm from 2700 to 4700 lumens	<b>830</b> 80 CRI, 3000K <b>835</b> 80 CRI, 3500K <b>840</b> 80 CRI, 4000K <b>850</b> 80 CRI, 5000K	4'	D Diffuse (opal)	<b>UNV</b> Universal Voltage, 120-277 volt <b>347</b> 347V	<b>DIM</b> <sup>1</sup> 0-10V dimming <b>SDIM</b> Step dimming to 40% input power <b>LDE</b> <sup>2</sup> Lutron LDE5, 5% dimming <b>DALI</b> DALI dimming	<b>F1</b> 3/8" Flex, 3 Wire 18 gauge 6' <b>F2</b> 3/8" Flex, 4 Wire 18 gauge 6' <b>F1/D</b> 3/8" Twin Flex, 3 Wire 18 gauge 6' for dimmable luminaires <b>F2/SW</b> 3/8" Single Flex, 5 Wire 18 gauge 6' for dimmable luminaires <b>GLR</b> Fusing, Fast Blow <b>EMLED</b> Bodine BSL310 10W battery pack (requires driver enclosure on top of luminaire) <b>EMLED7</b> Bodine BSL17 7W battery pack (requires driver enclosure on top of luminaire) <b>DSC</b> Quick driver disconnect <b>CHIC</b> Chicago Plenum rated <b>ER100</b> <sup>4,5,9,10</sup> UL924 listed sensor bypass relay, factory installed between driver & sensor <b>GTD/E</b> <sup>5,9</sup> UL924 listed Bodine GTD factory installed on driver input <b>SWZCSR</b> <sup>1,4,8</sup> Remote Interact Pro scalable sensor with integral daylight & occupancy sensing, advanced grouping with dwell time <b>SWZDTRM</b> <sup>1,4</sup> Remote SpaceWise only sensor, daylighting and occupancy, advanced grouping with dwell time <b>RADIO</b> <sup>1,4,6</sup> Interact Pro RF sensor, enables wireless connected lighting control <b>AG</b> Antimicrobial paint

### Footnotes

- 1 Integral controls options dimmable to 5% via wireless wall switch. Non-controls options are 0-10v dimmable to 1% for Standard configurations, and 10% for Base configurations.
- 2 Specify LDE option only for 27L and 36L lumen packages.
- 3 Available only with Base configurations.
- 4 Specify DIM driver option only.
- 5 Not available with 347V option.
- 6 Not available with surface or suspended accessories.
- 7 Maximum of 4 luminaires per controller.
- 8 Must order IRT9015 Interact commissioning remote with each system order.
- 9 Must be installed in conjunction with a UL1008 device.
- 10 Must be ordered with an integral controls option.

### Accessories (order separately)

- **FMA14** - 1'x4' "F" mounting frame for NEMA "F" mounting
- **FSK14** - 1'x4' surface mount field installation kit (welded seams, not available with emergency options)
- **FSF14** - 1'x4' surface mount field assembly kit (field assembled, not available with emergency options)
- **SWZDT**<sup>1,4,7,8</sup> - SpaceWise wireless controller with daylighting and occupancy, advanced grouping with dwell time functionality (compatible with all 0-10V options, see SWZDT spec sheet)
- **SBAZ10-CS**<sup>1,4,7,8</sup> - Interact Ready System Bridge Accessory, refer to Philips System Bridge Accessory specification sheet for options and ordering details
- **IRT9015** - handheld remote for grouping and configuration (at least one remote required for any SWZCS installation).



# 1DLG DuaLED recessed 1x4

up to 4700 lumens


## Application

- A highly efficient, visually comfortable, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives.
- Low profile configuration is only 2-11/16" high and is compatible with virtually any plenum.
- Clean, modern design provides architectural styling compatible with virtually any area.
- Soft opal diffuser with large luminous area minimizes apparent brightness and provides high visual comfort perfect for a wide variety of general lighting applications like offices, schools, retail, or healthcare.
- Multiple lumen packages over a wide range provide significant application flexibility over light levels and/or luminaire spacing.
- A high lumen package can be used in conjunction with wide luminaire spacing to reduce luminaire quantities and overall cost while maintaining good uniformity.
- Directs a controlled amount of light to the higher angles in the room to balance the brightness of the surfaces and eliminate "cave effect" while creating the impression of a larger, brighter space without glare.
- Excellent color rendering with a CRI of 80.
- LEDs are an excellent source for use with controls since dimming or frequent switching does not degrade the performance or life of the source. External sensors are available for use.
- Designed for use with standard Grid (NEMA "G") or Narrow Grid (NEMA "NFG") ceiling T-bars. Drywall or plaster requirements can be accommodated by using an FMA14 "F" mounting frame (sold separately.)
- Listed for use in non-insulated ceilings (Type Non-IC).
- DuaLED luminaires are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers. ([www.designlights.org/QPL](http://www.designlights.org/QPL))

## Construction/Finish

- Uncomplicated design is well under 3" in depth and only requires a few parts outside of the electrical system and hardware, creating several benefits:
  - Less material required
  - Less packaging required
  - Reduced weight
  - Less energy required for construction and assembly
  - More luminaires can be shipped per truck to reduce fuel use and emissions
- Luminaire is painted after fabrication with a matte white polyester powder coating for a high quality, durable finish with no unfinished edges to create an installation hazard or potential for corrosion.
- T-bar grid clips are included for easy installation.

## Dimensions



\* EMLED and EMLED7 are 1-3/4" (45mm) deeper

## Electrical

- Driver and LED boards are easily accessible from below without tools. Multiple LED boards are individually replaceable if needed via plug-in connectors to ensure long service life.
- 0-10v dimming to 1% for Standard configurations, and 5% for Base configurations
- Emergency options are available to add even more application flexibility. Emergency models require a taller driver enclosure that increases luminaire depth.
- Five year limited luminaire warranty includes LED boards and driver (emergency driver and batteries have a three year warranty in models so equipped). Visit [www.philips.com/warranties](http://www.philips.com/warranties) for complete warranty information.
- Predicted L70 lumen maintenance up to 70,000 hours for Standard configurations and 50,000 hours for Base configurations.
- To estimate lumen output in emergency mode, multiply emergency pack wattage by luminaire efficacy, then by 1.10. Typical lumen output is 1300lm for EMLED and 850lm for EMLED7.
- cETLus listed to UL and CSA standards, suitable for damp locations.

## Enclosure

- Diffuser has large surface area for brightness control.
- Opal diffuser provides soft, comfortable lighting while maintaining high efficiency.
- Diffuser requires no frames or fasteners and can be easily removed from below without tools if needed.



## General Notes

- All options factory installed.
- All accessories are field installed.
- Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

## Energy Data

Luminaire	Catalog Number	Input Power	Efficacy
1x4 Standard	1DLG27L840	22	127
	1DLG36L840	29	123
	1DLG41L840	34	121
	1DLG47L840	39	120
1x4 Base	1DLG37B840	33	121

## Ceiling configuration



# 1DLG DuaLED recessed 1x4

up to 4700 lumens

## Wireless Controls Options

### SpaceWise DT (SWZDT)

- Standalone daylight and occupancy sensing with advanced grouping, wireless mesh networking and dwell time.
- Commissioning via compatible Android phone and Philips Field App
- Dimming via compatible Zigbee wireless wall switch only (see link below for details)
- Register for the commissioning app at <http://registration.componentcloud.philips.com/appregistration/>
- Integral sensing options may not be combined
- For more information including recommended switches, refer to the following: –

**SWZDT** – [www.usa.lighting.philips.com/systems/lighting-systems/spacewise](http://www.usa.lighting.philips.com/systems/lighting-systems/spacewise)

### Emergency Options (ER100)

- Power Sensing (Factory default) – Recommended UL924 option requires unswitched power sense line, absence of voltage on the normal circuit triggers luminaire to 100% output
- Power Interruption Detection (Field option) – Detects AC power interruption >30ms triggers 90 minute emergency mode with luminaire at 100% output

### Interact Pro scalable sensor for Foundation, Advanced & Enterprise tiers (SWZCS and an evolution of SpaceWise)

- SWZCS is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the Foundation mode (similar to SpaceWise) when configured without a gateway or in an Interact Pro Advanced or Enterprise mode if a compatible gateway is used.
- Interact Pro includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity. The App provides flexibility to choose between a gateway or non gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote onsite to identify and group devices together.
- Compatible with:
  - SWS200 wireless scene switch
  - Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
  - Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
  - LCN3110: Battery powered IP65 presence sensor, OCC sensor IA CM IP65WH
  - LCN3120: Battery powered IP65 presence & daylight sensor, OCC-DL sensor IA CM IP65 WH
- For more information on Interact Pro visit: [www.interact-lighting.com/interactproscalablesystem](http://www.interact-lighting.com/interactproscalablesystem)

### Radio only sensor (RADIO)

- Integral RADIO only sensor simply enables wireless mesh connectivity to the luminaire without any occupancy or daylight sensing.
- Ideal for applications where sensing functionality is managed by other Interact devices and the luminaire only needs to have wireless connectivity.

# 1DLG DuaLED recessed 1x4


up to 4700 lumens

Interact Pro scalable system			
	Foundation	Advanced	Enterprise
Dimming, grouping, and zoning	✓	✓	✓
Bluetooth and ZigBee enabled	✓	✓	✓
Motion sensing and daylight harvesting	✓	✓	✓
Integration with 0-10V and phase dimming fixtures	✓	✓	✓
Code compliance	✓	✓	✓
Granular dimming and dwell time	✓	✓	✓
Energy reporting and monitoring		✓	✓
Scheduling		✓	✓
Demand response		✓	✓
BMS integration (BACnet)			✓
Floor plan visualization			✓
IoT sensors for wellness			✓
IoT Apps for productivity			✓

## Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.

System level	
Total number of gateways	Unlimited
Total number of devices	200 per network
• luminaires with integrated sensors	150
• smart TLEDs	150
Total number of ZGP devices (sensors and switches)	50
• sensors	30
• switches	50
• zones and groups	64
Group level	
Recommended number of lights	40 (recommended 25)
Number of ZGP devices	5
Number of scenes	16



# 1DLG DuaLED recessed 1x4

up to 4700 lumens

## Photometry

### 1x4 DuaLED, 3700 nominal delivered lumens

### LER – 111

<b>Catalog No.</b> 1DLG37B840-4-D-UNV <b>Test No.</b> 37670 <b>S/MH</b> 1.3 <b>Lamp Type</b> LED <b>Lumens/Lamp</b> 3738 <b>Input Watts</b> 34	<b>Candela distribution</b> <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1284</td><td>1284</td><td>1284</td><td>1284</td></tr> <tr><td>5</td><td>1266</td><td>1277</td><td>1283</td><td>1277</td></tr> <tr><td>15</td><td>1223</td><td>1235</td><td>1239</td><td>1235</td></tr> <tr><td>25</td><td>1138</td><td>1149</td><td>1157</td><td>1149</td></tr> <tr><td>35</td><td>1013</td><td>1025</td><td>1035</td><td>1025</td></tr> <tr><td>45</td><td>854</td><td>876</td><td>883</td><td>876</td></tr> <tr><td>55</td><td>669</td><td>694</td><td>700</td><td>694</td></tr> <tr><td>65</td><td>466</td><td>474</td><td>471</td><td>474</td></tr> <tr><td>75</td><td>244</td><td>249</td><td>245</td><td>249</td></tr> <tr><td>85</td><td>72</td><td>64</td><td>63</td><td>64</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1284	1284	1284	1284	5	1266	1277	1283	1277	15	1223	1235	1239	1235	25	1138	1149	1157	1149	35	1013	1025	1035	1025	45	854	876	883	876	55	669	694	700	694	65	466	474	471	474	75	244	249	245	249	85	72	64	63	64	<b>Light Distribution</b> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1000</td><td>26.7</td></tr> <tr><td>0-40</td><td>1642</td><td>43.9</td></tr> <tr><td>0-60</td><td>2930</td><td>78.4</td></tr> <tr><td>0-90</td><td>3738</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1000	26.7	0-40	1642	43.9	0-60	2930	78.4	0-90	3738	100.0	<b>Average Luminance</b> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>5378</td><td>5514</td><td>5559</td></tr> <tr><td>55</td><td>5194</td><td>5384</td><td>5434</td></tr> <tr><td>65</td><td>4911</td><td>4996</td><td>4960</td></tr> <tr><td>75</td><td>4198</td><td>4276</td><td>4207</td></tr> <tr><td>85</td><td>3662</td><td>3289</td><td>3223</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	5378	5514	5559	55	5194	5384	5434	65	4911	4996	4960	75	4198	4276	4207	85	3662	3289	3223																																																		
			Vertical Angle	Horizontal Angle																																																																																																																																																			
0°	45°	90°		-45°																																																																																																																																																			
0	1284	1284	1284	1284																																																																																																																																																			
5	1266	1277	1283	1277																																																																																																																																																			
15	1223	1235	1239	1235																																																																																																																																																			
25	1138	1149	1157	1149																																																																																																																																																			
35	1013	1025	1035	1025																																																																																																																																																			
45	854	876	883	876																																																																																																																																																			
55	669	694	700	694																																																																																																																																																			
65	466	474	471	474																																																																																																																																																			
75	244	249	245	249																																																																																																																																																			
85	72	64	63	64																																																																																																																																																			
Degrees	Lumens	% Luminaire																																																																																																																																																					
0-30	1000	26.7																																																																																																																																																					
0-40	1642	43.9																																																																																																																																																					
0-60	2930	78.4																																																																																																																																																					
0-90	3738	100.0																																																																																																																																																					
Angle	End	45°	Cross																																																																																																																																																				
45	5378	5514	5559																																																																																																																																																				
55	5194	5384	5434																																																																																																																																																				
65	4911	4996	4960																																																																																																																																																				
75	4198	4276	4207																																																																																																																																																				
85	3662	3289	3223																																																																																																																																																				
Comparative yearly lighting energy cost per 1000 lumens – <b>\$2.16</b> based on 3000 hrs. and \$.08 pwr KWH.  The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.  Photometric values based on test performed in compliance with LM-79.	<b>Coefficients of Utilization</b> <b>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</b> <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr> <td></td> <td>1</td><td>109</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>93</td> </tr> <tr> <td></td> <td>2</td><td>98</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td> </tr> <tr> <td></td> <td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td> </tr> <tr> <td></td> <td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td> </tr> <tr> <td></td> <td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>52</td> </tr> <tr> <td></td> <td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td> </tr> <tr> <td></td> <td>7</td><td>65</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td> </tr> <tr> <td></td> <td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td> </tr> <tr> <td></td> <td>9</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td> </tr> <tr> <td></td> <td>10</td><td>53</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td> </tr> </tbody> </table>			Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%									RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	118	118	118	115	115	115	111	111		1	109	104	98	106	101	96	96	93		2	98	90	82	95	88	81	84	79		3	90	79	70	86	77	69	73	68		4	81	69	60	80	68	59	66	58		5	75	61	53	72	60	53	58	52		6	69	56	46	68	55	46	53	46		7	65	51	41	63	50	41	47	40		8	59	46	38	57	46	36	44	36		9	56	42	34	55	41	34	40	33		10	53	39	30	51	39	30	38	30
Ceiling (pcc)	80%				70%			50%																																																																																																																																															
	70	50	30	70	50	30	50	30																																																																																																																																															
Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																						
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																						
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																														
	1	109	104	98	106	101	96	96	93																																																																																																																																														
	2	98	90	82	95	88	81	84	79																																																																																																																																														
	3	90	79	70	86	77	69	73	68																																																																																																																																														
	4	81	69	60	80	68	59	66	58																																																																																																																																														
	5	75	61	53	72	60	53	58	52																																																																																																																																														
	6	69	56	46	68	55	46	53	46																																																																																																																																														
	7	65	51	41	63	50	41	47	40																																																																																																																																														
	8	59	46	38	57	46	36	44	36																																																																																																																																														
	9	56	42	34	55	41	34	40	33																																																																																																																																														
	10	53	39	30	51	39	30	38	30																																																																																																																																														

### 1x4 DuaLED, 3600 nominal delivered lumens

### LER – 123

<b>Catalog No.</b> 1DLG36L840-4-D-UNV-DIM <b>Test No.</b> 35432 <b>S/MH</b> 1.3 <b>Lamp Type</b> LED <b>Lumens/Lamp</b> 3567 <b>Input Watts</b> 29.0	<b>Candela distribution</b> <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1218</td><td>1218</td><td>1218</td><td>1218</td></tr> <tr><td>5</td><td>1200</td><td>1214</td><td>1222</td><td>1214</td></tr> <tr><td>15</td><td>1159</td><td>1179</td><td>1186</td><td>1179</td></tr> <tr><td>25</td><td>1077</td><td>1095</td><td>1106</td><td>1095</td></tr> <tr><td>35</td><td>954</td><td>979</td><td>992</td><td>979</td></tr> <tr><td>45</td><td>802</td><td>831</td><td>845</td><td>831</td></tr> <tr><td>55</td><td>625</td><td>655</td><td>668</td><td>655</td></tr> <tr><td>65</td><td>433</td><td>459</td><td>461</td><td>459</td></tr> <tr><td>75</td><td>243</td><td>247</td><td>246</td><td>247</td></tr> <tr><td>85</td><td>73</td><td>62</td><td>66</td><td>62</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1218	1218	1218	1218	5	1200	1214	1222	1214	15	1159	1179	1186	1179	25	1077	1095	1106	1095	35	954	979	992	979	45	802	831	845	831	55	625	655	668	655	65	433	459	461	459	75	243	247	246	247	85	73	62	66	62	<b>Light Distribution</b> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>952</td><td>26.7</td></tr> <tr><td>0-40</td><td>1563</td><td>43.8</td></tr> <tr><td>0-60</td><td>2782</td><td>78.0</td></tr> <tr><td>0-90</td><td>3568</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	952	26.7	0-40	1563	43.8	0-60	2782	78.0	0-90	3568	100.0	<b>Average Luminance</b> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>5321</td><td>5512</td><td>5607</td></tr> <tr><td>55</td><td>5111</td><td>5357</td><td>5465</td></tr> <tr><td>65</td><td>4805</td><td>5099</td><td>5116</td></tr> <tr><td>75</td><td>4402</td><td>4476</td><td>4462</td></tr> <tr><td>85</td><td>3925</td><td>3333</td><td>3526</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	5321	5512	5607	55	5111	5357	5465	65	4805	5099	5116	75	4402	4476	4462	85	3925	3333	3526																																																		
			Vertical Angle	Horizontal Angle																																																																																																																																																			
0°	45°	90°		-45°																																																																																																																																																			
0	1218	1218	1218	1218																																																																																																																																																			
5	1200	1214	1222	1214																																																																																																																																																			
15	1159	1179	1186	1179																																																																																																																																																			
25	1077	1095	1106	1095																																																																																																																																																			
35	954	979	992	979																																																																																																																																																			
45	802	831	845	831																																																																																																																																																			
55	625	655	668	655																																																																																																																																																			
65	433	459	461	459																																																																																																																																																			
75	243	247	246	247																																																																																																																																																			
85	73	62	66	62																																																																																																																																																			
Degrees	Lumens	% Luminaire																																																																																																																																																					
0-30	952	26.7																																																																																																																																																					
0-40	1563	43.8																																																																																																																																																					
0-60	2782	78.0																																																																																																																																																					
0-90	3568	100.0																																																																																																																																																					
Angle	End	45°	Cross																																																																																																																																																				
45	5321	5512	5607																																																																																																																																																				
55	5111	5357	5465																																																																																																																																																				
65	4805	5099	5116																																																																																																																																																				
75	4402	4476	4462																																																																																																																																																				
85	3925	3333	3526																																																																																																																																																				
Comparative yearly lighting energy cost per 1000 lumens – <b>\$1.95</b> based on 3000 hrs. and \$.08 pwr KWH.  The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.  Photometric values based on test performed in compliance with LM-79.	<b>Coefficients of Utilization</b> <b>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</b> <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr> <td></td> <td>1</td><td>108</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>93</td> </tr> <tr> <td></td> <td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td> </tr> <tr> <td></td> <td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td> </tr> <tr> <td></td> <td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td> </tr> <tr> <td></td> <td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>51</td> </tr> <tr> <td></td> <td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td> </tr> <tr> <td></td> <td>7</td><td>64</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td> </tr> <tr> <td></td> <td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td> </tr> <tr> <td></td> <td>9</td><td>56</td><td>41</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td> </tr> <tr> <td></td> <td>10</td><td>52</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td> </tr> </tbody> </table>			Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%									RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	118	118	118	115	115	115	111	111		1	108	104	98	106	101	96	96	93		2	97	90	82	95	88	81	84	79		3	90	79	70	86	77	69	73	68		4	81	69	60	80	68	59	66	58		5	75	61	53	72	60	53	58	51		6	69	56	46	68	55	46	53	46		7	64	51	41	63	50	41	47	40		8	59	46	38	57	46	36	44	36		9	56	41	34	55	41	34	40	33		10	52	39	30	51	39	30	38	30
Ceiling (pcc)	80%				70%			50%																																																																																																																																															
	70	50	30	70	50	30	50	30																																																																																																																																															
Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																						
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																						
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																														
	1	108	104	98	106	101	96	96	93																																																																																																																																														
	2	97	90	82	95	88	81	84	79																																																																																																																																														
	3	90	79	70	86	77	69	73	68																																																																																																																																														
	4	81	69	60	80	68	59	66	58																																																																																																																																														
	5	75	61	53	72	60	53	58	51																																																																																																																																														
	6	69	56	46	68	55	46	53	46																																																																																																																																														
	7	64	51	41	63	50	41	47	40																																																																																																																																														
	8	59	46	38	57	46	36	44	36																																																																																																																																														
	9	56	41	34	55	41	34	40	33																																																																																																																																														
	10	52	39	30	51	39	30	38	30																																																																																																																																														

# 1DLG DuaLED recessed 1x4

up to 4700 lumens

## 1x4 DuaLED, 4100 nominal delivered lumens

## LER – 121

<b>Catalog No.</b> 1DLG41L840-4-D-UNV-DIM <b>Test No.</b> 35433 <b>S/MH</b> 1.3 <b>Lamp Type</b> LED <b>Lumens/Lamp</b> 4220 <b>Input Watts</b> 34.7	<b>Candela distribution</b> <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1440</td><td>1440</td><td>1440</td><td>1440</td></tr> <tr><td>5</td><td>1418</td><td>1435</td><td>1445</td><td>1435</td></tr> <tr><td>15</td><td>1371</td><td>1394</td><td>1402</td><td>1394</td></tr> <tr><td>25</td><td>1273</td><td>1295</td><td>1308</td><td>1295</td></tr> <tr><td>35</td><td>1129</td><td>1157</td><td>1173</td><td>1157</td></tr> <tr><td>45</td><td>948</td><td>981</td><td>1000</td><td>981</td></tr> <tr><td>55</td><td>739</td><td>774</td><td>791</td><td>774</td></tr> <tr><td>65</td><td>513</td><td>543</td><td>546</td><td>543</td></tr> <tr><td>75</td><td>287</td><td>293</td><td>291</td><td>293</td></tr> <tr><td>85</td><td>86</td><td>74</td><td>78</td><td>74</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1440	1440	1440	1440	5	1418	1435	1445	1435	15	1371	1394	1402	1394	25	1273	1295	1308	1295	35	1129	1157	1173	1157	45	948	981	1000	981	55	739	774	791	774	65	513	543	546	543	75	287	293	291	293	85	86	74	78	74	<b>Light Distribution</b> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1126</td><td>26.7</td></tr> <tr><td>0-40</td><td>1849</td><td>43.8</td></tr> <tr><td>0-60</td><td>3292</td><td>78.0</td></tr> <tr><td>0-90</td><td>4222</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1126	26.7	0-40	1849	43.8	0-60	3292	78.0	0-90	4222	100.0	<b>Average Luminance</b> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>6293</td><td>6508</td><td>6636</td></tr> <tr><td>55</td><td>6049</td><td>6329</td><td>6472</td></tr> <tr><td>65</td><td>5690</td><td>6033</td><td>6057</td></tr> <tr><td>75</td><td>5210</td><td>5303</td><td>5279</td></tr> <tr><td>85</td><td>4646</td><td>3957</td><td>4183</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	6293	6508	6636	55	6049	6329	6472	65	5690	6033	6057	75	5210	5303	5279	85	4646	3957	4183																																																	
Vertical Angle	Horizontal Angle																																																																																																																																																					
	0°	45°	90°	-45°																																																																																																																																																		
0	1440	1440	1440	1440																																																																																																																																																		
5	1418	1435	1445	1435																																																																																																																																																		
15	1371	1394	1402	1394																																																																																																																																																		
25	1273	1295	1308	1295																																																																																																																																																		
35	1129	1157	1173	1157																																																																																																																																																		
45	948	981	1000	981																																																																																																																																																		
55	739	774	791	774																																																																																																																																																		
65	513	543	546	543																																																																																																																																																		
75	287	293	291	293																																																																																																																																																		
85	86	74	78	74																																																																																																																																																		
Degrees	Lumens	% Luminaire																																																																																																																																																				
0-30	1126	26.7																																																																																																																																																				
0-40	1849	43.8																																																																																																																																																				
0-60	3292	78.0																																																																																																																																																				
0-90	4222	100.0																																																																																																																																																				
Angle	End	45°	Cross																																																																																																																																																			
45	6293	6508	6636																																																																																																																																																			
55	6049	6329	6472																																																																																																																																																			
65	5690	6033	6057																																																																																																																																																			
75	5210	5303	5279																																																																																																																																																			
85	4646	3957	4183																																																																																																																																																			
Comparative yearly lighting energy cost per 1000 lumens – <b>\$1.97</b> based on 3000 hrs. and \$.08 pwr KWH.  The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.  Photometric values based on test performed in compliance with LM-79.	<b>Coefficients of Utilization</b> <b>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</b> <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td>70</td><td>50</td><td>30</td> <td>70</td><td>50</td><td>30</td> <td>50</td><td>30</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr><td>1</td><td>108</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>96</td><td>93</td></tr> <tr><td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td><td>79</td></tr> <tr><td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td><td>68</td></tr> <tr><td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td><td>58</td></tr> <tr><td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>51</td><td>51</td></tr> <tr><td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td><td>46</td></tr> <tr><td>7</td><td>64</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td><td>40</td></tr> <tr><td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td><td>36</td></tr> <tr><td>9</td><td>56</td><td>41</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td><td>33</td></tr> <tr><td>10</td><td>52</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td><td>30</td></tr> </tbody> </table>			Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	70	50	30	70	50	30	50	30	RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	118	118	118	115	115	115	111	111	1	108	104	98	106	101	96	96	96	93	2	97	90	82	95	88	81	84	79	79	3	90	79	70	86	77	69	73	68	68	4	81	69	60	80	68	59	66	58	58	5	75	61	53	72	60	53	58	51	51	6	69	56	46	68	55	46	53	46	46	7	64	51	41	63	50	41	47	40	40	8	59	46	38	57	46	36	44	36	36	9	56	41	34	55	41	34	40	33	33	10	52	39	30	51	39	30	38	30	30
Ceiling (pcc)	80%				70%			50%																																																																																																																																														
	70	50	30	70	50	30	50	30																																																																																																																																														
Wall (pw)	70	50	30	70	50	30	50	30																																																																																																																																														
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																					
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																													
1	108	104	98	106	101	96	96	96	93																																																																																																																																													
2	97	90	82	95	88	81	84	79	79																																																																																																																																													
3	90	79	70	86	77	69	73	68	68																																																																																																																																													
4	81	69	60	80	68	59	66	58	58																																																																																																																																													
5	75	61	53	72	60	53	58	51	51																																																																																																																																													
6	69	56	46	68	55	46	53	46	46																																																																																																																																													
7	64	51	41	63	50	41	47	40	40																																																																																																																																													
8	59	46	38	57	46	36	44	36	36																																																																																																																																													
9	56	41	34	55	41	34	40	33	33																																																																																																																																													
10	52	39	30	51	39	30	38	30	30																																																																																																																																													

## 1x4 DuaLED, 4700 nominal delivered lumens

## LER – 120

<b>Catalog No.</b> 1DLG47L840-4-D-UNV-DIM <b>Test No.</b> 35436 <b>S/MH</b> 1.3 <b>Lamp Type</b> LED <b>Lumens/Lamp</b> 4706 <b>Input Watts</b> 39.1	<b>Candela distribution</b> <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1606</td><td>1606</td><td>1606</td><td>1606</td></tr> <tr><td>5</td><td>1581</td><td>1603</td><td>1611</td><td>1603</td></tr> <tr><td>15</td><td>1528</td><td>1556</td><td>1564</td><td>1556</td></tr> <tr><td>25</td><td>1419</td><td>1447</td><td>1459</td><td>1447</td></tr> <tr><td>35</td><td>1257</td><td>1292</td><td>1307</td><td>1292</td></tr> <tr><td>45</td><td>1056</td><td>1096</td><td>1114</td><td>1096</td></tr> <tr><td>55</td><td>823</td><td>865</td><td>881</td><td>865</td></tr> <tr><td>65</td><td>571</td><td>606</td><td>606</td><td>606</td></tr> <tr><td>75</td><td>319</td><td>325</td><td>324</td><td>325</td></tr> <tr><td>85</td><td>96</td><td>81</td><td>86</td><td>81</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1606	1606	1606	1606	5	1581	1603	1611	1603	15	1528	1556	1564	1556	25	1419	1447	1459	1447	35	1257	1292	1307	1292	45	1056	1096	1114	1096	55	823	865	881	865	65	571	606	606	606	75	319	325	324	325	85	96	81	86	81	<b>Light Distribution</b> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1256</td><td>26.7</td></tr> <tr><td>0-40</td><td>2062</td><td>43.8</td></tr> <tr><td>0-60</td><td>3671</td><td>78.0</td></tr> <tr><td>0-90</td><td>4708</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1256	26.7	0-40	2062	43.8	0-60	3671	78.0	0-90	4708	100.0	<b>Average Luminance</b> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>7007</td><td>7274</td><td>7394</td></tr> <tr><td>55</td><td>6734</td><td>7075</td><td>7205</td></tr> <tr><td>65</td><td>6335</td><td>6728</td><td>6732</td></tr> <tr><td>75</td><td>5785</td><td>5887</td><td>5878</td></tr> <tr><td>85</td><td>5141</td><td>4345</td><td>4603</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	7007	7274	7394	55	6734	7075	7205	65	6335	6728	6732	75	5785	5887	5878	85	5141	4345	4603																																																	
Vertical Angle	Horizontal Angle																																																																																																																																																					
	0°	45°	90°	-45°																																																																																																																																																		
0	1606	1606	1606	1606																																																																																																																																																		
5	1581	1603	1611	1603																																																																																																																																																		
15	1528	1556	1564	1556																																																																																																																																																		
25	1419	1447	1459	1447																																																																																																																																																		
35	1257	1292	1307	1292																																																																																																																																																		
45	1056	1096	1114	1096																																																																																																																																																		
55	823	865	881	865																																																																																																																																																		
65	571	606	606	606																																																																																																																																																		
75	319	325	324	325																																																																																																																																																		
85	96	81	86	81																																																																																																																																																		
Degrees	Lumens	% Luminaire																																																																																																																																																				
0-30	1256	26.7																																																																																																																																																				
0-40	2062	43.8																																																																																																																																																				
0-60	3671	78.0																																																																																																																																																				
0-90	4708	100.0																																																																																																																																																				
Angle	End	45°	Cross																																																																																																																																																			
45	7007	7274	7394																																																																																																																																																			
55	6734	7075	7205																																																																																																																																																			
65	6335	6728	6732																																																																																																																																																			
75	5785	5887	5878																																																																																																																																																			
85	5141	4345	4603																																																																																																																																																			
Comparative yearly lighting energy cost per 1000 lumens – <b>\$2.00</b> based on 3000 hrs. and \$.08 pwr KWH.  The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.  Photometric values based on test performed in compliance with LM-79.	<b>Coefficients of Utilization</b> <b>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</b> <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td>70</td><td>50</td><td>30</td> <td>70</td><td>50</td><td>30</td> <td>50</td><td>30</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr><td>1</td><td>108</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>96</td><td>93</td></tr> <tr><td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td><td>79</td></tr> <tr><td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td><td>68</td></tr> <tr><td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td><td>58</td></tr> <tr><td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>51</td><td>51</td></tr> <tr><td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td><td>46</td></tr> <tr><td>7</td><td>64</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td><td>40</td></tr> <tr><td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td><td>36</td></tr> <tr><td>9</td><td>56</td><td>41</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td><td>33</td></tr> <tr><td>10</td><td>52</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td><td>30</td></tr> </tbody> </table>			Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	70	50	30	70	50	30	50	30	RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	118	118	118	115	115	115	111	111	1	108	104	98	106	101	96	96	96	93	2	97	90	82	95	88	81	84	79	79	3	90	79	70	86	77	69	73	68	68	4	81	69	60	80	68	59	66	58	58	5	75	61	53	72	60	53	58	51	51	6	69	56	46	68	55	46	53	46	46	7	64	51	41	63	50	41	47	40	40	8	59	46	38	57	46	36	44	36	36	9	56	41	34	55	41	34	40	33	33	10	52	39	30	51	39	30	38	30	30
Ceiling (pcc)	80%				70%			50%																																																																																																																																														
	70	50	30	70	50	30	50	30																																																																																																																																														
Wall (pw)	70	50	30	70	50	30	50	30																																																																																																																																														
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																					
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																													
1	108	104	98	106	101	96	96	96	93																																																																																																																																													
2	97	90	82	95	88	81	84	79	79																																																																																																																																													
3	90	79	70	86	77	69	73	68	68																																																																																																																																													
4	81	69	60	80	68	59	66	58	58																																																																																																																																													
5	75	61	53	72	60	53	58	51	51																																																																																																																																													
6	69	56	46	68	55	46	53	46	46																																																																																																																																													
7	64	51	41	63	50	41	47	40	40																																																																																																																																													
8	59	46	38	57	46	36	44	36	36																																																																																																																																													
9	56	41	34	55	41	34	40	33	33																																																																																																																																													
10	52	39	30	51	39	30	38	30	30																																																																																																																																													



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
 400 Crossing Blvd, Suite 600  
 Bridgewater, NJ 08807  
 Telephone 855-486-2216

Signify Canada Ltd.  
 281 Hillmount Road,  
 Markham, ON, Canada L6C 2S3  
 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.