

# Vaya Flood LP G2 White

Low power architectural LED flood light for crisp white lighting effects

Date: \_\_\_\_\_  
Type: \_\_\_\_\_  
Firm Name: \_\_\_\_\_  
Project: \_\_\_\_\_

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

- Powerful - Throwing light with 10lx up to 67 m / 1fc up to 218 ft high, this narrow beam luminaire is a powerful solution for any size of project.
- Compact - Unlike other flood lighting solutions, the Vaya Flood series are compact sized & light-weight luminaires, that combine an aluminium die-cast housing which is both anodized and powder coated to protect against corrosion, tempered glass, pressure equalizing air vents and IP66 outdoor rating, making the product robust against harsh outdoor environments.



[Product page](#)

Beam Angle	10°, 20°, 40°
Lumens*	3,123 to 3,797
Efficacy	73 to 87.9
CRI†	82
Color Temperature§	3000 K, 4000 K

Input Voltage	100 to 240 VAC, 50/60 Hz
Power Consumption	44 W
Weight	3.53 kg (7.8 lb)
Housing Material	Die-cast aluminium, dark grey powder-coated finish
Approbations	CE, PSE, CQC, RCM
Environment	Dry/Damp/Wet Location, IP66
Applications	Flood Lighting, Spot Lighting, Wall Washing

## 3000 K Specification Sheets

Custom products information available

PDF Download	Beam Angle	Lumens*	Efficacy	CRI†	Item Number	12 NC
<a href="#">3000 K, 10°, CE/CQC/PSE</a>	10°	3,483	81.4	82	350-000015-00	912400133925
<a href="#">3000 K, 20°, CE/CQC/PSE</a>	20°	3,357	79.7	82	350-000015-01	912400133926
<a href="#">3000 K, 40°, CE/CQC/PSE</a>	40°	3,123	73	82	350-000015-02	912400133957

**COLORKINETICS**  
vaya series

## 4000 K Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy	CRI <sup>†</sup>	Item Number	12 NC
<a href="#">4000 K, 10°, CE/CQC/PSE</a>	10°	3,797	87.9	82	350-000015-08	912400133927
<a href="#">4000 K, 20°, CE/CQC/PSE</a>	20°	3,688	87.9	82	350-000015-09	912400133934
<a href="#">4000 K, 40°, CE/CQC/PSE</a>	40°	3,387	85.7	82	350-000015-10	912400133937

\* Lumen output measurements comply with IES LM-79-08 testing procedures.

<sup>‡</sup> Correlated color temperature (CCT) complies with ANSI C78.377-2008 for the chromaticity of solid state lighting products.

<sup>†</sup> CRI refers to CRI Ra value, CRI R9 refers to R9 value in accordance with IESNA LM-79 standards.

---

**COLORKINETICS** vaya series

© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics  
www.colorkinetics.com/vaya