

# ArchiPoint iColor Powercore

Exterior daylight-visible LED point with intelligent color light

Date: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Firm Name: \_\_\_\_\_  
 Project: \_\_\_\_\_

ArchiPoint iColor Powercore is a daylight-visible, exterior-rated LED point of light ideally suited for a range of direct-view and beacon applications, as well as for accent applications such as path and marker lighting. These versatile low-profile luminaires display large-scale video, graphics, and intricately designed effects in a host of settings, including architectural, retail, and entertainment installations. ArchiPoint iColor Powercore offers high-intensity output with the efficiency and cost-effectiveness of Powercore technology in a rugged, aluminium housing.

- Daylight visible—Outputs up to 25,150 nits of intelligent color light in a weatherproof, low-profile housing, perfect for large-scale video, dynamic effects, and other direct-view applications. Easily visible in brightly lit urban environments and daylight—even in direct sunlight.
- Direct view or illumination—Supports large-scale video for architectural, media façade, and advertising applications for viewing day or night. Indirect illumination delivers high levels of intensity for beacon, paths and marker lighting.
- Multiple mounting base options—Conduit Mounting Base offers side and back openings for flexible connections in surface-mounted installations. Concealed Conduit Mounting Base hides all conduit and wiring behind the mounting surface for a clean look.



[Product page](#)

Viewing	125°, 150°
Lumens*	501 to 774
LED Channels	Red/Green/Blue
Input Voltage	100 to 240 VAC, auto-ranging, 50/60 Hz
Power Consumption	25 W

Weight	1.5 kg (3.2 lb)
Housing Material	Die-cast aluminium with silver gray powder-coated finish
Approbations	UL/cUL, FCC Class A, CE
Environment	Dry/Damp/Wet Location, IP66
Applications	Direct View

## Specification Sheets

PDF Download	Item Number	12 NC	Mounting Base Item Number	Mounting Base 12 NC
<a href="#">Clear Flat Lens with Concealed Conduit Mounting Base, 3/4 in NPT (U.S. trade size conduit)</a>	123-000022-01	910503702580	123-000152-02	910503702576
<a href="#">Clear Flat Lens with Concealed Conduit Mounting Base, M25 (metric size conduit)</a>	123-000022-01	910503702580	123-000152-03	910503702577
<a href="#">Clear Flat Lens with Conduit Mounting Base, 3/4 in NPT (U.S. trade size conduit)</a>	123-000022-01	910503702580	123-000152-00	910503702574
<a href="#">Clear Flat Lens with Conduit Mounting Base, M25 (metric size conduit)</a>	123-000022-01	910503702580	123-000152-01	910503702575
<a href="#">Translucent Dome Lens with Concealed Conduit Mounting Base, 3/4 in NPT (U.S. trade size conduit)</a>	123-000022-00	910503702579	123-000152-02	910503702576
<a href="#">Translucent Dome Lens with Concealed Conduit Mounting Base, M25 (metric size conduit)</a>	123-000022-00	910503702579	123-000152-03	910503702577
<a href="#">Translucent Dome Lens with Conduit Mounting Base, 3/4 in NPT (U.S. trade size conduit)</a>	123-000022-00	910503702579	123-000152-00	910503702574
<a href="#">Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)</a>	123-000022-00	910503702579	123-000152-01	910503702575

\* Lumen output measurements comply with IES LM-79-08 testing procedures.



© 2021 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics  
[www.colorkinetics.com/lis/rgb/archipoint/](http://www.colorkinetics.com/lis/rgb/archipoint/)