

by (s) ignify

Wall Mount

GeoForm

GCM LED wall sconce





Gardco GeoForm cylinder medium LED wall sconce features a sleek cylindrical shape that will complement or enhance a range of architectural styles. GeoForm Cylinder is available with two light engines: precision optics which feature type 2, 3, and 4 distributions, as well as light effects optics which offer wall wash, spot, and pencil beam distributions. GeoForm with light effects can be used in up, down, or up and down configurations. Emergency battery backup option provides path-of-egress illumination, and multiple control options further enhance energy savings.

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notos:	

Ordering guide

example: GCM-B01-830-WAW-U-SPT-UNV-BZ

Luminaire GCM	Configuration Down (nom. lumens)	Color Temperature	Distribution Down	Configu	uration Up	Distribution Up	Voltage
GCM GeoForm Cylinder Medium	Precision Plus optics (Down only) A01¹ 1,500 lumens A02¹ 2,500 lumens A03 4,000 lumens A04 5,000 lumens A05 6,000 lumens Light Effects optics (Down only) B01¹ 700 lumens B02¹ 1,000 lumens B03¹ 2,200 lumens Light Effects optics (Up AND down only) B04¹ 1,400 lumens B05¹ 2,000 lumens	830 80CRI 3000K 840 80CRI 4000K 740 70CRI 4000K 750 70CRI 5000K 830 80CRI 3000K 840 80CRI 4000K	T2M Type 2 down only T3M Type 3 down only T4M Type 4 down only WAW Wall Wash SPT Spot PEN Pencil Beam WAW Wall Wash SPT Spot	None L	Leave blank for down only Leave blank for down only Uplight lumen output,	None Leave blank for down only None Leave blank for down only WAW Wall Wash SPT Spot	120 120V 208 208V 240 240V 277 277V 347 347V 480 480V UNV 120-277V (50/60Hz) HVU 347-480V (50/60Hz)
Dimming Contro	B06¹ 4,400 lumens	840 80CRI 4000K Electrical	PEN Pencil Beam	r	match downlight configuration	PEN Pencil Beam	
driver DLEA ² Dimmi (contr	blank (10kV kA dimming standard) ng Leads Externally Accessible ols by others) Adjustable Wattage Selector	FS1 Single Fuse (120 FS2 Double Fuse (20 FS3 Double fuse Cal (208V, 240V, or	dard) r 20kV/10kA (option) r, 277, or 347VAC) 08V, 240V, or 480V) nadian double pull	EC ⁷ E	Leave blank Emergency Battery Pack (-20°C to 40°C) 120 or 277V only	Textured BK Black WH White BZ Bronze DG Dark Gray MG Medium Gray Customer specified RAL Specify optional col (ex: OC-LGP or OC- CC Custom Color (must requires factory que	RAL7024) supply color chip,

- 1. Emergency Battery Pack not available.
- 2. Only one option can be selected from Dimming Controls column.
- 3. Not available in 480V.

- 4. Only available in 120- 277V or UNV.
- 5. Only available in 120–277, must specify voltage.
- 6. 120-277V only. Luminaire must be ordered with DLEA option if using WIAP.
- 7. EC option requires 120 OR 277V.

Luminaire Accessories (order separately)

GF-WS-BK Wall Mounted Box for surface conduit, painted black.








Wall sconce

Dimensions


GCM Medium Cylinder


Standard

Weight: 8.4 Lbs (3.8kg)




Light Effect





Accessory details

GF-WS-BK Details



Wall sconce

GCM Lumen values

3000K, 80CRI

			Average		Туре 2М			Туре 3М			Type 4M	
Ordering Code	сст	CRI	System Wattage	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)
GCM-A01-830	3000	80	10	1483	B1-U0-G1	145	1503	B1-U0-G1	147	1467	B0-U0-G1	144
GCM-A02-830	3000	80	17	2478	B1-U0-G1	147	2511	B1-U0-G1	149	2452	B1-U0-G1	145
GCM-A03-830	3000	80	25	3522	B1-U0-G1	143	3570	B1-U0-G1	145	3485	B1-U0-G1	142
GCM-A04-830	3000	80	34	4601	B1-U0-G1	137	4664	B1-U0-G1	139	4553	B1-U0-G1	136
GCM-A05-830	3000	80	41	5501	B2-U0-G2	134	5575	B2-U0-G2	136	5443	B1-U0-G1	132

4000K, 80CRI

	Average		Average	Type 2M			Туре ЗМ			Туре 4М		
Ordering Code	сст	CRI	System Wattage	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)
GCM-A01-840	4000	80	10	1537	B1-U0-G1	151	1558	B1-U0-G1	153	1521	B0-U0-G1	149
GCM-A02-840	4000	80	17	2569	B1-U0-G1	152	2604	B1-U0-G1	154	2542	B1-U0-G1	151
GCM-A03-840	4000	80	25	3652	B1-U0-G1	148	3701	B1-U0-G1	150	3613	B1-U0-G1	147
GCM-A04-840	4000	80	34	4771	B1-U0-G1	142	4835	B2-U0-G2	144	4721	B1-U0-G1	141
GCM-A05-840	4000	80	41	5703	B2-U0-G2	139	5780	B2-U0-G2	141	5643	B1-U0-G2	137

4000K, 70CRI

			Average		Туре 2М			Туре 3М			Type 4M		
Ordering Code	сст	CRI	System Wattage	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	
GCM-A01-740	4000	70	10	1732	B1-U0-G1	170	1756	B1-U0-G1	172	1714	B1-U0-G1	168	
GCM-A02-740	4000	70	17	2895	B1-U0-G1	171	2934	B1-U0-G1	174	2865	B1-U0-G1	170	
GCM-A03-740	4000	70	25	4115	B1-U0-G1	167	4171	B1-U0-G1	170	4072	B1-U0-G1	166	
GCM-A04-740	4000	70	34	5376	B2-U0-G2	160	5449	B2-U0-G2	163	5320	B1-U0-G1	159	
GCM-A05-740	4000	70	41	6427	B2-U0-G2	156	6514	B2-U0-G2	158	6359	B1-U0-G2	155	

5000K, 70CRI

			Average	Туре 2М			Туре 3М			Type 4M			
Ordering Code	сст	CRI	System Wattage	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	
GCM-A01-750	5000	70	10	1663	B1-U0-G1	163	1686	B1-U0-G1	165	1646	B1-U0-G1	161	
GCM-A02-750	5000	70	17	2780	B1-U0-G1	165	2818	B1-U0-G1	167	2751	B1-U0-G1	163	
GCM-A03-750	5000	70	25	3952	B1-U0-G1	161	4005	B1-U0-G1	163	3910	B1-U0-G1	159	
GCM-A04-750	5000	70	34	5163	B2-U0-G2	154	5233	B2-U0-G2	156	5109	B1-U0-G1	153	
GCM-A05-750	5000	70	41	6172	B2-U0-G2	150	6255	B2-U0-G2	152	6107	B1-U0-G2	149	

LED Wattage and Lumen Values (Emergency Mode)

				Туре 2М		Туре	∍ 3M	Type 4M		
Ordering Code	сст	CRI	Avg. System Wattage (W)		BUG Rating	Lumen Output	BUG Rating	Lumen Output	BUG Rating	
GCM-AXX-740-X-EM	4000	70	6	1000	B0-U0-G0	1014	B0-U0-G1	838	B0-U0-G0	
GCM-AXX-750-X-EM	5000	70	6	960	B0-U0-G0	973	B0-U0-G1	804	B0-U0-G0	
GCM-AXX-830-X-EM	3000	80	6	856	B0-U0-G0	868	B0-U0-G1	717	B0-U0-G0	
GCM-AXX-840-X-EM	4000	80	6	887	B0-U0-G0	899	B0-U0-G1	743	B0-U0-G0	

Wall sconce

Light Effects Optics 3000K, 80 CRI (Up or Down)

		Average				· · · · · · · · · · · · · · · · · · ·		Spot	(SPT)	Pencil Beam (PEN)		
Ordering Code	ССТ	CRI	System Wattage	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)			
GCM-B01-830	3000	80	8	699	88	767	97	66	8			
GCM-B02-830	3000	80	18	1397	78	1534	86	133	7			
GCM-B03-830	3000	80	30	2446	82	2685	90	232	8			

Light Effects Optics 3000K, 80 CRI (Up and Down)

			Average	Wall Was	h (WAW)	Spot	(SPT)	Pencil Be	am (PEN)
Ordering Code	сст	CRI	System Wattage	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)
GCM-B04-830	3000	80	16	1397	88	1534	97	133	8
GCM-B05-830	3000	80	36	2795	78	3068	86	266	7
GCM-B06-830	3000	80	60	4891	82	5369	90	465	8


Light Effects Optics 4000K, 80 CRI (Up or Down)


			Average	Wall Was	h (WAW)	Spot	(SPT)	Pencil Be	am (PEN)
Ordering Code	сст	CRI	System Wattage	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)
GCM-B01-840	4000	80	8	734	92	805	101	70	9
GCM-B02-840	4000	80	18	1467	82	1611	90	139	8
GCM-B03-840	4000	80	30	2568	86	2819	94	244	8


Light Effects Optics 4000K, 80 CRI (Up and Down)

			Average	Wall Wash (WAW)		Spot	(SPT)	Pencil Beam (PEN)		
Ordering Code	сст	CRI	System Wattage	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	
GCM-B04-840	4000	80	16	1467	92	1611	101	139	9	
GCM-B05-840	4000	80	36	2935	82	3222	90	279	8	
GCM-B06-840	4000	80	60	5136	86	5638	94	488	8	

Optical Distributions







Type 2 Type 3 Type 3

Wall sconce

Specifications

Construction

Main body housing and door frame made of low copper die cast aluminum alloy for a high resistance to corrosion. Removable die cast backplate to allow access to driver or other electronic components for servicing. The housing acts as the main heat sinking component, for maximum thermal dissipation. Giving the freedom to have a clean minimalist aesthetic design while allowing it to house emergency battery backup equipment and various other options. Luminaire housing rated to IP65, tested in accordance to Section 9 of IEC 60598-1

IK Rating IK08 high impact resistance rating for both the housing and optics

IP Rating IP65 rated luminaire with IP66 rated light engine

Light engine

Electrical components are RoHS compliant, IP66 sealed light engine equipped LEDs tested by ISO 17025-2005 accredited lab in accordance with IESNA LM-80 guidelines in compliance with EPA ENERGY STAR, extrapolations in accordance with IESNA TM-21. Metal core board ensures greater heat transfer and longer lifespan.

LED Module

Precision plus LED printed circuit board assembly made of 20 LEDs populated on aluminum metal clad board for optimal thermal dissipation ensuring long LED life. Light Effects feature single COB LED array.

Optical System

Precision plus optics composed of high performance UV stabilized for optical grade polymer refractor lenses to achieve desired distribution optimized spacing, target lumens and a superior lighting uniformity. Performance tested per LM-63, LM-79 and TM-15 (IESNA) certifying its photometric performance. 0% uplight and UO per IESNA TM-15. Light effects optics composed of low iron tempered clear glass with molded gasket attached to lens without tools or RTV. Lenses provide narrow spot, pencil beam, and wall wash optical distributions.

Mounting

Mounting is achieved through integral back plate that features a hook and lock quick mount plate that secures with two set screws from bottom of luminaire. Mounting plate is located in the center of the luminaire body. Luminaire ships fully assembled, ready to install.

Installation

GeoForm features an integral hook on its mounting plate which allows a single installer to perform wiring without assistance. See installation instructions for complete details.

Control options

0-10V dimming (DLEA): Access to 0-10V dimming leads supplied through back of luminaire (for secondary dimming controls by others). Cannot be used with other control options.

Field Adjustable Wattage Selector (FAWS): Luminaire equipped with the ability to manually adjust the wattage in the field to reduce total luminaire lumen output and light levels. Comes pre-set to the highest position lumen output selected. Use chart below to estimate reduction in lumen output desired. Cannot be used with other control options or motion response.

FAWS Position	Percent of Typical Lumen Output	FAW
1	25%	
2	50%	
3	55%	
4	65%	
5	75%	

tput	FAWS Position	Percent of Typical Lumen Output
	6	80%
	7	85%
	8	90%
	9	95%
	10	100%

Note: Typical value accuracy +/- 5%

Emergency Battery Backup (EC): Emergency battery pack included integral to the luminaire, allowing for a consistent look between emergency and non-emergency luminaires. EC is cold weather rated for use in ambient temperature conditions from -20°C (-4°F) to 40°C (104°F) designed to have a secondary driver with relay to immediately detect AC power loss to power luminaire for a minimum of 90 minutes from the time power is lost. Available with 120V or 277V.

Electrica

Driver: Driver efficiency (>90% standard). 120-480V available (restrictions apply). Open/short circuit protection. 0-10V dimming driver down to 10% standard. RoHS compliant.

Button Photocontrol (PCB): Button style design for internal luminaires mounting applications. The photocontrol is constructed of a high impact UV stabilized polycarbonate housing. Rated voltage of 120V or 208-277V with a load rating of 1000 VA. The photocell will turn on with 1-4Fc of ambient light.

Surge protection (SP1/SP2): Each luminaire is provided as standard with surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/5kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid-State Street Lighting Consortium) Model Specification for LED Roadway Luminaires Appendix D Electrical Immunity High Test Level 10kV / 5kA. Optional 20kV is available for additional protection.

Listings

UL/cUL listed to the UL 1598 standard, suitable for wet locations when mounted downward facing. GeoForm with Precision Plus optics listed for damp locations when inverted. GeoForm with light effects optics listed for wet location in up or down orientation. Suitable for use in ambient temperatures from ~40° to 40°C (~40° to 104°F). GeoForm configurations with Precision Plus optics are qualified under Design Lights Consortium® Premium category. Consult DLC Qualified Products List on Specific Classifications and for more details. CCTs 3000K and warmer are IDA Dark Sky Approved. FCC Compliant.

Finish

Each standard color luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) textured polyester powder coat finish. The surface treatment achieves a minimum of 1000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard. Standard colors include bronze (BZ), black (BK), white (WH), dark gray (DGY), and medium gray (MGY). Consult factory for specs on optional or custom colors.

Service Tag

Each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making installation and maintenance operations faster and easier, no matter what stage of the luminaire's lifetime. Just download the APP and register your product right away. For more details visit: signify.com

Warranty

GeoForm luminaires feature a 5-year limited warranty. See signify.com/warranties for complete details and exclusions.

Wall sconce

Predicted Lumen Depreciation Data

Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. L_{70} is the predicted time when LED performance depreciates to 70% of initial lumen output. Calculated per IESNA TM21-11. Published L_{70} hours limited to 6 times actual LED test hours

Ambient Temp°C	Drive current	L ₇₀ per TM-21	Lumen Maintenance % at 60,000 hrs
25°C	up to 1200 mA	>102,000 hours	>91%

Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

Il trademarks are owned by Signify Holding or their respective owners.