



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

#### Ordering Information

Catalog No.	Finish	Mountings	Compatible Plug in Breakers
FXS99	Silver	Drywall and J-box mount only. Connects to Tangent Suspended Track units.	Compatible with PLD Plug in Breakers. Refer to Spec Sheet PLD120 for complete offering.

#### Features

- Wire Cover:** Plastic Polycarbonate
- Mounting Plate:** .060 thick galvanized steel.
- Round Knock Out:** 7/8 dia. knockouts for electrical feed. Circuit can be fed into connector. Offset to accommodate grid ceiling runners.
- Ground Terminals:** (3) ground terminals.
- Circular Knock Out:** Allows feeding from j-box with proper UL area for splice inspection without removing connector from j-box.
- Mounting Holes:** (4) holes on 3.5 in. centers secure connector to j-box or mounting surface.
- Tangent Track Connector:** (2) assemblies keyed to maintain proper polarity with track. Installs into track providing electrical and mechanical connection.
- Circuit Breaker Opening:** One can be installed. Limits the amount of electrical load that can be placed on the circuit. Can be used as standard On/Off switch.
- Electrical Wires:** Three 12ga wires in metal sheathing at a 10' length.

- Tamperproof Locking Screw:** (2) Mechanically secures connector into track. Color matches fixture color.

#### Finish

All Painted finishes are baked enamel.

#### Electrical

Capacity is 120 volts, 60Hz. All Tangent Track luminaires are polarized and continuously grounded throughout. Electrical conductors are concealed in an insulating liner. Intended for wiring to branch circuit building wire with ground. All wiring must be in accordance with National and Local Codes.

#### Labels

U.L. listed. Note: to assure full compliance with local energy codes and regulations check with your local code official.

