


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_



### Ordering Guide

Example: CF14 T A GF 2 N D 70S E F

<b>Product Code</b>	CF14	Westbrooke	
<b>Mounting</b>	T	Top Arm	
<b>Finish</b>	A B H J	Black White Bronze Green	
<b>Lens</b>	GF KL KS TS	Flat Glass Ribbed Acrylic Teardrop Acrylic Sag Textured Polycarbonate Sag	
<b>Optics</b>	2 3 4 5	Type II Type III Type IV Type V	*1
<b>Photo Control</b>	N	None	
<b>Socket</b>	D G	Medium Mogul	
<b>Wattage</b>	70S 100S 150S 200S 250S 400S 70H 100H 150H 250H 320H	70W HPS 100W HPS 150W HPS 200W HPS 250W HPS 400W HPS 70W MH 100W MH 150W MH 250W MH 320W PMH	*3,5 *3 *2,3 *4 *4 *3 *2,3
<b>Voltage</b>	E F G H K	120V 208V 240V 277V 347V	
<b>Options</b>	F	Fluted Spinning	

\*1 Type V Optics (5) available with Medium base (D) socket only.  
 \*2 Available with Flat Glass Lens (GF) only.  
 \*3 Available with Mogul base (G) socket only.  
 \*4 Available with Medium base (D) socket only.  
 \*5 Not available in 347V (K).

### Specifications

#### HOUSING:

413F, Low-Copper cast aluminum. 0.090" thick spun aluminum. Hinged lens frame is cast aluminum with stainless steel spring latch for tool-less lamp access. A weatherproof ballast assembly isolates the ballast from water and heat for longer life. Decorative fluted aluminum spinning available for ballast housing. All non-ferrous fasteners prevent corrosion and ensure longer life.

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

# CF14 Westbrooke

## MH/HPS Pendant

### Specifications

---

#### OPTICAL ASSEMBLY:

Type II Cutoff. Type III Cutoff. Type IV Cutoff. Type V Cutoff. Precision formed, segmented specular aluminum internal cutoff reflector with horizontal lamp mounting. Reflector is rotatable in 90° increments. U.V. stabilized, clear acrylic sag lens. Clear tempered flat glass lens. U.V. stabilized acrylic long globe with Optical Rib (TM) technology. U.V. stabilized, clear, textured polycarbonate sag lens.

#### LAMPING:

MH Mogul base: ED28. 70W-150W HPS Mogul base: ED23.5. 200-400W HPS Mogul base: E18. MH and HPS Medium base: E17.

#### ELECTRICAL ASSEMBLY:

4kv rated mogul base porcelain socket. Nickel-plated screw shell with center contact. Key-slotted Ballast Assembly with stainless steel plungers and Quick Disconnects for tool-less removal. 4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

#### BALLAST:

All HID ballasts are core and coil and regulated with power factors better than 90% (HPF). Ballast provides +/- 5% lamp power regulation with +/- 10% input voltage regulation. Ballasts are factory pre-wired and tested. Metal halide ballasts are capable of starting at -20° F or -30° C and HPS at -40°F or -40°C. NOTE: All ballasts are EISA / Title 20 / Title 24 compliant where applicable.

#### MOUNTING:

Top Arm Mount (T). Arm sold separately.

#### CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

#### WARRANTY:

Three-year limited warranty.

#### Height :

Flat Glass: 22 1/4" (57cm)

#### Height :

Polycarbonate Sag: 25" (64cm)

#### Height :

Acrylic Sag Lens: 27 3/4" (70cm)

#### Height :

Teardrop Globe: 36 1/2" (93cm)

#### Width:

21" (53cm)

#### Max. EPA:

1.6 sq. ft.

#### Max. Weight:

44 lbs

#### IESNA Classifications:

Full Cutoff: Flat Glass lens

#### IESNA Classifications:

Cutoff: Acrylic Sag lens

#### IESNA Classifications:

Cutoff: Ribbed acrylic Teardrop

#### IESNA Classifications:

Cutoff: Polycarbonate Sag

