



Wall Mount

LED Wall Sconce

100 line



Multiple styles for your application

Gardco LED 100 line wall sconces provide compact designs that provide wide flexibility in high performance illumination.

The broad choice in housing styles, optics and lamp combinations offers numerous options in balancing the illumination and aesthetic requirements of a project. Whether they are used on building entrances, over ATMs or on loading docks, there is no need to compromise appearance for performance. Available with 6 different low-profile forms to choose from, 100 line has you covered.

Benefits

- Multiple lumen packages with output ranging from 2,687 to 9,797 lumens
- Energy saving LEDs provide up to 110 LPW efficacy
- Three distribution patterns available in Type 2, 3, 4
- Emergency Battery Back Up available to provide path-of-egress illumination
- Energy saving control options, such as motion response and wireless controls

100 LED Wall Sconce

Luminaires that offer new opportunities to make a sustainable architectural statement and provide a much-needed alternative to glare-inducing wall packs. Used for illuminating building façades, loading docks and walkways.



101L
Trapezoidal Wedge



102L
Rounded Wedge



104L
Half Cylinder



106L
Quarter Sphere



107L
Gullwing Sconce

Ordering guide*

example: 101L-32L-700-NW-G1-3-120-IMR12-BZ

Prefix	Number of LEDs	Drive Current	LED Color - Generation	Distribution	Emergency	Voltage	Options		
							Controls	Electrical	Finish
<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
101L Trapezoidal Wedge LED wall sconce	16L 16 LEDs (1 modules)	530 530mA 700 700mA	CW-G1 Cool White 5700K, 70CRI Generation 1	2 Type 2 3 Type 3 4 Type 4	EBPC Emergency Battery Pack Cold Weather Leave blank to omit an emergency option	UNV 120-277V HVU 347-480V	DD 0-10V Dimming Driver DCC Dual Circuit Control DynaDimmer: Automatic Profile Dimming	Fusing F1 Single (120, 277, 347VAC) F2 Double (208, 240, 480VAC) F3 Canadian Double Pull (208, 240, 480VAC)	Textured BK Black WH White BZ Bronze DGY Dark Gray MGY Medium Gray Customer specified RAL Specify optional color or RAL (ex: OC-LGP or OC-RAL7024) CC Custom color (Must supply color chip for required factory quote)
102L Rounded Wedge LED wall sconce	32L 32 LEDs (2 modules)	650 650mA 1000 1000mA	NW-G1 Neutral White 4000K, 70CRI Generation 1			120 120V 208 208V 240 240V 277 277V 347 347V 480 480V	C550 Safety 50% Dimming CM50 Median 50% Dimming CE50 Economy 50% Dimming DA50 All Night 50% Dimming Photoelectric/Receptacle Systems (Twist Lock Receptacle - 101L only) PCB Photocontrol Button TLRD5 Twist Lock Receptacle 5-Pin TLRD7 Twist Lock Receptacle 7-Pin TLRPC Twist Lock Receptacle w/Photocell Infrared Motion Response Systems IMR12 Integral with #3 lens IMR13 Integral with #4 lens Limelight Wireless Controls LLC2 Module with #2 lens LLC3 Module with #3 lens		
104L Half Cylinder LED wall sconce		530 530mA 650 650mA							
106L Quarter Sphere LED wall sconce		700 700mA 1000 1000mA							
107L Gullwing Sconce LED wall sconce									

Luminaire Accessories (order separately)*

Mounting Accessories

Wall Mount

WS Wall Mounted Box for Surface Conduit

Controls Accessories

Wireless controls remote mount module

LLCR2-(F) #2 lens (specify F with finish)

LLCR3-(F) #3 lens (specify F with finish)

Wireless controls remote controller accessory

Wireless controls system offers a remote radio/sensor module that allows connectivity to Wireless system gateway. Remote module can be mounted to wall or pole with j-box supplied. May be specified by choosing one of two different lenses to accommodate a variety of mounting heights/sensor detection ranges. Must specify option DD on luminaires that are planned to be used with remote mount controllers.

* Prior to ordering, consult specification sheets on gardcolighting.com for the most current information, notes, and exclusions.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

