


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: V151 A B3 N D 70S E

Product Code	V151	Independence
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
Optics	B3	Type III Refractive Panels
	B5	Type V Refractive Panels
	T3	Type III Cutoff
	T5	Type V Cutoff
	V3	Vertical Rib Type III
	V5	Vertical Rib Type V
Photo Control	N	None
	B	Button Eye Photo Control
	R	Twist-lock Receptacle *1
Socket	D	Medium
	G	Mogul
Wattage	70S	70W HPS
	100S	100W HPS
	150S	150W HPS
	250S	250W HPS
	70H	70W MH
	100H	100W MH
	150H	150W PMH
	250H	250W PMH
Voltage	E	120V
	F	208V
	G	240V
	H	277V

*1 Twistlock receptacle (R) not available with 347V (K).
 *2 Available with Mogul base (G) socket only.
 *3 Available with Medium base (D) socket only.
 NOTE: "-LLR" to end of fixture coding for "Less Ladder Rest" option.

Specifications

HOUSING:

360 low-copper die-cast aluminum alloy . Tool-less lamp access. Tool-less ballast access. Twistlock ballast assembly with quick disconnects for easy maintenance. A weatherproof ballast assembly isolates the ballast from water and heat for longer life. The optional photo control eye or twist-lock receptacle is located in the ballast enclosure for easy access via a removable door. Hinged roof with stainless steel spring latch. All non-ferrous fasteners prevent corrosion and ensure longer life. Decorative cast aluminum Ladder Rest. Slip Fitter Dimensions: 3" I.D. x 3" deep .

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

OPTICAL ASSEMBLY:

Type III Refractive Panels. Type V Refractive Panels. Optically designed, U.V. stabilized, injection molded, acrylic refractive panels. Type III Cutoff. Type V Cutoff. Precision formed, segmented specular aluminum internal cutoff reflector with horizontal lamp mounting. Decorative frosted glass chimney. U.V. stabilized, injection molded, clear acrylic panels. Type III Vertical Rib (precision formed, segmented specular aluminum internal cutoff reflector with horizontal lamp mounting). Type V Vertical Rib (specular aluminum internal cutoff reflector with horizontal lamp mounting). (NOTE: No decorative frosted glass chimney.) U.V. stabilized, injection molded ribbed acrylic panels with internal vertical ribs. Tool-less removal panels for ease of cleaning.

V151 Independence

Post top

Specifications

LAMPING:

MH and HPS Medium base: E17. MH Mogul base: ED28. 70W-150W HPS Mogul base: ED23.5. 250W HPS Mogul base: E18.

ELECTRICAL ASSEMBLY:

Twistlock Ballast Assembly with Quick Disconnects for easy maintenance. Ballasts are HPF core and coil. 4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. 4kv rated mogul base porcelain socket. Nickel-plated screw shell with center contact.

BALLAST:

All HID ballasts are core and coil and regulated with power factors better than 90% (HPF). Ballast provides +/- 5% lamp power regulation with +/- 10% input voltage regulation. Ballasts are factory pre-wired and tested. Metal halide ballasts are capable of starting at -20° F or -30° C and HPS at -40°F or -40°C. NOTE: All ballasts are EISA / Title 20 / Title 24 compliant where applicable. (NOTE: For plug-in igniter option, consult factory.)

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Three-year limited warranty.

Height :

33 1/2" (85cm)

Width:

16 1/2" (42cm)

Max. EPA:

1.65 sq. ft.

Max. Weight:

28 lbs

IESNA Classifications:

Semi Cutoff: Refractive Panels

IESNA Classifications:

Cutoff: Cutoff optics

