

## Panel Load Schedule

Panel Type	Panel Dimensions	Contains	Panel Name
DRC1220FR-GL-ENC	14-9/16" W x 12-7/32" H x 3-9/16" D (370 mm W x 310 mm H x 91 mm D)	1 x DDRC1220FR-GL	
Mains	Voltage	Derated Total Allowed Load	Mounting Location
		130 Amps per DDRC1220FR-GL	

DEVICE	DDRC1220FR-GL				Device ID	
Channel	Room	Room #	Zone	Fixture	Circuit	Notes
1						
2						
3						
4						
5						
6						
7						
8						
9						
10						
11						
12						

refer to DDRC1220FR-GL data sheets for 277V channel restrictions