

Panel Load Schedule

Panel Type	Panel Dimensions	Contains	Panel Name
DBC516FR-ENC	14-9/16" W x 12-7/32" H x 3-9/16" D (370 mm W x 310 mm H x 91 mm D)	DDBC516FR	
Mains	Voltage	Derated Total Allowed Load	Mounting Location
		11 Amps per relay output, 20 mA per DALI output 10 mA (sink/source) per 1-10 V output per driver output	

DEVICE	DDBC516FR					Device ID	
RELAY OUTPUTS							
Channel	Room	Room #	Zone	Fixture	Circuit	Notes	
1							
2							
3							
4							
5							

refer to DDBC516FR data sheets for 277V channel restrictions

10V OUTPUTS						
Channel	Room	Room #	Zone	Fixture	Circuit	Notes
1						
2						
3						
4						
5						