









Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

★ High
★ Medium
★ Low
– NA

									
		Budget-grade	Value-grade	Value-grade	Value-grade	Spec-grade	Spec-grade	Spec-grade	Spec-grade
		Good	Better	Better	Better	Best	Best	Best	Best
		SDS Selectable LED Strip	FluxStream EZ LED Strip	FluxStream LED Strip	FluxStream LED Industrial	FluxSpace LED Linear (round)	FluxSpace LED Linear (square, lens & no lens)	FluxSpace LED Linear (wide uplight)	5F LED Industrial
Applications	Education	★	★	★	★	★	★	★	★
	Office	★	★	★	★	★	★	★	★
	Healthcare	–	★	★	★	★	★	★	★
	Retail	★	★	★	★	★	★	★	★
	Industrial	★	★	★	★	★	★	★	★
	Residential	★	★	★	★	★	★	★	–
Features	Sizes	2', 4', 8'	4', 8'	2', 3', 4', 8'	4', 8'	2', 3', 4', 8'	2', 3', 4', 8'	2', 3', 4', 8'	4', 8'
	Modular Wiring	–	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	–
	DLC	Standard	Standard	Std. & Prem.	Std. & Prem.	Std. & Prem.	Std. & Prem.	Std. & Prem.	Std. & Prem.
Performance	Lumen Output	1200, 1800, 2400, 3600, 4800, 7300, & 9800	4000, & 8000	2000, 3000, 4000, 5500, 6000, 7000, 8000, 11000, & 14000	2000, 3000, 4000, 5500, 6000, 7000, 8000, 11000, & 14000	2000, 3000, 4000, 4500, 5000, 6000, 7000, 8000, 9000, 10000, 12000, 14000, 16000, 18000, 20000, & 24000	2000, 3000, 4000, 4500, 5000, 6000, 7000, 8000, 9000, 10000, 12000, 14000, 16000, 18000, 20000, & 24000	2000, 3000, 4000, 4500, 5000, 6000, 7000, 8000, 9000, 10000, 12000, 14000, 16000, 18000, 20000, & 24000	4000, 5500, 7000, 8000, 11000, & 14000
	Color Render Index	80 CRI	80 CRI	80 CRI	80 CRI	80 CRI & 90 CRI	80 CRI & 90 CRI	80 CRI & 90 CRI	80 CRI
	Color Temperature	3500K, 4000K, & 5000K (color selectable)	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K
	Tunable White	–	–	–	–	2700-6500 TW	2700-6500 TW	2700-6500 TW	–
	Efficacy	up to 119lm/W	up to 104lm/W	up to 133lm/W	up to 133lm/W	up to 160lm/W	159 lm/W, 170 lm/W (no lens)	up to 161lm/W	up to 159lm/W
	Ambient Temp.	-20 to +40°C	-10 to +25°C	-20 to +40°C	-20 to +40°C	-20 to +50°C	-20 to +50°C	-20 to +50°C	-20 to +40°C
	Emergency	Yes, (field installed)	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Voltage	120-277V	120-277V	120V, 277V, 347V, & 120-277V	120V, 277V, 347V, & 120-277V	120V, 208V, 240V, 277V, 347V, & 120-277V	120V, 208V, 240V, 277V, 347V, & 120-277V	120V, 208V, 240V, 277V, 347V, & 120-277V	120-277V & 347V	
Lifespan	5 year warranty	5 year warranty	5 year warranty	5 year warranty	5 year warranty	5 year warranty	5 year warranty	5 year warranty	
Sensors/Controls	Sensor	–	Occupancy	Occupancy	Occupancy	Occupancy	Occupancy	Occupancy	Occupancy
	SpaceWise	–	–	Yes	Yes	Yes	Yes	Yes	Yes
	Interact Ready	–	–	Yes	Yes	Yes	Yes	Yes	–
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V
	Link	