



GENLYTE
SOLUTIONS

a signify business

Commercial Building Product Guide

2025

Tackle your lighting project quickly

Tight project timelines can't hold you back; get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip high performance luminaires from Genlyte Solutions brands include Lightolier, Day-Brite, Chloride, and Stonco Keene offerings.

Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project. Whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet-to-be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.



Design Build

Our stocking solutions are
now ready to go with your
stock and design ready needs



Stock ready

Stock and Flow
Ships in **2 days**



Design ready

Design Build
Ships in **5-10 days**

ModuLyte

Benefit from budget-friendly, commercial grade quality downlighting

Frame-optional design architecture and modular optics that can be field or factory-installed, you can be confident that ModuLyte is equipped to support a variety of project conditions.

Meet deadlines and project schedules without the stress by quickly connecting the light engine to its driver via a screw-on Communications Multipurpose Plenum (CPM) cable.

Selectable CCT and lumen output options create peace-of-mind during design and installation. Convenient switches make it easy for contractors to toggle between options to ensure lighting creates the right environment on any project.



Product Highlight



Flexibility at your fingertips

LIGHTOLIER




Product Highlight

Selectable Troffer (DSRT)

Robust low glare luminaire designed to provide three lumen and three CCT field selectable options per size at 80CRI. Available for use in recessed, suspended, and surface mount applications with optional daylight and occupancy sensor.

DSRT is 120-277V (UNV), with 0-10V dimming, and a 3in deep housing.



Slim, sturdy, and selectable

Day-Brite

Commercial building applications

Around the clock lighting solutions

Lighting is more than just a necessity; it's a vital component that can significantly impact a business's success. Invest in superior lighting solutions to transform a commercial space into a vibrant, efficient, and safe environment.

At [Genlyte Solutions](#), our portfolio of lighting brands offers the perfect solutions to create an optimal commercial environment. Explore our product suggestions to elevate your space and foster a more productive and comfortable atmosphere for your team and customers.

Stock
ready

2 day
shipping


Design
ready

5-10 day
shipping

Reception Area

 LEDALITE

Pique Duo



ArcForm Duo

ArcForm Duo & Pique Duo

- Flawless lens aesthetic with premium metal trims with a budget friendly price point
- Best in class efficacy with AccuRender CRI 90+ technology
- Low weight for ease of handling

Design
ready

 LEDALITE




SilkSpace Definition

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Accessible from the bottom with lift-and-shift lenses
- Interact Ready
- Available in traditional and uncommon grid sizes

Design
ready

 LEDALITE



DecoForm

- Unique open cavity one-piece regressed lens delivers a unique look that blends into the space
- Modular Top Tile adds color and depth easily
- Available in Recessed or Suspended mounts

Design
ready

LIGHTOLIER



LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock
ready

Design
ready

LIGHTOLIER



ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock
ready

Design
ready

LIGHTOLIER



THC & THP Track Heads

- Molded polycarbonate track attachment fitting and push tab
- Solid brass movable contact
- Integrated heat sink: Passive cooling, integrated into optic and driver housing
- (Matte) white and black finishes

Stock
ready

Corridors



LIGHTOLIER



ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

Day-Brite



NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock ready

Stock
ready

2 day
shipping


Design
ready

5-10 day
shipping

Conference & Meeting Rooms

 LEDALITE

Pique Duo



ArcForm Duo

ArcForm Duo & Pique Duo

- Flawless lens aesthetic with premium metal trims with a budget friendly price point
- Best in class efficacy with AccuRender CRI 90+ technology
- Low weight for ease of handling

Design
ready

 LEDALITE



SilkSpace Definition

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Accessible from the bottom with lift-and-shift lenses
- Interact Ready
- Available in traditional and uncommon grid sizes

Design
ready

 LEDALITE




Shine

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Multiple lumen packages and CCTs
- Accessible from below with lift-and-shift lenses
- Available in traditional and uncommon grid sizes

Design
ready

 LEDALITE



DecoForm

- Unique open cavity one-piece regressed lens delivers a unique look that blends into the space
- Modular Top Tile adds color and depth easily
- Available in Recessed or Suspended mounts

Design
ready

LIGHTOLIER



LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock
ready

Design
ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock
ready

Private Offices Spaces

LIGHTOLIER



LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock
ready

Design
ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock
ready

LIGHTOLIER



ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock
ready

Design
ready

Stock
ready

2 day
shipping

Design
ready

5-10 day
shipping

Exit and Emergency

CHLORIDE



Value+

- Snap together design
- Nicad battery
- Smaller compact housing
- Operating temperature range: 10°C (50°F) to 40°C (104°F)

Stock
ready

CHLORIDE



Value+ Low End Family

- Snap together design
- Nicad battery
- Smaller compact housing
- Operating temperature range: 10°C (50°F) to 40°C (104°F)

Stock
ready

CHLORIDE



44R Line Edge Lit

- A lower profile design is less obtrusive than traditional signs, making it more aesthetically appealing
- Ceiling, wall and end surface mounting

Stock
ready

Break Room

LIGHTOLIER



Modulyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

Day-Brite




NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock ready

Stock
ready

2 day
shipping

Design
ready

5-10 day
shipping

Restrooms

Day-Brite



NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock
ready

Day-Brite



FluxStream Wraparound

- Up to 100,000 hour predicted L70 LED lumen maintenance
- Suitable for damp locations
- Multiple mounting methods
- Ease of installation and maintenance

Stock
ready

Design
ready

Day-Brite



VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock
ready

LIGHTOLIER



ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock
ready

Design
ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock
ready

Storage Rooms

Day-Brite



SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock ready

Day-Brite



VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock ready

Day-Brite



NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Color selectable 4000K/5000K

Stock ready

LIGHTOLIER



ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



SlimSurface Downlight

- The thinnest available solution with an integral driver for existing J-boxes or new construction
- Glare controlling lens for comfortable light distribution
- Choice of design with square and round apertures

Stock ready

Design ready

Parking Lots & Exterior Lighting

Stonco KEENE



LytePro Wall

- Low-profile design
- Three sizes to accommodate multiple mounting heights
- Optical distributions offer full cutoff performance and excellent uniformity for precise wall and area illumination

Stock
ready

Design
ready

Stonco KEENE



LytePro Garage & Canopy

- SpiroGuide light engine that reduces glare and increases uniformity
- Luminous white uplight option with a halo bezel that glows
- Dimming controls and UL924 emergency options
- Lightweight and "click!" no-screw surface mounting

Design
ready

Stonco KEENE



LytePro Area

- Mounting to round or square pole without need for accessories
- Large bolt spacing range for easy retrofit application
- Button or twist-lock photocell, motion response, and field adjustable wattage

Stock
ready

Design
ready

Stonco KEENE



Garage & Canopy

- IP65 rated luminaire
- Die-cast round housing protect LEDs and driver
- DLC Premium
- 10kV surge protection
- 120-347V

Stock
ready

Stonco KEENE



Wall Pack

- Equipped with an integrated Daylight Sensor
- Rugged robust design
- Uniform illumination
- IP65 rated luminaire
- Die-cast housings protect LEDs and drivers

Stock
ready


Stonco KEENE



SlimFlood Selectable

- Can be mounted on the ground, wall, or pole
- Field selectable CCT of 3000K-5000K
- Field adjustable optics
- IP65 rated, 5-year limited warranty

Stock
ready



Day-Brite



VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock
ready

 **GARDCO**



QuickShip Poles

- Gardco straight round steel (SRS) or straight square steel (SSS) pole configurations

Design
ready

Get started with the Design Ready catalog



Ready to create your vision?

Check out the Design Ready website and catalog for ordering information on the product families fit for bringing your Design Build project to life. Scan the QR code to learn more.







© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 800-555-0500

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.